





HRS NO.	PART NO.	SLOTTING		
		A	B	C
CL541-0648-0	DF1B-4DS-2.5RC	2.5	7.5	5.5
0649-3	6	5.0	10.0	8.0
0650-2	8	7.5	12.5	10.5
0600-4	10	10.0	15.0	13.0
0601-7	12	12.5	17.5	15.5
0602-0	14	15.0	20.0	18.0
0603-2	16	17.5	22.5	20.5
0604-5	18	20.0	25.0	23.0
0605-8	20	22.5	27.5	25.5
0606-0	22	25.0	30.0	28.0
0607-3	24	27.5	32.5	30.5
0608-6	26	30.0	35.0	33.0
0609-9	28	32.5	37.5	35.5
0610-8	30	35.0	40.0	38.0
0612-3	34	40.0	45.0	43.0
0613-6	36	42.5	47.5	45.5
0615-1	40	47.5	52.5	50.5

TOLERANCES SEE TABLE FOR SPECIFIED, UNLESS OTHERWISE		
OVER	TO	TOLERANCE
6	6	±0.3
6	18	±0.5
18	50	±0.7
50	125	±1
125	250	±1.3
ANGULAR		±1°

- 1 4 PINS HEADER HAVE ONE PROJECTION AT CENTER. OTHER PINS HAVE 2PROJECTION AS PER DRAWING.
- 2 CONTACT NOS. <1, 2, 9, 10.... 40> AND NUMBER OF CONTACTS AND ONE SMALLER NUMBER OF CONTACTS SHALL BE MARKED.
- 3 FORMAT CHANGING.
- 4 UNLESS OTHERWISE SPECIFIED, THE TOLERANCE SHALL CONFORM TO THE TABLE 1.

NO.		MATERIAL		FINISH , REMARKS		1		POLYAMIDE		NATURAL<WHITE>, UL94V-0					
UNITS mm				SCALE 2 : 1		COUNT  3		DESCRIPTION OF REVISIONS DIS-H-005568		DESIGNED HT. SATO		CHECKED HK. UMEHARA		DATE 11. 03. 04	
 HIROSE ELECTRIC CO., LTD.				APPROVED : KJ. KATAYOSE		05. 01. 05		DRAWING NO.		EDC3-160092-02					
				CHECKED : TY. OMA		05. 01. 05		PART NO.		DF1B-*DS-2. 5RC					
				DESIGNED : TS. KUMAZAWA		05. 01. 05		CODE NO.		CL541					
				DRAWN : TS. KUMAZAWA		05. 01. 05				 					