

SPECIFICATIONS

Model Number:


MC24K3

Part Number:

19031618A Spec Number:26013730A00 April 8, 2013



Mechanical Drawing:



Motor:

Nominal Voltage	= 24 vdc
Operating Voltage Range	= 12 - 28 vdc
Nominal Running Current	= 0.440 amps
Locked Rotor Current	= 1.50 amps
Running Power	= 10.6 watts
Average Speed	= 4200 RPM
Bearings	= Ball
Max Air Flow	= 118 CFM
Acoustics	= 56.3 dBA

Construction:

Venturi: Plastic, Black, UL 94V-0
 Propeller: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 75,000 hours at 40°C.

Additional Features:

Brushless DC Motor	
Polarity Protected.	
Locked Rotor Protection.	
Automatic Restart Capability	
Operating Temperature:	-10°C to 70°C
Storage Temperature:	-40°C to 85°C

Agency Approvals:

UL

Termination:

12" Lead wires, AWG 22, UL 1061

Red: = (+) Power

Black: = (-) Ground