



PL12-82-P7P

3.7 m | 12 ft Standard Parabolic, Low VSWR Unshielded Antenna, single-polarized, 8.200–8.500 GHz, CPR112G, gray antenna, with flash, non-standard pack—two-piece reflector

General Specifications

Antenna Type	PL - Standard Parabolic, Low VSWR Unshielded Antenna, single-polarized
Diameter, nominal	3.7 m 12 ft
Packing	Non-standard pack
Reflector Construction	Two-piece reflector
Antenna Input	CPR112G
Antenna Color	Gray
Antenna Type	PL - Standard Parabolic, Low VSWR Unshielded Antenna, single-polarized
Diameter, nominal	3.7 m 12 ft
Flash Included	Yes
Polarization	Single

Electrical Specifications

Operating Frequency Band	8.200 – 8.500 GHz
Beamwidth, Horizontal	0.7 °
Beamwidth, Vertical	0.7 °
Cross Polarization Discrimination (XPD)	30 dB
Electrical Compliance	ETSI Class 1
Front-to-Back Ratio	54 dB
Gain, Low Band	46.8 dBi
Gain, Mid Band	47.0 dBi
Gain, Top Band	47.1 dBi
Operating Frequency Band	8.200 – 8.500 GHz
Radiation Pattern Envelope Reference (RPE)	2901C
Return Loss	30.7 dB
VSWR	1.06

Mechanical Specifications

Fine Azimuth Adjustment	±5°
Fine Elevation Adjustment	±5°
Mounting Pipe Diameter	115 mm 4.5 in
Net Weight	245 kg 540 lb
Side Struts, Included	1 inboard 1 outboard
Side Struts, Optional	2 outboard
Wind Velocity Operational	110 km/h 68 mph

PL12-82-P7P

Wind Velocity Survival Rating200 km/h | 124 mph

POWERED BY

Wind Forces At Wind Velocity Survival Rating


Angle α for MT Max	-125 °
Axial Force (FA)	34587 N 7775 lbf
Side Force (FS)	9441 N 2122 lbf
Twisting Moment (MT)	-15900 N•m
Weight with 1/2 in (12 mm) Radial Ice	528 kg 1164 lb
Zcg with 1/2 in (12 mm) Radial Ice	566 mm 22 in
Zcg without Ice	483 mm 19 in

PL12-82-P7P

POWERED BY



Wind Forces At Wind Velocity Survival Rating Image




Packed Dimensions

Note

Non-standard packing option—contact 1-800-255-1479 (North America), 1-800-873-2307 (International), or an Andrew representative

Antenna Dimensions And Mounting Information



ANTENNA DIMENSIONS All dimensions in mm (inches)			
A	3775 (148.5)	J	355 (14.0)
B	3915 (154.5)	K	1205 (47.5)
C	3050 (120)	L	215 (8.5)
D	685 (27.0)	M	330 (13)
E	145 (5.75)	N	1225 (48.25)
F	1430 (56.25)	P	1145 (45.0)
G	1525 (60)	R	790 (31.0)
H	835 (32.75)	S	1140 (44.75)

Regulatory Compliance/Certifications

Agency

ISO 9001:2008

Classification

Designed, manufactured and/or distributed under this quality management system

* Footnotes

Axial Force (FA)

Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Cross Polarization Discrimination (XPD)

The difference between the peak of the co-polarized main beam and the maximum cross-polarized signal over an angle twice the 3 dB beamwidth of the co-polarized main beam.

Front-to-Back Ratio

Denotes highest radiation relative to the main beam, at $180^\circ \pm 40^\circ$, across the band. Production antennas do not exceed rated values by more than 2 dB unless stated otherwise.

Gain, Mid Band

For a given frequency band, gain is primarily a function of antenna size. The gain of Andrew antennas is determined by either gain by comparison or by computer integration of the measured antenna patterns.

PL12-82-P7P

POWERED BY



Operating Frequency Band	Bands correspond with CCIR recommendations or common allocations used throughout the world. Other ranges can be accommodated on special order.
Packing	Andrew standard packing is suitable for export. Antennas are shipped as standard in totally recyclable cardboard or wire-bound crates (dependent on product). For your convenience, Andrew offers heavy duty export packing options.
Radiation Pattern Envelope Reference (RPE)	Radiation patterns determine an antenna's ability to discriminate against unwanted signals under conditions of radio congestion. Radiation patterns are dependent on antenna series, size, and frequency.
Return Loss	The figure that indicates the proportion of radio waves incident upon the antenna that are rejected as a ratio of those that are accepted.
Side Force (FS)	Maximum side force exerted on the mounting pipe as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
Twisting Moment (MT)	Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
VSWR	Maximum; is the guaranteed Peak Voltage-Standing-Wave-Ratio within the operating band.
Wind Velocity Operational	The wind speed where the antenna deflection is equal to or less than 0.1 degrees. In the case of ValuLine antennas, it is defined as a maximum deflection of 0.3 x the 3 dB beam width of the antenna.
Wind Velocity Survival Rating	The maximum wind speed the antenna, including mounts and radomes, where applicable, will withstand without permanent deformation. Realignment may be required. This wind speed is applicable to antenna with the specified amount of radial ice.