






NOTES:


1. MATERIAL: PHOS BRONZE
2. FINISH: SEE LEGEND
3. PRODUCT SPECIFICATION: PS-10-07
4. PACKAGING: LOOSE TERMINALS: PER PK-2759-001
CHAIN FORM TERMINALS: PER PK-6459-001
5. INSERTION FORCE OF TERMINAL INTO (2.54)/.100 CL HOUSING IS 11.1 N / 2.5 LBS MAX.
6. TERMINAL RETENTION IN HOUSING IS 26.7N / 6LBS MIN. WHEN PULLED AT THE RATE OF 25.4MM / 1 INCH PER MINUTE.
7. DIMENSIONS GIVEN ACROSS CENTERLINES ARE SYMMETRICAL ABOUT THOSE CENTERLINES WITHIN HALF THE TOTAL TOLERANCE.
8. CRIMP IS FOR 22-30 GA WIRE WITH (.157)/.062 DIA. INSULATION MAX.
9. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.



SECTION A-A
BACKGROUND OMITTED



SECTION B-B
BACKGROUND OMITTED




41572-*(***)*


MATERIAL	FORM
A= SEE NOTE 1	L=LOOSE BLANK=CHAIN PER DETAIL B
PLATING	
(P909) OVERALL HOT TIN DIP: (0.00254)/.000100 MIN.	
(154) OVERALL TIN: (0.00254)/.000100 MIN. OVER	
(0.00127)/.000050 MIN. NICKEL	

PART NO.	ENG NO.
08-65-0804	41572-A(P909)
08-65-0805	41572-A(P909)L
41572-0002	41572-A(154)

WINDING DETAIL B
NOT TO SCALE



SELECT GOLD LOCATION



ADD PK-6459-001 EC NO: UCP2014-0151 DRWN:MKIPPER 2013/07/18 CHKD:ANDERSON 2013/07/18 APPR:FSMITH 2013/07/24	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 10:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	TITLE KK (2.54)/.100 CRIMP TERMINAL 22-30 GA 6459 WITH CAT EAR molex	
				mm	INCH	DRAWN BY SAMIEC	DATE 1993/03/19	MATERIAL NO. SEE CHART				
			4 PLACES	± ---	± ---	CHECKED BY PATEL	DATE 1993/03/19					
			3 PLACES	± ---	± .010	APPROVED BY		DATE	DOCUMENT NO.			
			2 PLACES	± 0.25	± .015	SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
			1 PLACE	± 0.38	± ---							
			0 PLACE	±	±							
REV			ANGULAR ±1/2°							SHEET NO. 1 OF 1		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									