



13		12		11		10		9		8		7		6		5		4		3		2		1							
BLACK				WHITE				RED				BLUE				CLEAR				YELLOW				MIN		MAX		RECOVERED		LENGTH	
MATERIAL NUMBER		ENGINEERING NUMBER		MATERIAL NUMBER		ENGINEERING NUMBER		MATERIAL NUMBER		ENGINEERING NUMBER		MATERIAL NUMBER		ENGINEERING NUMBER		MATERIAL NUMBER		NUMBER ENGINEERING		EXPANDED ID "D"		RECOVERED ID		WALL THK REF		FEET/METERS					
192670015		PF-3/64-1BK		192670016		PF-3/64-1WT		192670017		PF-3/64-1RD		192670018		PF-3/64-1BL		192670019		PF-3/64-1CL		192670020		PF-3/64-1YL		.046/1.17		.023/0.58		.018/0.46			
192670045		PF-1/16-1BK		192670046		PF-1/16-1WT		192670047		PF-1/16-1RD		192670048		PF-1/16-1BL		192670049		PF-1/16-1CL		192670050		PF-1/16-1YL		.063/1.60		.031/0.79		.018/0.46			
192670075		PF-3/32-1BK		192670076		PF-3/32-1WT		192670077		PF-3/32-1RD		192670078		PF-3/32-1BL		192670079		PF-3/32-1CL		192670080		PF-3/32-1YL		.093/2.36		.046/1.17		.020/0.51			
192670105		PF-1/8-1BK		192670106		PF-1/8-1WT		192670107		PF-1/8-1RD		192670108		PF-1/8-1BL		192670109		PF-1/8-1CL		192670110		PF-1/8-1YL		.125/3.18		.062/1.57		.020/0.51			
192670135		PF-3/16-1BK		192670136		PF-3/16-1WT		192670137		PF-3/16-1RD		192670138		PF-3/16-1BL		192670139		PF-3/16-1CL		192670140		PF-3/16-1YL		.187/4.75		.093/2.36		.020/0.51			
192670165		PF-1/4-1BK		192670166		PF-1/4-1WT		192670167		PF-1/4-1RD		192670168		PF-1/4-1BL		192670169		PF-1/4-1CL		192670170		PF-1/4-1YL		.250/6.35		.125/3.18		.025/0.64			
192670195		PF-3/8-1BK		192670196		PF-3/8-1WT		192670197		PF-3/8-1RD		192670198		PF-3/8-1BL		192670199		PF-3/8-1CL		192670200		PF-3/8-1YL		.375/9.53		.187/4.75		.025/0.64			
192670225		PF-1/2-1BK		192670226		PF-1/2-1WT		192670227		PF-1/2-1RD		192670228		PF-1/2-1BL		192670229		PF-1/2-1CL		192670230		PF-1/2-1YL		.500/12.70		.250/6.35		.025/0.64			
192670255		PF-3/4-1BK		192670256		PF-3/4-1WT		192670257		PF-3/4-1RD		192670258		PF-3/4-1BL		192670259		PF-3/4-1CL		192670260		PF-3/4-1YL		.750/19.05		.375/9.53		.030/0.76			
192670285		PF-1-1BK		192670286		PF-1-1WT		192670287		PF-1-1RD		192670288		PF-1-1BL		192670289		PF-1-1CL		192670290		PF-1-1YL		1.000/25.40		.500/12.70		.035/0.89			
192670315		PF-1-1/2-1BK		192670316		PF-1-1/2-1WT		192670317		PF-1-1/2-1RD		192670318		PF-1-1/2-1BL		192670319		PF-1-1/2-1CL		192670320		PF-1-1/2-1YL		1.500/38.10		.750/19.05		.040/1.02			
192670345		PF-2-1BK		192670346		PF-2-1WT		192670347		PF-2-1RD		192670348		PF-2-1BL		192670349		PF-2-1CL		192670350		PF-2-1YL		2.000/50.80		1.000/25.40		.045/1.14			
192670375		PF-3-1BK		192670376		PF-3-1WT		192670377		PF-3-1RD		192670378		PF-3-1BL		192670379		PF-3-1CL		192670380		PF-3-1YL		3.000/76.20		1.500/38.10		.050/1.27			
192670405		PF-4-1BK														192670409		PF-3-1CL						4.000/101.60		2.000/50.80		.055/1.40			
192670033		PF-3/64-4BK		192670034		PF-3/64/4WT		192670035		PF-3/64-4RD		192670036		PF-3/64-4BL		192670037		PF-3/64-4CL		192670038		PF-3/64-4YL		.046/1.17		.023/0.58		.018/0.46			
192670063		PF-1/16-4BK		192670064		PF-1/16-4WT		192670065		PF-1/16-4RD		192670066		PF-1/16-4BL		192670067		PF-1/16-4CL		192670068		PF-1/16-4YL		.063/1.60		.031/0.79		.018/0.46			
192670093		PF-3/32-4BK		192670094		PF-3/32-4WT		192670095		PF-3/32-4RD		192670096		PF-3/32-4BL		192670097		PF-3/32-4CL		192670098		PF-3/32-4YL		.093/2.36		.046/1.17		.020/0.51			
192670123		PF-1/8-4BK		192670124		PF-1/8-4WT		192670125		PF-1/8-4RD		192670126		PF-1/8-4BL		192670127		PF-1/8-4CL		192670128		PF-1/8-4YL		.125/3.18		.062/1.57		.020/0.51			
192670153		PF-3/16-4BK		192670154		PF-3/16-4WT		192670155		PF-3/16-4RD		192670156		PF-3/16-4BL		192670157		PF-3/16-4CL		192670158		PF-3/16-4YL		.187/4.75		.093/2.36		.020/0.51			
192670183		PF-1/4-4BK		192670184		PF-1/4-4WT		192670185		PF-1/4-4RD		192670186		PF-1/4-4BL		192670187		PF-1/4-4CL		192670188		PF-1/4-4YL		.250/6.35		.125/3.18		.025/0.64			
192670213		PF-3/8-4BK		192670214		PF-3/8-4WT		192670215		PF-3/8-4RD		192670216		PF-3/8-4BL		192670217		PF-3/8-4CL		192670218		PF-3/8-4YL		.375/9.53		.187/4.75		.025/0.64			
192670243		PF-1/2-4BK		192670244		PF-1/2-4WT		192670245		PF-1/2-4RD		192670246		PF-1/2-4BL		192670247		PF-1/2-4CL		192670248		PF-1/2-4YL		.500/12.70		.250/6.35		.025/0.64			
192670273		PF-3/4-4BK		192670274		PF-3/4-4WT		192670275		PF-3/4-4RD		192670276		PF-3/4-4BL		192670277		PF-3/4-4CL		192670278		PF-3/4-4YL		.750/19.05		.375/9.53		.030/0.76			
192670303		PF-1-4BK		192670304		PF-1-4WT		192670305		PF-1-4RD		192670306		PF-1-4BL		192670307		PF-1-4CL		192670308		PF-1-4YL		1.000/25.40		.500/12.70		.035/0.89			
192670333		PF-1-1/2-4BK		192670334		PF-1-1/2-4WT		192670335		PF-1-1/2-4RD		192670336		PF-1-1/2-4BL		192670337		PF-1-1/2-4CL		192670338		PF-1-1/2-4YL		1.500/38.10		.750/19.05		.040/1.02			
192670363		PF-2-4BK		192670364		PF-2-4WT		192670365		PF-2-4RD		192670366		PF-2-4BL		192670367		PF-2-4CL		192670368		PF-2-4YL		2.000/50.80		1.000/25.40		.045/1.14			
192670393		PF-3-4BK		192670394		PF-3-4WT		192670395		PF-3-4RD		192670396		PF-3-4BL		192670397		PF-3-4CL		192670398		PF-3-4YL		3.000/76.20		1.500/38.10		.050/1.27			
192670423		PF-4-4BK														192670427		PF-4-4CL						4.000/101.60		2.000/50.80		.055/1.40			
192670039		PF-3/64-5BK		192670040		PF-3/64-5WT		192670041		PF-3/64-5RD		192670042		PF-3/64-5BL		192670043		PF-3/64-5CL		192670044		PF-3/64-5YL		.046/1.17		.023/0.58		.018/0.46			
192670069		PF-1/16-5BK		192670070		PF-1/16-5WT		192670071		PF-1/16-5RD		192670072		PF-1/16-5BL		192670073		PF-1/16-5CL		192670074		PF-1/16-5YL		.063/1.60		.031/0.79		.018/0.46			
192670099		PF-3/32-5BK		192670100		PF-3/32-5WT		192670101		PF-3/32-5RD		192670102		PF-3/32-5BL		192670103		PF-3/32-5CL		192670104		PF-3/32-5YL		.093/2.36		.046/1.17		.020/0.51			
192670129		PF-1/8-5BK		192670130		PF-1/8-5WT		192670131		PF-1/8-5RD		192670132		PF-1/8-5BL		192670133		PF-1/8-5CL		192670134		PF-1/8-5YL		.125/3.18		.062/1.57		.020/0.51			
192670159		PF-3/16-5BK		192670160		PF-3/16-5WT		192670161		PF-3/16-5RD		192670162		PF-3/16-5BL		192670163		PF-3/16-5CL		192670164		PF-3/16-5YL		.187/4.75		.093/2.36		.020/0.51			
192670189		PF-1/4-5BK		192670190		PF-1/4-5WT		192670191		PF-1/4-5RD		192670192		PF-1/4-5BL		192670193		PF-1/4-5CL		192670194		PF-1/4-5YL		.250/6.35		.125/3.18		.025/0.64			
192670219		PF-3/8-5BK		192670220		PF-3/8-5WT		192670221		PF-3/8-5RD		192670222		PF-3/8-5BL		192670223		PF-3/8-5CL		192670224		PF-3/8-5YL		.375/9.53		.187/4.75		.025/0.64			
192670249		PF-1/2-5BK		192670250		PF-1/2-5WT		192670251		PF-1/2-5RD		192670252		PF-1/2-5BL		192670253		PF-1/2-5CL		192670254		PF-1/2-5YL		.500/12.70		.250/6.35		.025/0.64			
SALES DRAWING																															
NOTES: 1. MATERIAL: POLYOLEFIN 2. OTHER CUT LENGTHS ARE AVAILABLE. ⑧ 3. PARTS ARE RoHS COMPLIANT. CHANGED TITLE EC NO: IPG2013-0982 2013/01/10 DRWNGROJAS01 2013/01/10 CHKD: JMACNEIL 2013/01/31 APPR: JMACNEIL REV B1 QUALITY SYMBOLS ▽=0 ▽=0 GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ± ---° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DIMENSION STYLE IN/MM DRAWN BY DATE BENDERLE 2004/08/04 CHECKED BY DATE R DEROSS 2004/08/04 APPROVED BY DATE R DEROSS 2004/08/04 MATERIAL NO. SEE CHART SCALE 1:1 DESIGN UNITS INCH THIRD ANGLE PROJECTION TITLE ⑧ POLYOLEFIN HEAT SHRINK TUBING 19267 SERIES SD-19267-001 SHEET NO. 1 OF 1 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																															
tb_frame_C_P_AM_T		12		11		10		9		8		7		6		5		4		3		2		1							

13		12		11		10		9		8		7		6		5		4		3		2		1	
BLACK		WHITE		RED		CLEAR		YELLOW		MIN		MAX		RECOVERED		LENGTH		FEET/METERS							
MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	EXPANDED ID "D"	RECOVERED ID	WALL THK REF													
192680018	PFV-3/64-1BK	192680019	PFV-3/64-1WT	192680020	PFV-3/64-1RD	192680021	PFV-3/64-1CL	192680022	PFV-3/64-1YL	.046/1.17	.023/0.58	.018/0.46													
192680043	PFV-1/16-1BK	192680044	PFV-1/16-1WT	192680045	PFV-1/16-1RD	192680046	PFV-1/16-1CL	192680047	PFV-3/32-1YL	.063/1.60	.032/0.81	.018/0.46													
192680068	PFV-3/32-1BK	192680069	PFV-3/32-1WT	192680070	PFV-3/32-1RD	192680071	PFV-3/32-1CL	192680072	PFV-3/32-1YL	.093/2.36	.046/1.17	.020/0.51													
192680093	PFV-1/8-1BK	192680094	PFV-1/8-1WT	192680095	PFV-1/8-1RD	192680096	PFV-1/8-1CL	192680097	PFV-1/8-1YL	.125/3.18	.063/1.60	.020/0.51													
192680118	PFV-3/16-1BK	192680119	PFV-3/16-1WT	192680120	PFV-3/16-1RD	192680121	PFV-3/16-1CL	192680122	PFV-3/16-1YL	.187/4.75	.093/2.36	.020/0.51													
192680143	PFV-1/4-1BK	192680144	PFV-1/4-1WT	192680145	PFV-1/4-1RD	192680146	PFV-1/4-1CL	192680147	PFV-1/4-1YL	.250/6.35	.125/3.18	.025/0.64													
192680193	PFV-3/8-1BK	192680194	PFV-3/8-1WT	192680195	PFV-3/8-1RD	192680196	PFV-3/8-1CL	192680197	PFV-3/8-1YL	.375/9.53	.187/4.75	.025/0.64													
192680218	PFV-1/2-1BK	192680219	PFV-1/2-1WT	192680220	PFV-1/2-1RD	192680221	PFV-1/2-1CL	192680222	PFV-1/2-1YL	.500/12.70	.250/6.35	.025/0.64													
192680243	PFV-5/8-1BK	192680244	PFV-5/8-1WT	192680245	PFV-5/8-1RD	192680246	PFV-5/8-1CL	192680247	PFV-5/8-1YL	.625/15.88	.313/7.95	.025/0.64													
192680268	PFV-3/4-1BK	192680269	PFV-3/4-1WT	192680270	PFV-3/4-1RD	192680271	PFV-3/4-1CL	192680272	PFV-3/4-1YL	.750/19.05	.375/9.53	.035/0.89													
192680293	PFV-1-1BK	192680294	PFV-1-1WT	192680295	PFV-1-1RD	192680296	PFV-1-1CL	192680297	PFV-1-1YL	1.000/25.40	.500/12.70	.035/0.89													
192680318	PFV-1-1/4-1BK	192680319	PFV-1-1/4-1WT	192680320	PFV-1-1/4-1RD	192680321	PFV-1-1/4-1CL	192680322	PFV-1-1/4-1YL	1.250/31.75	.630/16.00	.035/0.89													
192680343	PFV-1-1/2-1BK	192680344	PFV-1-1/2-1WT	192680345	PFV-1-1/2-1RD	192680346	PFV-1-1/2-1CL	192680347	PFV-1-1/2-1YL	1.500/38.10	.750/19.05	.040/1.02													
192680368	PFV-2-1BK	192680369	PFV-2-1WT	192680370	PFV-2-1RD	192680371	PFV-2-1CL	192680372	PFV-2-1YL	2.000/50.80	1.000/25.40	.045/1.14													
192680393	PFV-3-1BK	192680394	PFV-3-1WT	192680395	PFV-3-1RD	192680396	PFV-3-1CL	192680397	PFV-3-1YL	3.000/76.20	1.500/38.10	.050/1.27													
192680418	PFV-4-1BK	192680419	PFV-4-1WT	192680420	PFV-4-1RD	192680421	PFV-4-1CL	192680422	PFV-4-1YL	4.000/101.60	2.000/50.80	.055/1.40													
192680033	PFV-3/64-4BK	192680034	PFV-3/64-4WT	192680035	PFV-3/64-4RD	192680036	PFV-3/64-4CL	192680037	PFV-3/64-4YL	.046/1.17	.023/0.58	.018/0.46													
192680058	PFV-1/16-4BK	192680059	PFV-1/16-4WT	192680060	PFV-1/16-4RD	192680061	PFV-1/16-4CL	192680062	PFV-1/16-4YL	.063/1.60	.032/0.81	.018/0.46													
192680083	PFV-3/32-4BK	192680084	PFV-3/32-4WT	192680085	PFV-3/32-4RD	192680086	PFV-3/32-4CL	192680087	PFV-3/32-4YL	.093/2.36	.046/1.17	.020/0.51													
192680108	PFV-1/8-4BK	192680109	PFV-1/8-4WT	192680110	PFV-1/8-4RD	192680111	PFV-1/8-4CL	192680112	PFV-1/8-4YL	.125/3.18	.063/1.60	.020/0.51													
192680133	PFV-3/16-4BK	192680134	PFV-3/16-4WT	192680135	PFV-3/16-4RD	192680136	PFV-3/16-4CL	192680137	PFV-3/16-4YL	.187/4.75	.093/2.36	.020/0.51													
192680158	PFV-1/4-4BK	192680159	PFV-1/4-4WT	192680160	PFV-1/4-4RD	192680161	PFV-1/4-4CL	192680162	PFV-1/4-4YL	.250/6.35	.125/3.18	.025/0.64													
192680208	PFV-3/8-4BK	192680209	PFV-3/8-4WT	192680210	PFV-3/8-4RD	192680211	PFV-3/8-4CL	192680212	PFV-3/8-4YL	.375/9.53	.187/4.75	.025/0.64													
192680233	PFV-1/2-4BK	192680234	PFV-1/2-4WT	192680235	PFV-1/2-4RD	192680236	PFV-1/2-4CL	192680237	PFV-1/2-4YL	.500/12.70	.250/6.35	.025/0.64													
192680258	PFV-5/8-4BK	192680259	PFV-5/8-4WT	192680260	PFV-5/8-4RD	192680261	PFV-5/8-4CL	192680262	PFV-5/8-5YL	.625/15.88	.312/7.95	.025/0.64													
192680283	PFV-3/4-4BK	192680284	PFV-3/4-4WT	192680285	PFV-3/4-4RD	192680286	PFV-3/4-4CL	192680287	PFV-3/4-4YL	.750/19.05	.375/9.53	.035/0.89													
192680308	PFV-1-4BK	192680309	PFV-1-4WT	192680310	PFV-1-4RD	192680311	PFV-1-4CL	192680312	PFV-1-4YL	1.000/25.40	.500/12.70	.035/0.89													
192680333	PFV-1-1/4-4BK	192680334	PFV-1-1/4-4WT	192680335	PFV-1-1/4-4RD	192680336	PFV-1-1/4-4CL	192680337	PFV-1-1/4-4YL	1.250/31.75	.630/16.00	.035/0.89													
192680038	PFV-3/64-5BK	192680039	PFV-3/64-5WT	192680040	PFV-3/64-5RD	192680041	PFV-3/64-5CL	192680042	PFV-3/64-5YL	.046/1.17	.023/0.58	.018/0.46													
192680063	PFV-1/16-5BK	192680064	PFV-1/16-5WT	192680065	PFV-1/16-5RD	192680066	PFV-1/16-5CL	192680067	PFV-1/16-5YL	.063/1.60	.032/0.81	.018/0.46													
192680088	PFV-3/32-5BK	192680089	PFV-3/32-5WT	192680090	PFV-3/32-5RD	192680091	PFV-3/32-5CL	192680092	PFV-3/32-5YL	.093/2.36	.046/1.17	.020/0.51													
192680113	PFV-1/8-5BK	192680114	PFV-1/8-5WT	192680115	PFV-1/8-5RD	192680116	PFV-1/8-5CL	192680117	PFV-1/8-5YL	.125/3.18	.063/1.60	.020/0.51													
192680138	PFV-3/16-5BK	192680139	PFV-3/16-5WT	192680140	PFV-3/16-5RD	192680141	PFV-3/16-5CL	192680142	PFV-3/16-5YL	.187/4.75	.093/2.36	.020/0.51													
192680163	PFV-1/4-5BK	192680164	PFV-1/4-5WT	192680165	PFV-1/4-5RD	192680166	PFV-1/4-5CL	192680167	PFV-1/4-5YL	.250/6.35	.125/3.18	.025/0.64													
192680213	PFV-3/8-5BK	192680214	PFV-3/8-5WT	192680215	PFV-3/8-5RD	192680216	PFV-3/8-5CL	192680217	PFV-3/8-5YL	.375/9.53	.187/4.75	.025/0.64													
192680238	PFV-1/2-5BK	192680239	PFV-1/2-5WT	192680240	PFV-1/2-5RD	192680241	PFV-1/2-5CL	192680242	PFV-1/2-5YL	.500/12.70	.250/6.35	.025/0.64													
192680263	PFV-5/8-5BK	192680264	PFV-5/8-5WT	192680265	PFV-5/8-5RD	192680266	PFV-5/8-5CL	192680267	PFV-5/8-5YL	.625/15.88	.313/7.95	.025/0.64													
192680358	PFV-1-1/2-4BK	192680359	PFV-1-1/2-4WT	192680360	PFV-1-1/2-4RD	192680361	PFV-1-1/2-4CL	192680362	PFV-1-1/2-4YL	1.500/38.10	.750/19.05	.040/1.02													
192680383	PFV-2-4BK	192680384	PFV-2-4WT	192680385	PFV-2-4RD	192680386	PFV-2-4CL	192680387	PFV-2-4YL	2.000/50.80	1.000/25.4	.045/1.14													
192680408	PFV-3-4BK	192680409	PFV-3-4WT	192680410	PFV-3-4RD	192680411	PFV-3-4CL	192680412	PFV-3-4YL	3.000/76.20	1.500/38.10	.050/1.27													
192680433	PFV-4-4BK	192680434	PFV-4-4WT	192680435	PFV-4-4RD	192680436	PFV-4-4CL	192680437	PFV-4-4YL	4.000/101.60	2.000/50.80	.055/1.40													

	10	9	8	7	6	5	4	3	2	19269
	BLACK		CLEAR		MIN	MAX	RECOVERED			
	MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	EXPANDED ID "D"	RECOVERED ID	WALL THK REF	LENGTH FEET/METERS		
F	192690008	PF3-1/8-1BK			.125/3.018	.040/1.02	.038/0.97	4.0/1.2		
	192690013	PF3-3/16-1BK			.187/4.75	.060/1.52	.045/1.14			
			192690043	PF3-3/16-1CL	.225/5.72	.050/1.27	.045/1.14			
	192690018	PF3-1/4-1BK			.250/6.35	.080/2.03	.047/1.19			
			192690048	PF3-1/4-1CL	.293/7.44	.065/1.65	.047/1.19			
	192690023	PF3-3/8-1BK			.375/9.53	.120/3.05	.050/1.27			
			192690053	PF3-3/8-1CL	.427/10.85	.095/2.43	.050/1.27			
E	192690028	PF3-1/2-1BK			.500/12.70	.157/3.99	.055/1.40			
			192690058	PF3-1/2-1CL	.700/17.78	.175/4.45	.055/1.40			
	192690033	PF3-3/4-1BK			.750/19.05	.230/5.84	.065/1.65			
	192690038	PF3-1-1BK			1.000/25.40	.320/8.13	.075/1.90			



SALES DRAWING

NOTES:



(A1)

- MATERIAL: POLYOLEFIN WITH ADHESIVE LINER.
- OTHER CUT LENGTHS ARE AVAILABLE.
- PARTS ARE RoHS COMPLIANT.

(A1)

CORRECT MAT'L EC NO: IFG2013-0982 DRWN:GROJASO1 2013/01/10 CHKD:JMACNEIL 2013/01/10 APPR:JMACNEIL 2013/01/31	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION				
				mm	INCH	DRAWN BY BENDERLE	DATE 2004/09/23	TITLE (A1) POLYOLEFIN W/ ADHESIVE LINER HEAT SHRINK TUBING 19269 SERIES					
			4 PLACES	± ---	± ---	CHECKED BY	DATE						
			3 PLACES	± ---	± .010	R DEROSS	2004/09/23	MOLEX MOLEX INCORPORATED					
			2 PLACES	± 0.25	± .02	APPROVED BY	DATE						
			1 PLACE	± 0.51	± ---	R DEROSS	2004/09/23	DOCUMENT NO. SD-19269-001					
			ANGULAR ± ---°		MATERIAL NO.	SHEET NO. 1 OF 1							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART								
			A1	REV	SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

10		9		8		7		6		5		4		3		2		19270	
BLACK		RED		MIN		MAX		RECOVERED		LENGTH FEET/METERS		4.0/1.2							
MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	EXPANDED ID "D"	RECOVERED ID	WALL THK REF													
192700008	PFB-04-1BK	192700013	PFB-04-1RD	.400/10.16	.150/3.81	.060/1.53													
192700018	PFB-07-1BK	192700023	PFB-07-1RD	.750/19.05	.220/5.59	.095/2.41													
192700028	PFB-11-1BK	192700033	PFB-11-1RD	1.100/27.94	.375/9.53	.120/3.05													
192700038	PFB-15-1BK	192700043	PFB-15-1RD	1.500/38.10	.500/19.05	.140/3.56													
192700048	PFB-20-1BK	192700053	PFB-20-1RD	2.000/50380	.750/19.05	.155/3.98													
192700058	PFB-30-1BK	192700063	PFB-30-1RD	3.540/89.92	1.18/29.97	.155/3.98													
192700068	PFB-40-1BK	192700073	PFB-40-1RD	4.72/119.89	1.57/39.88	.170/4.37													



SALES DRAWING

NOTES:

- 1. MATERIAL: POLYOLEFIN
- 2. OTHER CUT LENGTHS ARE AVAILABLE.
- 3. PARTS ARE RoHS COMPLIANT.

(A1)

CHANGED TITLE		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: IPG2013-0982		DRAWN: GJAS01		mm		IN/MM		1:1		INCH		THIRD ANGLE PROJECTION	
2013/01/10		2013/01/10		4 PLACES ± --- ± ---		DRAWN BY		DATE		TITLE			
CHKD: JMACNEIL		2013/01/10		3 PLACES ± --- ± .010		BENDERLE		2004/09/23		(A1)		POLYOLEFIN	
APPR: JMACNEIL		2013/01/31		2 PLACES ± 0.25 ± .02		CHECKED BY		DATE		2004/09/23		HEAT SHRINK TUBING	
				1 PLACE ± 0.51 ± ---		R DEROSS		2004/09/23		MOLEX INCORPORATED		19270 SERIES	
				ANGULAR ± --- °		APPROVED BY		DATE		2004/09/23			
						R DEROSS							
						MATERIAL NO.		DOCUMENT NO.		SD-19270-001		SHEET NO.	
						SEE CHART						1 OF 1	
						SIZE B							