

# Field and Factory Programmable Spread Spectrum Clock Generator for EMI Reduction

## Features

- Wide Operating Output (SSCLK) Frequency Range
  - 3 MHz to 200 MHz
- Programmable Spread Spectrum with nominal 31.5 kHz Modulation Frequency
  - Center Spread:  $\pm 0.25\%$  to  $\pm 2.5\%$
  - Down Spread:  $-0.5\%$  to  $-5.0\%$
- Input frequency range
  - External Crystal: 8 to 30 MHz Fundamental Crystals
  - External Reference: 8 to 166 MHz Clock
- Integrated Phase-Locked Loop (PLL)
- Field Programmable devices available
- Programmable Crystal Load Capacitor Tuning Array
- Low Cycle-to-cycle Jitter
- Spread Spectrum on/off function
- Powerdown or Output Enable function
- Commercial and Industrial temperature ranges
- 3.3 V operation
- 8-pin TSSOP and SOIC packages

## Functional Description

The CY25100 is a Spread Spectrum Clock Generator (SSCG) IC used to reduce EMI found in today's high speed digital electronic systems.

The device uses a Cypress proprietary PLL and Spread Spectrum Clock (SSC) technology to synthesize and modulate the frequency of the input clock. By frequency modulating the clock, the measured EMI at the fundamental and harmonic frequencies are greatly reduced. This reduction in radiated energy can significantly reduce the cost of complying with regulatory agency (EMC) requirements and improve time-to-market without degrading system performance.


The CY25100 uses a factory or field-programmable configuration memory array to synthesize output frequency, spread percentage, crystal load capacitor, reference clock output on/off, spread spectrum on/off function, and PD#/OE options.

The spread percentage is programmed to either center spread or down spread with various spread percentages. The range for center spread is from  $\pm 0.25\%$  to  $\pm 2.50\%$ . The range for down spread is from  $-0.5\%$  to  $-5.0\%$ .

The input to the CY25100 can either be a crystal or a clock signal. The CY25100 has two clock outputs: REFCLK and SSCLK. The non-spread spectrum REFCLK output has the same frequency as the input of the CY25100.

For a complete list of related documentation, click [here](#).

## Logic Block Diagram




## Contents

|                                                      |          |                                                      |           |
|------------------------------------------------------|----------|------------------------------------------------------|-----------|
| <b>Pinouts</b> .....                                 | <b>3</b> | <b>DC Electrical Characteristics</b> .....           | <b>6</b>  |
| <b>Pin Description</b> .....                         | <b>3</b> | <b>AC Electrical Characteristics</b> .....           | <b>7</b>  |
| <b>Programming Description</b> .....                 | <b>4</b> | <b>Application Circuit</b> .....                     | <b>8</b>  |
| <b>Field Programmable CY25100</b> .....              | <b>4</b> | <b>Switching Waveforms</b> .....                     | <b>9</b>  |
| CyberClocks™ Online Software .....                   | 4        | <b>Informational Graphs</b> .....                    | <b>10</b> |
| CY3672 Programmer and                                |          | <b>Ordering Information</b> .....                    | <b>12</b> |
| CY3690/CY3691 Socket Adapters .....                  | 4        | Possible Configurations .....                        | 12        |
| Factory Programmable CY25100 .....                   | 4        | Ordering Code Definitions .....                      | 13        |
| <b>Product Functions</b> .....                       | <b>4</b> | <b>Package Diagrams</b> .....                        | <b>13</b> |
| Input Frequency (XIN, Pin 3 and XOUT, Pin 2) .....   | 4        | <b>Acronyms</b> .....                                | <b>15</b> |
| CXIN and CXOUT (Pin 3 and Pin 2) .....               | 4        | <b>Document Conventions</b> .....                    | <b>15</b> |
| Output Frequency (SSCLK, Pin 7) .....                | 4        | Units of Measure .....                               | 15        |
| Spread Percentage (SSCLK, Pin 7) .....               | 4        | <b>Document History Page</b> .....                   | <b>16</b> |
| Reference Output (REFOUT, Pin 6) .....               | 4        | <b>Sales, Solutions, and Legal Information</b> ..... | <b>18</b> |
| Modulation Frequency .....                           | 4        | Worldwide Sales and Design Support .....             | 18        |
| Power Down or Output Enable (PD# or OE, Pin 4) ..... | 4        | Products .....                                       | 18        |
| <b>Absolute Maximum Rating</b> .....                 | <b>5</b> | PSoC® Solutions .....                                | 18        |
| <b>Recommended Crystal Specifications</b> .....      | <b>5</b> | Cypress Developer Community .....                    | 18        |
| <b>Operating Conditions</b> .....                    | <b>5</b> | Technical Support .....                              | 18        |

## Pinouts

Figure 1. CY25100 8-pin SOIC/TSSOP



## Pin Description

| Pin | Name      | Type   | Description                                                                                                                                                                                                                                                               |
|-----|-----------|--------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1   | VDD       | Power  | 3.3 V power supply.                                                                                                                                                                                                                                                       |
| 2   | XOUT      | Output | Crystal output. Leave this pin floating if external clock is connected to pin 3.                                                                                                                                                                                          |
| 3   | XIN/CLKIN | Input  | Crystal input or reference clock input.                                                                                                                                                                                                                                   |
| 4   | PD#/OE    | Input  | User has the option of choosing either PD# or OE function.<br>Power Down pin: Active LOW. If PD# = 0, PLL and crystal oscillator circuit are powered down, and outputs are weakly pulled low.<br>Output Enable pin: Active HIGH. If OE = 1, SSCLK and REFCLK are enabled. |
| 5   | VSS       | Power  | Power supply ground.                                                                                                                                                                                                                                                      |
| 6   | REFCLK    | Output | Buffered reference output.                                                                                                                                                                                                                                                |
| 7   | SSCLK     | Output | Spread spectrum clock output.                                                                                                                                                                                                                                             |
| 8   | SSON#     | Input  | Spread spectrum control: Active LOW. 0 = spread on. 1 = spread off.                                                                                                                                                                                                       |

Table 1. User Specified Variables

| Pin Function | Input Frequency | Total Crystal Load Capacitance | Output Frequency | Spread Percent (0.5% – 5%, 0.25% granularity) | Reference Output | Power Down or Output Enable |
|--------------|-----------------|--------------------------------|------------------|-----------------------------------------------|------------------|-----------------------------|
| Pin Name     | XIN and XOUT    | XIN and XOUT                   | SSCLK            | SSCLK                                         | REFOUT           | PD#/OE                      |
| Pin#         | 3 and 2         | 3 and 2                        | 7                | 7                                             | 6                | 4                           |
| Unit         | MHz             | pF                             | MHz              | % and Center- or Down-spread                  | On or Off        | Select PD# or OE            |
|              | USER SPECIFIED  | USER SPECIFIED                 | USER SPECIFIED   | USER SPECIFIED                                | USER SPECIFIED   | USER SPECIFIED              |

## Programming Description

### Field Programmable CY25100

The CY25100 is programmed at the package level, and must be programmed prior to installation on a circuit board. Field programmable devices are denoted by an “F” in the ordering code, and are blank when shipped. The CY25100 is Flash technology based, which allows it to be reprogrammed up to 100 times. This allows fast and easy design changes and product updates, and eliminates issues with old and out of date inventory.

Samples and small prototype quantities can be programmed on the CY3672 programmer with the CY3690 (TSSOP package) or CY3691 (SOIC package) socket adapter.

### CyberClocks™ Online Software

CyberClocks™ Online Software is a web based software application that allows the user to custom-configure the CY25100. All of the parameters in [Table 1 on page 3](#) can be entered as variables into the software. CyberClocks Online outputs an industry-standard JEDEC file which is used for programming the CY25100. CyberClocks Online is available at [www.cyberclocksonline.com](http://www.cyberclocksonline.com) web site.

### CY3672 Programmer and CY3690/CY3691 Socket Adapters

The Cypress CY3672 programmer and the CY3690 or CY3691 socket adapter may be used to program field programmable versions of the CY25100. The CY3690 enables users to program the CY25100ZXCF and CY25100ZXIF (TSSOP). CY3691 provides the ability to program the CY25100SXCF and CY25100SXIF (SOIC). The CY3690 and CY3691 are separate orderable items, so the existing users of the CY3672 programmer need to order only the specific socket adapter to program the CY25100.

### Factory Programmable CY25100

Factory programming by Cypress is available for high volume orders. All requests must be submitted to the local Cypress Field Application Engineer (FAE) or sales representative. After the request is processed, you will receive a new part number, samples, and data sheet with the programmed values. This part number is used for additional sample requests and production orders.

## Product Functions

### Input Frequency (XIN, Pin 3 and XOUT, Pin 2)

The input to the CY25100 can be a crystal or a clock. The input frequency range for crystals is 8 to 30 MHz, and for clock signals is 8 to 166 MHz.

### C<sub>XIN</sub> and C<sub>XOUT</sub> (Pin 3 and Pin 2)

The CY25100 has internal load capacitors at Pin 3 (C<sub>XIN</sub>) and Pin 2 (C<sub>XOUT</sub>). C<sub>XIN</sub> always equals C<sub>XOUT</sub>, and they are programmable from 12 pF to 60 pF, in 0.5 pF increments. This feature eliminates the need for external crystal load capacitors.

The following formula is used to calculate the value of C<sub>XIN</sub> and C<sub>XOUT</sub> for matching the crystal load (C<sub>L</sub>):

$$C_{XIN} = C_{XOUT} = 2C_L - C_P$$

where C<sub>L</sub> is the crystal load capacitor as specified by the crystal manufacturer and C<sub>P</sub> is the parasitic PCB capacitance on each node of the crystal.

For example, if a crystal with C<sub>L</sub> of 16 pF is used, and C<sub>P</sub> is 2 pF, C<sub>XIN</sub> and C<sub>XOUT</sub> are calculated as:

$$C_{XIN} = C_{XOUT} = (2 \times 16) - 2 = 30 \text{ pF}$$

If using a driven reference, set C<sub>XIN</sub> and C<sub>XOUT</sub> to the minimum value 12 pF, connect the reference to XIN/CLKIN, and leave XOUT unconnected.

### Output Frequency (SSCLK, Pin 7)

The modulated frequency at the SSCLK output is produced by synthesizing the input reference clock. The modulation can be stopped by SSON# digital control input (SSON# = HIGH, no modulation). If modulation is stopped, the clock frequency is the nominal value of the synthesized frequency without modulation (spread percentage = 0). The range of synthesized clock is from 3 to 200 MHz.

### Spread Percentage (SSCLK, Pin 7)

The SSCLK spread can be programmed at any percentage value from ±0.25% to ±2.5% for center spread and from -0.5% to -5.0% for down spread.

### Reference Output (REFOUT, Pin 6)

The reference clock output has the same frequency and the same phase as the input clock. This output can be programmed to be enabled (clock on) or disabled (High Z, clock off). If this output is not required, it is recommended that the disabled (High Z, Clock Off) option be selected.

### Modulation Frequency

The modulation frequency is 31.5 kHz for all SSCLK frequencies from 3 to 200 MHz.

### Power Down or Output Enable (PD# or OE, Pin 4)

The part can be programmed to include either PD# or OE function. PD# function powers down the oscillator and PLL. The OE function disables the outputs.

## Absolute Maximum Rating

Supply Voltage ( $V_{DD}$ ) ..... -0.5 to +7.0 V  
 DC Input Voltage ..... -0.5 V to  $V_{DD} + 0.5$  V  
 Storage Temperature  
 (Non condensing) ..... -55 °C to +125 °C

Junction Temperature ..... -40 °C to +125 °C  
 Data Retention at  $T_j = 125$  °C ..... > 10 years  
 Package Power Dissipation ..... 350 mW  
 Static Discharge Voltage  
 (per MIL-STD-883, Method 3015) .....  $\geq 2000$  V

## Recommended Crystal Specifications

| Parameter  | Description                                              | Comments                                                                    | Min | Typ | Max | Unit     |
|------------|----------------------------------------------------------|-----------------------------------------------------------------------------|-----|-----|-----|----------|
| $f_{NOM}$  | Nominal Crystal Frequency                                | Parallel resonance, fundamental mode, AT cut                                | 8   | —   | 30  | MHz      |
| $C_{LNOM}$ | Nominal Load Capacitance                                 | Internal load caps                                                          | 6   | —   | 30  | pF       |
| $R_1$      | Equivalent Series Resistance (ESR)                       | Fundamental mode                                                            | —   | —   | 25  | $\Omega$ |
| $R_3/R_1$  | Ratio of Third Overtone Mode ESR to Fundamental Mode ESR | Ratio used because typical $R_1$ values are much less than the maximum spec | 3   | —   | —   | —        |
| DL         | Crystal Drive Level                                      | No external series resistor assumed                                         | —   | 0.5 | 2   | mW       |

## Operating Conditions

| Parameter    | Description                                                                                         | Min  | Typ  | Max  | Unit |
|--------------|-----------------------------------------------------------------------------------------------------|------|------|------|------|
| $V_{DD}$     | Supply Voltage                                                                                      | 3.13 | 3.30 | 3.45 | V    |
| $T_A$        | Ambient Commercial Temperature                                                                      | 0    | —    | 70   | °C   |
|              | Ambient Industrial Temperature                                                                      | -40  | —    | 85   | °C   |
| $C_{LOAD}$   | Maximum Load Capacitance at Pin 6 and Pin 7                                                         | —    | —    | 15   | pF   |
| $f_{REF}$    | External Reference Crystal (Fundamental tuned crystals only)                                        | 8    | —    | 30   | MHz  |
|              | External Reference Clock                                                                            | 8    | —    | 166  | MHz  |
| $f_{SSCLK}$  | SSCLK Output Frequency, $C_{LOAD} = 15$ pF                                                          | 3    | —    | 200  | MHz  |
| $f_{REFCLK}$ | REFCLK Output Frequency, $C_{LOAD} = 15$ pF                                                         | 8    | —    | 166  | MHz  |
| $f_{MOD}$    | Spread Spectrum Modulation Frequency                                                                | 30.0 | 31.5 | 33.0 | kHz  |
| $t_{PU}$     | Power Up Time for all $V_{DD}$ 's to reach minimum specified voltage (power ramp must be monotonic) | 0.05 | —    | 500  | ms   |

## DC Electrical Characteristics

| Parameter                              | Description                                 | Condition                                                                                                                                                   | Min                 | Typ | Max                 | Unit          |
|----------------------------------------|---------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|-----|---------------------|---------------|
| $I_{OH}$                               | Output High Current                         | $V_{OH} = V_{DD} - 0.5 \text{ V}$ , $V_{DD} = 3.3 \text{ V}$ (source)                                                                                       | 10                  | 12  |                     | mA            |
| $I_{OL}$                               | Output Low Current                          | $V_{OL} = 0.5 \text{ V}$ , $V_{DD} = 3.3 \text{ V}$ (sink)                                                                                                  | 10                  | 12  |                     | mA            |
| $V_{IH}$                               | Input High Voltage                          | CMOS levels, 70% of $V_{DD}$                                                                                                                                | $0.7 \times V_{DD}$ | –   | $V_{DD}$            | V             |
| $V_{IL}$                               | Input Low Voltage                           | CMOS levels, 30% of $V_{DD}$                                                                                                                                | –                   | –   | $0.3 \times V_{DD}$ | V             |
| $I_{IH}$                               | Input High Current, PD#/OE and SSON# Pins   | $V_{in} = V_{DD}$                                                                                                                                           | –10                 | –   | 10                  | $\mu\text{A}$ |
| $I_{IL}$                               | Input Low Current, PD#/OE and SSON# Pins    | $V_{in} = V_{SS}$                                                                                                                                           | –10                 | –   | 10                  | $\mu\text{A}$ |
| $I_{OZ}$                               | Output Leakage Current                      | Three-state output, PD#/OE = 0, output pulldown resistor disabled                                                                                           | –10                 |     | 10                  | $\mu\text{A}$ |
| $C_{XIN}$ or $C_{XOUT}$ <sup>[1]</sup> | Programmable Capacitance at Pin 2 and Pin 3 | Capacitance at minimum setting                                                                                                                              | –                   | 12  | –                   | pF            |
|                                        |                                             | Capacitance at maximum setting                                                                                                                              | –                   | 60  | –                   | pF            |
| $C_{IN}$ <sup>[1]</sup>                | Input Capacitance at Pin 4 and Pin 8        | Input pins excluding XIN and XOUT                                                                                                                           | –                   | 5   | 7                   | pF            |
| $I_{VDD}$                              | Supply Current                              | $V_{DD} = 3.45 \text{ V}$ , $F_{in} = 30 \text{ MHz}$ ,<br>REFCLK = 30 MHz,<br>SSCLK = 66 MHz,<br>$C_{LOAD} = 15 \text{ pF}$ ,<br>PD#/OE = SSON# = $V_{DD}$ | –                   | 25  | 35                  | mA            |
| $I_{DDS}$                              | Standby Current                             | $V_{DD} = 3.45 \text{ V}$ , Device powered down with PD# = 0 V (driven reference pulled down)                                                               | –                   | 15  | 30                  | $\mu\text{A}$ |

**Note**

1. Guaranteed by characterization, not 100% tested.

## AC Electrical Characteristics

The AC Electrical Characteristics for part CY25100 is as follows. [2]


| Parameter        | Description                            | Condition                                                                                                       | Min | Typ | Max | Unit |
|------------------|----------------------------------------|-----------------------------------------------------------------------------------------------------------------|-----|-----|-----|------|
| DC               | Output Duty Cycle                      | SSCLK, Measured at $V_{DD}/2$                                                                                   | 45  | 50  | 55  | %    |
|                  | Output Duty Cycle                      | REFCLK, Measured at $V_{DD}/2$ , Duty Cycle of CLKIN = 50% at input bias                                        | 40  | 50  | 60  | %    |
| SR1              | Rising Edge Slew Rate                  | SSCLK from 3 to 100 MHz; REFCLK from 3 to 100 MHz; 20%–80% of $V_{DD}$                                          | 0.7 | 1.1 | 3.6 | V/ns |
| SR2              | Falling Edge Slew Rate                 | SSCLK from 3 to 100 MHz; REFCLK from 3 to 100 MHz; 80%–20% of $V_{DD}$                                          | 0.7 | 1.1 | 3.6 | V/ns |
| SR3              | Rising Edge Slew Rate                  | SSCLK from 100 to 200 MHz; REFCLK from 100 to 166 MHz; 20%–80% of $V_{DD}$                                      | 1.0 | 1.6 | 4.0 | V/ns |
| SR4              | Falling Edge Slew Rate                 | SSCLK from 100 to 200 MHz; REFCLK from 100 to 166 MHz; 80%–20% of $V_{DD}$                                      | 1.2 | 1.6 | 4.0 | V/ns |
| $t_{CCJ1}^{[3]}$ | Cycle-to-Cycle Jitter, SSCLK (Pin 7)   | CLKIN = SSCLK = 166 MHz, 2% spread, REFCLK off                                                                  | –   | 90  | 120 | ps   |
|                  |                                        | CLKIN = SSCLK = 66 MHz, 2% spread, REFCLK off                                                                   | –   | 100 | 130 | ps   |
|                  |                                        | CLKIN = SSCLK = 33 MHz, 2% spread, REFCLK off                                                                   | –   | 130 | 170 | ps   |
| $t_{CCJ2}^{[3]}$ | Cycle-to-Cycle Jitter, SSCLK (Pin 7)   | CLKIN = SSCLK = 166 MHz, 2% spread, REFCLK on                                                                   | –   | 100 | 130 | ps   |
|                  |                                        | CLKIN = SSCLK = 66 MHz, 2% spread, REFCLK on                                                                    | –   | 105 | 140 | ps   |
|                  |                                        | CLKIN = SSCLK = 33 MHz, 2% spread, REFCLK on                                                                    | –   | 200 | 260 | ps   |
| $t_{CCJ3}^{[3]}$ | Cycle-to-Cycle Jitter, REFCLK (Pin 6)  | CLKIN = SSCLK = 166 MHz, 2% spread, REFCLK on                                                                   | –   | 80  | 100 | ps   |
|                  |                                        | CLKIN = SSCLK = 66 MHz, 2% spread, REFCLK on                                                                    | –   | 100 | 130 | ps   |
|                  |                                        | CLKIN = SSCLK = 33 MHz, 2% spread, REFCLK on                                                                    | –   | 135 | 180 | ps   |
| $t_{STP}$        | Power down Time (pin 4 = PD#)          | Time from falling edge on PD# to stopped outputs (Asynchronous)                                                 | –   | 150 | 350 | ns   |
| $t_{OE1}$        | Output Disable Time (pin 4 = OE)       | Time from falling edge on OE to stopped outputs (Asynchronous)                                                  | –   | 150 | 350 | ns   |
| $t_{OE2}$        | Output Enable Time (pin 4 = OE)        | Time from rising edge on OE to outputs at a valid frequency (Asynchronous)                                      | –   | 150 | 350 | ns   |
| $t_{PU1}$        | Power Up Time, Crystal is used         | Time from rising edge on PD# to outputs at valid frequency (Asynchronous)                                       | –   | 3.5 | 5   | ms   |
| $t_{PU2}$        | Power Up Time, Reference clock is used | Time from rising edge on PD# to outputs at valid frequency (Asynchronous), reference clock at correct frequency | –   | 2   | 3   | ms   |

### Notes

- Guaranteed by characterization, not 100% tested.
- Jitter is configuration dependent. Actual jitter is dependent on XIN jitter and edge rate, number of active outputs, output frequencies, spread percentage, temperature, and output load.

## Application Circuit

Figure 2. Application Circuit Diagram [4, 5, 6]




### Notes

4. Because the load capacitors ( $C_{XIN}$  and  $C_{XOUT}$ ) are provided by the CY25100, no external capacitors are needed on the  $X_{IN}$  and  $X_{OUT}$  pins to match the crystal load capacitor ( $C_L$ ). Only a single 0.1-µF bypass capacitor is required on the  $V_{DD}$  pin.
5. If an external clock is used, apply the clock to  $X_{IN}$  (pin 3) and leave  $X_{OUT}$  (pin 2) floating (unconnected).
6. If  $SSON\#$  (pin 8) is LOW ( $V_{SS}$ ), the frequency modulation is on at  $SSCLK$  (pin 7).




## Switching Waveforms

**Figure 3. Duty Cycle Timing ( $DC = t_{1A}/t_{1B}$ )**




**Figure 4. Output Rise/Fall Time (SSCLK and REFCLK)**




Output Rise time ( $T_r$ ) =  $(0.6 \times V_{DD})/SR1$  (or SR3)  
Output Fall time ( $T_f$ ) =  $(0.6 \times V_{DD})/SR2$  (or SR4)

Refer to AC Electrical Characteristics table for SR (Slew Rate) values.

**Figure 5. Power Down and Power Up Timing**









**Figure 6. Output Enable/Disable Timing**



## Informational Graphs

The Informational Graphs are as follows. [7]









### Note

7. The Informational Graphs are meant to convey the typical performance levels. No performance specifications is implied or guaranteed. Refer to [DC Electrical Characteristics](#) on page 6 and [AC Electrical Characteristics](#) on page 7 for device specifications.

## Informational Graphs (continued)

The Informational Graphs are as follows. [7]



## Ordering Information

| Ordering Code     | Package Description                                                | Product Flow                |
|-------------------|--------------------------------------------------------------------|-----------------------------|
| <b>Pb-free</b>    |                                                                    |                             |
| CY25100SXCF       | 8-pin SOIC                                                         | Commercial, 0 °C to 70 °C   |
| CY25100SXCFT      | 8-pin SOIC – Tape and Reel                                         | Commercial, 0 °C to 70 °C   |
| CY25100SXIF       | 8-pin SOIC                                                         | Industrial, –40 °C to 85 °C |
| CY25100SXIFT      | 8-pin SOIC – Tape and Reel                                         | Industrial, –40 °C to 85 °C |
| CY25100ZXCf       | 8-pin TSSOP                                                        | Commercial, 0 °C to 70 °C   |
| CY25100ZXCFT      | 8-pin TSSOP – Tape and Reel                                        | Commercial, 0 °C to 70 °C   |
| CY25100ZXIF       | 8-pin TSSOP                                                        | Industrial, –40 °C to 85 °C |
| CY25100ZXIFT      | 8-pin TSSOP – Tape and Reel                                        | Industrial, –40 °C to 85 °C |
| <b>Programmer</b> |                                                                    |                             |
| CY3672-USB        | Programmer, for devices with ordering codes ending in “F” and “FT” |                             |
| CY3690            | CY25100ZXCf/IF Adapter (TSSOP) for CY3672-USB Programmer           |                             |
| CY3691            | CY25100SXCF/IF Adapter (SOIC) for CY3672-USB Programmer            |                             |

Some product offerings are factory programmed customer specific devices with customized part numbers. The Possible Configurations table shows the available device types, but not complete part numbers. Contact your local Cypress FAE or Sales Representative for more information.

## Possible Configurations

| Ordering Code                   | Package Description         | Product Flow                |
|---------------------------------|-----------------------------|-----------------------------|
| CY25100Zlxxx <sup>[8, 9]</sup>  | 8-pin TSSOP                 | Industrial, –40 °C to 85 °C |
| CY25100ZlxxxT <sup>[8, 9]</sup> | 8-pin TSSOP – Tape and Reel | Industrial, –40 °C to 85 °C |
| <b>Pb-free</b>                  |                             |                             |
| CY25100SXCxx <sup>[8]</sup>     | 8-pin SOIC                  | Commercial, 0 °C to 70 °C   |
| CY25100SXCxxT <sup>[8]</sup>    | 8-pin SOIC – Tape and Reel  | Commercial, 0 °C to 70 °C   |
| CY25100SXlxxx <sup>[8]</sup>    | 8-pin SOIC                  | Industrial, –40 °C to 85 °C |
| CY25100SXlxxxT <sup>[8]</sup>   | 8-pin SOIC – Tape and Reel  | Industrial, –40 °C to 85 °C |
| CY25100ZXCxx <sup>[8]</sup>     | 8-pin TSSOP                 | Commercial, 0 °C to 70 °C   |
| CY25100ZXCxxT <sup>[8]</sup>    | 8-pin TSSOP – Tape and Reel | Commercial, 0 °C to 70 °C   |
| CY25100ZXlxx <sup>[8]</sup>     | 8-pin TSSOP                 | Industrial, –40 °C to 85 °C |
| CY25100ZXlxxT <sup>[8]</sup>    | 8-pin TSSOP – Tape and Reel | Industrial, –40 °C to 85 °C |

### Note

- Ordering codes with “xxx” or “xx” are factory-programmed configurations. “xxx” or “xx” denotes the specific device configuration. “w” denotes the revision. Factory programming is available for high-volume orders. For more details, contact your local Cypress field application engineer or Cypress Sales Representative.
- Not recommended for new designs. New designs should use Pb-free devices.


## Ordering Code Definitions

|    |       |   |   |   |   |           |   |                                                                 |
|----|-------|---|---|---|---|-----------|---|-----------------------------------------------------------------|
| CY | 25100 | X | X | X | F | (xx, xxx) | T |                                                                 |
|    |       |   |   |   |   |           |   | T = Tape and Reel; blank = Tube                                 |
|    |       |   |   |   |   |           |   | Custom configuration code (factory programmed device only)      |
|    |       |   |   |   |   |           |   | Programming: F = field programmable; blank = factory programmed |
|    |       |   |   |   |   |           |   | Temperature Range: X = C or I<br>C = Commercial; I = Industrial |
|    |       |   |   |   |   |           |   | X = Pb-free package                                             |
|    |       |   |   |   |   |           |   | Package Type: X = S or Z<br>S = 8-pin SOIC; Z = 8-pin TSSOP     |
|    |       |   |   |   |   |           |   | Base part number                                                |
|    |       |   |   |   |   |           |   | Company ID: CY = Cypress                                        |

## Package Diagrams

**Figure 7. 8-pin SOIC (150 Mils) S08.15/SZ08.15/SW815 Package Outline, 51-85066**


8 Lead (150 Mil) SOIC – S08



51-85066 \*F

**Package Diagrams** (continued)


**Figure 7. 8-pin TSSOP (4.40 mm Body) Z08.173/ZZ08.173 Package Outline, 51-85093**



DIMENSIONS IN MM[INCHES] MIN.  
MAX.

REFERENCE JEDEC MO-153

| PART #   |                |
|----------|----------------|
| Z08.173  | STANDARD PKG.  |
| ZZ08.173 | LEAD FREE PKG. |



51-85093 \*E

## Acronyms

| Acronym | Description                                |
|---------|--------------------------------------------|
| DC      | Direct Current                             |
| EMI     | Electromagnetic Interference               |
| ESR     | Equivalent Series Resistance               |
| FAE     | Field Application Engineer                 |
| JEDEC   | Joint Electron Devices Engineering Council |
| OE      | Output Enable                              |
| PCB     | Printed Circuit Board                      |
| PD      | Power Down                                 |
| PLL     | Phase Locked Loop                          |
| SOIC    | Small Outline Integrated Circuit           |
| SSC     | Spread Spectrum Clock                      |
| SSCG    | Spread Spectrum Clock Generator            |
| TSSOP   | Thin Shrunk Small Outline Package          |

## Document Conventions

### Units of Measure

| Symbol | Unit of Measure |
|--------|-----------------|
| °C     | degree Celsius  |
| kHz    | kilohertz       |
| MHz    | megahertz       |
| μA     | microampere     |
| μF     | microfarad      |
| mA     | milliampere     |
| mm     | millimeter      |
| ms     | millisecond     |
| mW     | milliwatt       |
| ns     | nanosecond      |
| Ω      | ohm             |
| %      | percent         |
| pF     | picofarad       |
| ps     | picosecond      |
| V      | volt            |

## Document History Page

| Document Title: CY25100, Field and Factory Programmable Spread Spectrum Clock Generator for EMI Reduction<br>Document Number: 38-07499 |         |                 |                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
|----------------------------------------------------------------------------------------------------------------------------------------|---------|-----------------|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Rev.                                                                                                                                   | ECN No. | Orig. of Change | Submission Date | Description of Change                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| **                                                                                                                                     | 126578  | CKN             | 06/27/03        | New data sheet.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| *A                                                                                                                                     | 128753  | IJATMP          | 08/29/03        | Changes to reflect field programmability                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| *B                                                                                                                                     | 130342  | RGL             | 12/02/03        | Changes to Application Circuit diagram and correction to the package description listed under the Ordering Information table for CY3690 and CY3691.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| *C                                                                                                                                     | 204121  | RGL             | See ECN         | Add Industrial Temperature Range<br>Corrected the Ordering Information to match the DevMaster                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| *D                                                                                                                                     | 215392  | RGL             | See ECN         | Added Lead Free devices                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| *E                                                                                                                                     | 2513909 | AESA            | 06/10/08        | Updated template. Added Note "Not recommended for new designs."<br>Added part number CY25100KSXCF, CY25100KSXIF, CY25100KSXI-xxx, CY25100KZXC-xxx, CY25100KZXI-xxx, CY25100KSXI-xxxT, CY25100KZXC-xxxT, CY25100KZXI-xxxT, and CY25100KZXIF in ordering information table.<br>Added Pb-Free header in the ordering information table.<br>Removed Pb-Free from Package description in the ordering information table.<br>Changed CY3672-PRG with CY3672-USB in the ordering information table.<br>Removed CY25100SCF, CY25100SIF, CY25100ZCF, CY25100ZIF, and CY3672 in the ordering information table.<br>Changed Lead free to Pb-Free.                                                                                                                                       |
| *F                                                                                                                                     | 2601881 | KVM / PYRS      | 11/06/08        | Rising edge slew rate (SR3) minimum limit changed from 1.2 V/ns to 1.0 V/ns.<br>Removed part numbers added in rev *E.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| *G                                                                                                                                     | 2742910 | KVM             | 07/23/09        | General text cleanup<br>Moved General Description to p. 1 to replace the Benefits section<br>Removed "FTG" from references to CY3672<br>Added "Type" column to Pin Description table<br>Revised software description section<br>Revised Modulation Frequency section to remove mention of optional modulation frequencies<br>Added minimum values to $I_{IH}$ and $I_{IL}$<br>Added to $I_{OZ}$ conditions: applies only for output pulldown disabled<br>Standardized timing parameter names to upper case<br>Corrected some part numbers to remove dashes and revision code<br>Added part numbers to the Ordering Information table: CY25100ZI-xxx, CY25100ZI-xxxT, CY25100SXCF, CY25100SXIF, CY25100ZXCFT and CY25100ZXIFT<br>Revised Ordering Information table footnotes |
| *H                                                                                                                                     | 2897317 | KVM             | 03/22/10        | Removed obsolete parts from Ordering Information table and moved 'xxx' parts to Possible Configurations table<br>Updated package diagrams                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| *I                                                                                                                                     | 3366141 | PURU            | 09/12/2011      | Updated <a href="#">Logic Block Diagram</a> .<br>Added <a href="#">Ordering Code Definitions</a> .<br>Updated <a href="#">Package Diagrams</a> .<br>Added <a href="#">Acronyms</a> and <a href="#">Units of Measure</a> .<br>Updated in new template.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |



**Document History Page** (continued)

| Document Title: CY25100, Field and Factory Programmable Spread Spectrum Clock Generator for EMI Reduction<br>Document Number: 38-07499 |         |                 |                 |                                                                                                                                                                                                                   |
|----------------------------------------------------------------------------------------------------------------------------------------|---------|-----------------|-----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Rev.                                                                                                                                   | ECN No. | Orig. of Change | Submission Date | Description of Change                                                                                                                                                                                             |
| *J                                                                                                                                     | 4108421 | CINM            | 08/30/2013      | Updated <a href="#">Package Diagrams</a> :<br>spec 51-85066 – Changed revision from *E to *F.<br>spec 51-85093 – Changed revision from *C to *D.<br><br>Updated in new template.<br><br>Completing Sunset Review. |
| *K                                                                                                                                     | 4581659 | TAVA            | 11/28/2014      | Added related documentation hyperlink in page 1.<br>Updated package diagram.                                                                                                                                      |

## Sales, Solutions, and Legal Information

### Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at [Cypress Locations](#).

#### Products

|                                              |                                           |
|----------------------------------------------|-------------------------------------------|
| <a href="#">Automotive</a>                   | <a href="#">cypress.com/go/automotive</a> |
| <a href="#">Clocks &amp; Buffers</a>         | <a href="#">cypress.com/go/clocks</a>     |
| <a href="#">Interface</a>                    | <a href="#">cypress.com/go/interface</a>  |
| <a href="#">Lighting &amp; Power Control</a> | <a href="#">cypress.com/go/powerpsoc</a>  |
|                                              | <a href="#">cypress.com/go/plc</a>        |
| <a href="#">Memory</a>                       | <a href="#">cypress.com/go/memory</a>     |
| <a href="#">PSoC</a>                         | <a href="#">cypress.com/go/psoc</a>       |
| <a href="#">Touch Sensing</a>                | <a href="#">cypress.com/go/touch</a>      |
| <a href="#">USB Controllers</a>              | <a href="#">cypress.com/go/USB</a>        |
| <a href="#">Wireless/RF</a>                  | <a href="#">cypress.com/go/wireless</a>   |

#### PSoC® Solutions

[psoc.cypress.com/solutions](#)

[PSoC 1](#) | [PSoC 3](#) | [PSoC 4](#) | [PSoC 5LP](#)

#### Cypress Developer Community

[Community](#) | [Forums](#) | [Blogs](#) | [Video](#) | [Training](#)

#### Technical Support

[cypress.com/go/support](#)

© Cypress Semiconductor Corporation, 2003-2014. The information contained herein is subject to change without notice. Cypress Semiconductor Corporation assumes no responsibility for the use of any circuitry other than circuitry embodied in a Cypress product. Nor does it convey or imply any license under patent or other rights. Cypress products are not warranted nor intended to be used for medical, life support, life saving, critical control or safety applications, unless pursuant to an express written agreement with Cypress. Furthermore, Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress products in life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Any Source Code (software and/or firmware) is owned by Cypress Semiconductor Corporation (Cypress) and is protected by and subject to worldwide patent protection (United States and foreign), United States copyright laws and international treaty provisions. Cypress hereby grants to licensee a personal, non-exclusive, non-transferable license to copy, use, modify, create derivative works of, and compile the Cypress Source Code and derivative works for the sole purpose of creating custom software and or firmware in support of licensee product to be used only in conjunction with a Cypress integrated circuit as specified in the applicable agreement. Any reproduction, modification, translation, compilation, or representation of this Source Code except as specified above is prohibited without the express written permission of Cypress.

Disclaimer: CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS MATERIAL, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Cypress reserves the right to make changes without further notice to the materials described herein. Cypress does not assume any liability arising out of the application or use of any product or circuit described herein. Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress' product in a life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Use may be limited by and subject to the applicable Cypress software license agreement.