


ENG. NO.
SD-70021-0*04




EDP NO.
—

ALL DIMENSIONS IN METRIC DO NOT SCALE DRAWING

適用電線表示
CRIMP SIZE CODE LETTER





断面 A-A
SECTION A-A
(SCALE:20-1)



注記:
NOTES:

- 1. 適合ハウジング: 70066-****, 70107-****
APPLICABLE HOUSING: 70066-****, 70107-****
- 2. 仕上げ ニッケル下地、錫メッキ
FINISH TIN OVER NICKEL PLATING



1.91	2.1	1.47	1.22	A	ø 1.6 MAX.	AWG#24-#30	バラ状 LOOSE	70021-0204
1.91	2.1	1.65	1.84	C		AWG#22-#24	連鎖状 CHAIN	70021-0004
D	C	B	A	適用電線表示 CRIMP SIZE CODE LETTER	被覆外径 INS. RANGE	適用電線範囲 WIRE RANGE	端子形状 FORM	MATERIAL No.
				材料 MATERIAL	磷青銅 PHOSPHOR BRONZE	molex MOLEX-JAPAN CO.,LTD. 日本モレックス株式会社		
				仕上げ FINISH	注記参照 SEE NOTES			
				適用電線範囲 WIRE RANGE	表参照 SEE CHART	EDP. NO. —		
				被覆外径 INS. RANGE	表参照 SEE CHART			
				DRAWN BY A. Mitake	CHK'D BY M. Kato	REV B		
				DATE 1/1/80	SCALE 10-1			
角度 ANGLE	±3°	B	変更 REVISED	U2004-4519	Y.M.S.	04/05/31	TITLE 名称 SL MALE CRIMP TERMINAL -LEAD FREE-	
30°以上 OVER	+0.3	A	変更 REVISED	(T20159)	H.H.I.	191/5/20		
10°以上 30°未満 OVER UNDER	+0.25	Q	新規格作成 RELEASED	(T00110)	M.M.S.	190/4/6		
10°未満 UNDER	+0.2	記号 LTR	変更内容 REVISION RECORD	DR. CHK.	日付 DATE			
一般公差 GENERAL TOLERANCES							REVISE ONLY ON CAD SYSTEM	



NOTES:

1. MATERIAL: PHOSPHOR BRONZE, 0.20/.008 THICK
2. FINISH: 3.81 MICROMETERS/150 MICROINCHES TIN OVER NICKEL UNDERPLATE OVERALL
3. PRODUCT SPECIFICATION: PS-70021
4. PACKAGING: PARTS SUPPLIED IN REEL FORM
5. TERMINAL FOR USE WITH: 70066-**** & 70107-**** HOUSINGS
6. TERMINAL TO BE USED WITH: 22-24 AWG STRANDED WIRE WITH .064 DIAMETER MAXIMUM INSULATION
7. REFER TO MOLEX OPERATIONAL AND SERVICE MANUAL FOR DETAILS
8. CRIMP SIZE INDICATOR: C=22-24 AWG

ADD VIEWS W/CARRIER EC NO: UCP2010-2842 DRAWN BY: MSIBARRA 2010/05/07 CHKD BY: JORGAN 2010/05/07 APPR: MILLER 2010/05/11	REV DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY MSIBARRA	DATE 2010/05/07	TITLE TERMINAL, MALE CRIMP			
			4 PLACES	± ---	± ---	CHECKED BY MJM	DATE 1986/10/30	MOLEX MOLEX INCORPORATED			
			3 PLACES	± ---	± .005	APPROVED BY SMILLER	DATE 2010/05/11				
			2 PLACES	± .13	± .01	MATERIAL NO. 16-02-0107		DOCUMENT NO. SD-70021-0021		SHEET NO. 1 OF 1	
			1 PLACE	± 0.25	± ---	SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
			ANGULAR ±1/2°								
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								



NOTES:

1. MATERIAL: PHOSPHOR BRONZE, 0.20/0.008 THICK
2. FINISH: 3.81 MICROMETERS/150 MICROINCHES TIN OVER
NICKEL UNDERPLATE OVERALL
3. PRODUCT SPECIFICATION: PS-70021
4. PACKAGING: PARTS SUPPLIED IN REEL FORM
5. TERMINAL FOR USE WITH: 70066-**** & 70107-**** HOUSINGS
6. TERMINAL TO BE USED WITH: 22-24 AWG STRANDED WIRE WITH
.064 DIAMETER MAXIMUM INSULATION
7. REFER TO MOLEX OPERATIONAL AND SERVICE MANUAL FOR DETAILS
8. CRIMP SIZE INDICATOR: C=22-24 AWG

ADD VIEW W/CARRIER EC NO: UCP2010-2842 DRAWN: MSIBARRA 2010/05/07 CHKD: DMORGAN 2010/04/29 APPR: SMILLER 2010/05/11			DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 15:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION			
					mm		INCH		DRAWN BY MSIBARRA	DATE 2010/04/29	TITLE TERMINAL, MALE CRIMP				
					4 PLACES ± ---		± ---		CHECKED BY DMORGAN		DATE 2010/04/29		MOLEX INCORPORATED		
					3 PLACES ± ---		± .010		APPROVED BY SMILLER		DATE 2010/05/11				
		2 PLACES ± 0.25		± .015				MATERIAL NO. 70021-1021		DOCUMENT NO. SD-70021-1021		SHEET NO. 1 OF 1			
		1 PLACE ± 0.35		± ---				SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
				ANGULAR ± 1/2°											
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									