







Copyright FCI.



PRODUCT NUMBER
51720C- ABBCCCDDEF--
NOTE ①



△ DETAIL A
SCALE 2:1
FOR SIGNAL SOLDER TO BOARD ONLY



△ DETAIL B
SCALE 2:1
FOR SIGNAL PRESS FIT ONLY



spec ref *				dr w wadmin 2006/11/08		projection 	MM 	size A4	scale 1:1
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng Jackie Huang 2013/06/27				ecn no ELX-DG-13802-1	
				chr - -					
				appr Pei-Ming Zheng 2013/06/30		product family PwrBlade		rel level Released	
surface	linear	0.X	±0.50		title RIGHT ANGLE HEADER w/GUIDE POWER / SIGNAL / POWER			dwg no 51720	rev R
		0.XX	±0.25						
		0.XXX	±0.10						
	angular	0°	±2°						

PrintE File - REV C - 2009-06-09



Copyright FCI.

PRODUCT NUMBER		DIM	LENGTH FORMULAS (SEE NOTE 10)
51720- ABBCCDDEF-- NOTE ①		DIM "A"	$6.35 \times BB + 2.54 \times (CCC/4) + 6.35 \times DD + 16.51$ (NOTE 10)
		DIM "B"	$6.35 \times BB + 2.54 \times (CCC/4) + 6.35 \times DD + 8.89$
		DIM "C"	$6.35 \times BB + 2.54 \times (CCC/4) + 6.35 \times DD + 7.62$
		DIM "D"	$6.35 \times BB + 9.53$
		DIM "E"	$6.35 \times BB + 2.54 \times (CCC/4) + 11.43$
		DIM "F"	$6.35 \times BB + 2.54 \times (CCC/4) + 6.35 \times DD + 17.27$
		DIM "G"	$6.35 \times BB + 5.72$
		DIM "H"	$6.35 \times BB + 2.54 \times (CCC/4) + 6.35$

CONNECTOR NOTES

- ①. PRODUCT NUMBER CODE:
51720 - A BB CCC DD E F LF
- NO THIS SUFFIX: 100u"/2.54um SnPb ON PCB INTERFACE
ADD THIS SUFFIX: 78u"/2.00um Sn OR 5u" Au ON PCB INTERFACE
RETENTION TO PCB (NOTE 8)
TAIL OPTIONS (NOTE 7)
NUMBER OF RIGHT END POWER CONTACTS (NOTE 6)
NUMBER OF SIGNAL CONTACTS (NOTE 5)
NUMBER OF LEFT END POWER CONTACTS (NOTE 4)
PLATING (NOTE 3)
BASE NUMBER

- ②. HOUSING MATERIAL: GLASS FILLED V-O HIGH TEMP THERMO PLASTIC.
SIGNAL CONTACT MATERIAL: COPPER ALLOY
POWER CONTACT MATERIAL: COPPER ALLOY
- ③. PLATING OPTION:
1: SEE ITEM PRINT 10064183 FOR PLATING SPEC OF 51720-ABBCCDDEF; 51720-ABBCCDDEFLF
- ④. LEFT END POWER CONTACTS, 01 TO 20 AVAILABLE.
MAXIMUM OF 20 POWER CONTACTS PER CONNECTOR.
- ⑤. SIGNAL CONTACTS, 004 TO 148 AVAILABLE.
- ⑥. RIGHT END POWER CONTACTS, 01 TO 20 AVAILABLE.
MAXIMUM OF 20 POWER CONTACTS PER CONNECTOR.
- ⑦. TAIL OPTIONS:
A = 3.43 SOLDER TO BOARD
△C = 3.43 PRESS FIT


- ⑧. RETENTION TO PCB OPTIONS:
A = BOARD LOCK (2.49 +0.05, -0.03 THRU HOLE IN PCB).
MOUNTING FOOT THICKNESS: 5.59
B = 3.81 THRU HOLE (REQUIRES 4.01±08 THRU HOLE IN PCB).
MOUNTING FOOT THICKNESS: 4.06
9. MANUFACTURE'S NAME, P/N, AND DATE CODE
TO APPEAR ON THIS SURFACE.
10. THE MAXIMUM OVERALL LENGTH (DIM A) OF A PART
IS 203.2
- ①①. PRODUCT SPECIFICATION GS-12-149
APPLICATION SPECIFICATION BUS-20-067
12. REFERENCE 51697 FOR SPECIALS WORKSHEET.

PCB NOTES:


13. ALL DIMENSIONS ARE BASIC UNLESS OTHERWISE SPECIFIED.
14. ALL THROUGH HOLES ARE LOCATED WITH A
TRUE POSITION OF 0.10
15. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- ①⑥. Ø1.151 ±0.02 DRILLED HOLES PLATED WITH
0.007 MIN SnPb or Sn OVER 0.03 TO 0.08
PLATING TO ACHIEVE A 1.02±0.07 HOLE.
17. A △ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE
WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.
- ①⑧. CONNECTOR KEEP OUT ZONE.

dr	wcadmin	2006/11/08	projection	MM	size	A4	scale	1:1			
eng	Jackie Huang	2013/06/27			ecn noELX-DG-13802-1						
chr	-	-									
appr	Pei-Ming Zheng	2013/06/30	product family		PwrBlade		rel levelReleased				
		title			RIGHT ANGLE HEADER w/GUIDE			dwg no51720		revR	
POWER / SIGNAL / POWER											
www.fci.com		cat. no.		51720		Product - Customer Drw				sheet 2 of 3	


PRODUCT NUMBER
51720C- ABBCCCDDEF _ _
NOTE ①





SECTION C-C
SCALE 1:1
FOR SIGNAL SOLDER TO BOARD ONLY



SECTION B-B
SCALE 1:1



SECTION A-A



dr	wcadmin	2006/11/08	projection	MM	size	A4	scale	1:1
eng	Jackie Huang	2013/06/27			ecn no	ELX-DG-13802-1		
chr	-	-			rel level	Released		
appr	Pei-Ming Zheng	2013/06/30	product family	PwrBlade	rev	R		
www.fci.com		cat. no.	51720	Product - Customer Drw	sheet 3 of 3			
title		RIGHT ANGLE HEADER w/GUIDE			dwg no	51720		
		POWER / SIGNAL / POWER						