



## 2007212-2 Product Details


[Share](#)

[Print](#)


[Email](#)


2007212-2

TE Internal Number: 2007212-2



Active


[View 3D PDF](#)

### .025 [0.64] Centerline Matched Impedance Connector (MICTOR)


[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Connector
- Connector Style = Receptacle
- Mated Stack Height (Vertical) = 6.60 mm, 9.00 mm, 10.92 mm, 12.57 mm, 18.75 mm, 22.86 mm
- 76 Positions
- Vertical Mount Angle

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)


[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

#### Documentation & Additional Information

##### Product Drawings:

- None Available

##### Catalog Pages/Data Sheets:

- None Available

##### Product Specifications:

- None Available

##### Application Specifications:

- None Available

##### Instruction Sheets:

- None Available

##### CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing](#) (DXF, Version 2)
- [3D Model](#) (IGES, Version 2)
- [3D Model](#) (STEP, Version 2)

##### Additional Information:

- [Product Line Information](#)
- [High Speed MICTOR Cable Assemblies](#)

##### Related Products:

- [Tooling](#)

[List all Documents](#)

#### Product Features (Please use the Product Drawing for all design activity)

##### Product Type Features:

- Product Type = Connector
- Mount Angle = Vertical

##### Dimensions:

- [Mated Stack Height \(Vertical\) \(mm \[in\]\)](#) = 6.60 [0.260], 9.00 [0.354], 10.92 [0.430], 12.57 [0.495], 18.75 [0.738], 22.86 [0.900]

##### Body Features:

- [Number of Positions](#) = 76
- Vacuum Cover = Without
- Centerline (mm [in]) = 0.025 [0.635]

##### Contact Features:

- Contact Plating, Mating Area, Material = Gold or Palladium Nickel or Performance Based

##### Housing Features:

- [Connector Style](#) = Receptacle

##### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

##### Packaging Features:

- Packaging Method = Tube

##### Other:

- Brand = AMP

#### Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

#### Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

#### Keep Me Informed

Receive TE News, Events &amp; Technology Updates

Enter your email address

