

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



more than you expect



Midcom

ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-4 @20°C	0.135 ohms ±20%
D.C. RESISTANCE	7-9 @20°C	0.400 ohms ±10%
INDUCTANCE	2-4 100kHz, 100mVAC, Ls	270uH ±10%
INDUCTANCE	7-9 100kHz, 100mVAC, Ls	142uH ±10%
DIELECTRIC	4-7 1250VAC, 1 second	1000VAC, 1 minute
URNS RATIO	(4-2):(7-9)	1.375:1, ±1%



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64	Decimals: ±.005 [1.3] Footprint: ±.001 [0.3]	DRAWING TITLE	PART NO.
		Method: Tray PKG-0318 www.we-online.com/midcom				TRANSFORMER	750311819
6A	11/10	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		eiSos p/n: 750311819	SPECIFICATION SHEET 1 OF 1

