

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

POS.
"n".

L -0.5

PART NO.

VERWENDET FÜR
E 93-52506

LOC	DIST	REVISIONS					
P	LTR	DESCRIPTION			DATE	DWN	APVD
		PLATING CHANGE TO PdNi + Au FLASH AT AREA F			14MAY2014	KJK	JK

D

C



B

A

-	-	-
-	-	-
3	7.12	966 073-3
4	9.66	-4
5	12.20	-5
6	14.74	-6
7	17.28	-7
8	19.82	-8
9	22.36	-9
10	24.90	1-0
11	27.44	1-1
12	29.98	1-2
13	32.52	1-3
14	35.06	1-4
15	37.60	1-5
16	40.14	1-6
17	42.68	1-7
18	45.22	1-8
19	47.76	1-9
20	50.30	2-0
21	52.84	2-1
22	55.38	2-2
23	57.92	2-3
24	60.46	2-4
25	63.00	2-5
26	65.54	2-6
27	68.08	2-7
28	70.62	2-8
29	73.16	2-9
30	75.70	3-0
31	78.24	3-1
32	80.78	3-2
33	83.32	3-3
34	85.86	3-4
35	88.40	3-5
36	90.94	3-966-073-6

2
OBSOLETE

OBSOLETE



- 1 MATING SIDE CONTACT AREA F:
MIN. 0.7µm PdNi + 0.1µm Au FLASH OVER 1.27µm Ni
SOLDER SIDE: MIN. 3.0µm TIN OVER 1.27µm Ni
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

CONTACT PIN	CuZn	1
HOUSING	PCT	BLACK
DESCRIPTION	MATERIAL	FINISH COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:
±0.2mm

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

FINISH
SEE TABLE

DWN
A.HO
CHK
M.SCHAARSCHMIDT
APVD
-
PRODUCT SPEC
108-18012
APPLICATION SPEC
-
WEIGHT
-

19.01.93
-
NAME
AMPMODU II PIN HEADER,
SINGLE ROW,WITH POLARIZATION
SIZE
A3
CAGE CODE
00779
DRAWING NO
C-966073
RESTRICTED TO
-
SCALE
5:1
SHEET
1 OF 1
REV
B