# PC-16 16 mm Carbon Potentiometer





Bushless version

## FEATURES

- Carbon resistive element
- IP54 protection according to IEC 60529
- Polyester substrate
- Modular gang type (up to 4)
- Self extinguishable material UL 94-V0
- Upon request:
  - Metalic support
  - Stereo matching
  - Switch
  - Nut & washer
  - Bushless option available

## MECHANICAL SPECIFICATIONS

| | |
|---|---|
| – Mechanical rotation angle: | 300° ± 5° |
| – Electrical rotation angle: | 280° ± 20° |
| – Torque: | 0.5 to 1.5 Ncm. (0.7 to 2.1 in-oz) |
| – Stop torque: | > 40 Ncm. ( >56 in-oz) |
| – Max. torque nut (binding out): | < 80 Ncm. (112 in-oz) |
| – Thrust and pull in the shaft: | > 25 N |

## ELECTRICAL SPECIFICATIONS

– Range of values (*)
100Ω ≤ Rn ≤ 5 M (Decad. 1.0 - 2.0 - 2.2 - 2.5 - 4.7 - 5.0)

– Tolerance (*): 100Ω ≤ Rn ≤ 1M Ω ------ ± 20%
1MΩ < Rn ≤ 5M Ω ------ ± 30%

– Max. Voltage: 250 VDC (lin) 125 VDC (no lin)

– Nominal Power 50°C (122°F) (see power rating curve)
0.2 W (lin) 0.1 W (no lin)

– Taper (*) (Log. & Alog. only Rn > 1K) Lin ; Log; Alog.

– Residual resistance(*): ≤ 0.5% Rn (5 Ω min.)

– Equivalent Noise Resistance: ≤ 3% Rn (3 Ω min.)

– Operating temperature**: –25°C + 70°C (–13°F + 158°F)

* Others upon request

** Up to 85°C depending on application

## HOW TO ORDER

STANDARD

| PC-16 | D | H | 10 | I | M06 | 203 | A | 2020 |
|---|---|---|---|---|---|---|---|---|
| Serie: PC-16 | Model: S =Single, D =Tandem, T =Triple, C =Quad. | Mounting style: H= Horizontal, V = Vertical (See note 1) | Bushing diameter: 07 = M7, 10 = M10, SC = Bushless (See note 2) | Terminals: I = PCB, C = Solder Lugs | Shafts: M04, M06, M07, M11, M17, P01, P22, --- (See note 3) | Value: 101 = 100 Ω, 203 = 20 K, 504 = 500 K, 505 = 5M (See note 4) | Taper: A = Linear, B = Log., C = Alog. (See note 10) Others tapers on request | Tolerance: 2020 = +/- 20%, 3030 = +/- 30% (See note 5) |

OPTIONAL EXTRAS

| 0 | | | | |
|---|---|---|---|---|
| Shafts spec. leng.: XX.X (See notes 6,9) | Mounting brackets: M1, M2 (See note 7) | Stereo matching: 3D = 3dB, 4D = 4dB, 6D = 6dB (See note 8) | Switch: I = PCB, C = Solder lugs (See note 9) | Nuts & Washers: -TA = loose nut & washer, MTA=assembled nut & washer, -T- = loose nut, MT- = assembled nut (See note 9) |

NOTES:

(1) Mounting style: Type "V" is only available in model "S" potentiometer and with printed circuit terminals.
(2) Bushings: Type "10" has two paralell flat surfaces for avoiding rotation. Bushless option only available for single model.
(3) M07 shaft is only available with M10 bushing. --- = no shaft
(4) Value: • Code: 10 1 100 Ω
10 → 2 first digits of the value.
1 → Number of zeros
• In models "D", "T", "C", with different values, they will be asked by drawings.
(5) Tolerance (non standard), upon request. Example: +7% -5% Code: 07 05
07 → negative tolerance
05 → positive tolerance
(6) Shaft special length:
• Only for special length and plain shafts (not knurled). Example: Shaft Ø6.35 L= 24.5 M07 ..... 24.5
• NOTE: Maximun length recommended: L = 45
M07 → special length shafts
24.5 → special length shafts
(7) Mounting brackets: Only applicable for model "S", mounting "H" and without switch.
(8) Stereo matching: not available for single models. Maximun will be: •3dB for model "D" •4dB for model "T" •6dB for model "C"
(9) Not available for Bushless version.
(10) Switch option not available with antilog taper.

NOTE: The information contained here should be used for reference purposes only.

## HOW TO ORDER CUSTOM DRAWING

PC-16 S V + DRAWING NUMBER (Max. 16 digits)

This way of ordering should be used for options which are not included in the "How to order" standard and optional extras.

## STANDARD OPTIONS

Shaft length ..... 0 Standard Length
Mounting brackets ..... Without mounting brackets
Stereo matching ..... Only on request (see note 8)
Switch ..... No switch
Nut & washer ..... Without nut and washer

## MODELS




PC-16 S/D/T/C..H...




PC-16 SV .....

## METALLIC SUPPORT




PC-16 SH.....M1




PC-16 SH....M2

## BUSHINGS




07




10

## EXAMPLES OF BUSHLESS VERSION



## TERMINALS







C







I

## TAPERS

Standard

A = Linear
B = Log.
C = Alog.




## POWER RATING CURVE




## NUTS & WASHERS

Bushing 10




Bushing 07




NOTE = Please note relative terminal positions when ordering non linear tapers.

## TESTS

| | | TYPICAL VARIATIONS |
|---|---|---|
| ELECTRICAL LIFE | 1.000 h. @ 50°C; 0.2 W | ±5 % |
| MECHANICAL LIFE : POT.*<br>SWITCH | 25.000 (10-15 CPM)<br>10.000 (1 A, 50 VAC) | ±3 % (Rn < 1 MΩ) |
| TEMPERATURE COEFFICIENT | –25°C; +70°C | ±300 ppm/°C (Rn < 100 KΩ) |
| THERMAL CYCLING | 16 h. @ 85°C; 2h. @ –25°C | ±2.5 % |
| DAMP HEAT | 500 h. @ 40°C @ 95% HR | ±5 % |
| VIBRATION (for each plane X,Y,Z) | 2 h. @ 10 Hz. ... 55 Hz. | ±2 % |

(*) only applicable to values ≥1K. For lower values please consult.

## SWITCH










PC-16S . . . H . . . . . . . I / C




PC-16SV . . . I

## SWITCH SPECIFICATIONS

| | |
|---|---|
| NOMINAL CURRENT | 1A, 250 VAC |
| CONTACT RESISTANCE (initial) | 10 m Ω |
| OPERATING TORQUE | 1 to 3 Ncm (1.4 to 4.2 in oz) |
| OPERATING ANGLE | 30° ± 5° |
| TEST VOLTAGE | 500 V |

## PACKAGING

Boxes of 100 pieces (single body model): Inner dimensions 250 x 160 x 95 mm

## METALIC SHAFTS

STANDARD




| A | L | CODE |
|---|---|---|
| 4 | 45 | M04 |
| 6 | 45 | M06 |
| 6.35 | 45 | M07 |




| A | B | C | L | CODE |
|---|---|---|---|---|
| 2 | 5 | 7 | 15 | M11 |
| 2 | 10 | 11 | 20 | M12 |
| 4 | 12 | 14 | 25 | M13 |
| 4 | 12 | 14 | 30 | M14 |
| 4 | 12 | 14 | 35 | M15 |
| 4 | 12 | 14 | 40 | M16 |
| 4 | 12 | 14 | 45 | M17 |

SPECIAL




| A |
|---|
| 4 |
| 6 |
| 6.35 |

## PLASTIC SHAFTS Ø3.1




P09

## PLASTIC SHAFTS Ø4




P01




P02




P03

## PLASTIC SHAFTS Ø4




P04







P07







P08




P10




P21

## PLASTIC SHAFTS Ø6




P05




P06







P11




P12




P13







P14




P15




P16




P17




P18







P19




P20

NOTE: Shaft position shown full CCW. Any other position for plastic shafts has to be shiftted n times 24°
Other positions upon request.




P22

**Disclaimer**

The product information in this catalogue is for reference purposes. Please consult for the most up to date and accurate design information.

Piher Sensors & Controls S.A., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, “Piher”), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product described herein.

Piher disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Piher’s terms and conditions of sale, including but not limited to the warranty expressed therein, which apply to these products.

No licence, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Piher.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Piher products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Piher for any damages arising or resulting from such use or sale. Please contact authorised Piher personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Information contained in and/or attached to this catalogue may be subject to export control regulations of the European Community, USA, or other countries. Each recipient of this document is responsible to ensure that usage and/or transfer of any information contained in this document complies with all relevant export control regulations. If you are in any doubt about the export control restrictions that apply to this information, please contact the sender immediately. For any Piher International Corp. Exports, Note: All products / technologies are EAR99 Classified commodities. Exports from the United States are in accordance with the Export Administration Regulations. Diversion contrary to US law is prohibited.

v121214