



# Multilayer Diplexer

For 2400-2500MHz / 4900-5950MHz

# DPX165950DT-8148A1

1.6x0.8mm [EIA 0603]\*

\* Dimensions Code JIS[EIA]



# **Multilayer Diplexer**

For 2400-2500MHz / 4900-5950MHz


#### **Conformity to RoHS Directive**

# DPX165950DT-8148A1

0.10±0.10

Dimensions in mm


### SHAPES AND DIMENSIONS



| Terminal functions |           |  |  |
|--------------------|-----------|--|--|
| 1                  | Low-band  |  |  |
| 2                  | GND       |  |  |
| <u>2</u><br>3      | High-band |  |  |
| 4                  | GND       |  |  |
| 5                  | Common    |  |  |
| 6                  | GND       |  |  |

### ■ RECOMMENDED LAND PATTERN

0.25±0.10



Dimensions in mm

OROHS Directive Compliant Product: See the following for more details.https://product.tdk.com/info/en/environment/rohs/index.html

<sup>•</sup> All specifications are subject to change without notice.

<sup>•</sup> Before using these products, be sure to request the delivery specifications.



## **ELECTRICAL CHARACTERISTICS**

#### □LOW-BAND

| Item                         | Frequency Range<br>(MHz) | Min.  | Тур.         | Max.                |
|------------------------------|--------------------------|-------|--------------|---------------------|
| Insertion Loss (dB)          | 2400 to 2500             | _     | 0.23         | 0.35                |
| insertion Loss (db)          |                          | _     | 0.30         | 0.45 (-40 to +85°C) |
| Return Loss (dB)             | 2400 to 2500             | 12.74 | 24           | _                   |
|                              | 4800 to 5000             | 21    | 25           | _                   |
| Attenuation (dB)             | 5000 to 5950             | 23    | 27           | _                   |
|                              | 7200 to 7500             | 25    | 36           | _                   |
| Characteristic Impedance (Ω) |                          |       | 50 (Nominal) |                     |

<sup>·</sup> Ta: +25±5°C

#### ☐HIGH-BAND

| Item                         | Frequer<br>(MHz) | ncy Range | Min.  | Тур.         | Max.                |
|------------------------------|------------------|-----------|-------|--------------|---------------------|
| Inpartian Laga (dP)          | 4900 to 5950     | EOEO      | _     | 0.45         | 0.60                |
| Insertion Loss (dB)          |                  | 3930      | _     | 0.50         | 0.67 (-40 to +85°C) |
| Return Loss (dB)             | 4900 to          | 5950      | 11.73 | 18           | _                   |
|                              | 824 to           | 2170      | 27    | 32           | _                   |
| Attonuation (dD)             | 2400 to          | 2500      | 32    | 42           | _                   |
| Attenuation (dB)             | 8100 to          | 8900      | 10    | 12           | _                   |
|                              | 9800 to          | 11900     | 25    | 29           | _                   |
| Characteristic Impedance (Ω) |                  |           |       | 50 (Nominal) |                     |

<sup>·</sup> Ta: +25±5°C

#### □COMMON

| Item                         | Frequency Range<br>(MHz) | Min.  | Тур.         | Max. |
|------------------------------|--------------------------|-------|--------------|------|
| Deturn Loop (dB)             | 2400 to 2500             | 12.74 | 26           |      |
| Return Loss (dB)             | 4900 to 5950             | 11.73 | 21           |      |
| Characteristic Impedance (Ω) |                          |       | 50 (Nominal) |      |

<sup>·</sup> Ta: +25±5°C

#### **TEMPERATURE RANGE**

| Operating temperature | Storage temperature |
|-----------------------|---------------------|
| (°C)                  | (°C)                |
| -40 to +85            | -40 to +85          |


All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.



### **■ FREQUENCY CHARACTERISTICS**


### □LOW-BAND

#### **Insertion Loss**




## □HIGH-BAND


#### **Insertion Loss**




#### **Return Loss**




#### **Return Loss**



#### Attenuation



#### **Attenuation**




- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.




## **■ FREQUENCY CHARACTERISTICS**

#### □COMMON

#### **Return Loss**




#### Isolation



All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.



## ■ RECOMMENDED REFLOW PROFILE



| Preheating |       |              | Soldering                |              |              |            |
|------------|-------|--------------|--------------------------|--------------|--------------|------------|
|            |       |              | Critical zone (T3 to T4) |              | Peak         |            |
| Temp.      |       | Time         | Temp.                    | Time         | Temp.        | Time       |
| T1         | T2    | t1           | Т3                       | t2           | T4           | t3*        |
| 150°C      | 200°C | 60 to 120sec | 217°C                    | 60 to 120sec | 240 to 260°C | 30sec max. |

<sup>\*</sup>t3: Time within 5°C of actual peak temperature The maximum number of reflow is 3.

All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.



# REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

# SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

# **⚠** REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.

<sup>·</sup> All specifications are subject to change without notice.

<sup>•</sup> Before using these products, be sure to request the delivery specifications.