

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREDERICK, MINNESOTA

FED. MFR. CODE 91929

SWITCH-BASIC

CATALOG LISTING

101HS1

(M)101HS1
ISSUE 3

REPLACES

RELEASE NO.

101HS1

PAGE 1 OF 1

M

DRAWING
NUMBER

ISSUE
12

CHECK

REVISIONS

A	CO15761	LMH	20 APR 61
B	CO15920	MBF	23 JUNE 61
C	CO29829	LSB	10 JAN 72
D	CO55162N	TSK	20 JAN 86
E	CO 62736	MAM	15 MAR 88
F	CO61043	BGS	16 SEP 88
G	CO 75625	JDB	15 JULY 93
H	CO 76375	WES	2 SEP 93
J	CO-94122	TSM	17 MAR 99

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK

CHECK



NOTE-

- 1 - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000^{±.002} CENTERS
- 2 - TRAVEL CHARACTERISTICS ARE REFERENCED FROM THE UPPER SURFACE OF THE MOUNTING HOLES WITH THIS CONSTRUCTION
- 3 - FOR USE IN AMBIENT TEMPERATURE RANGE FROM MINUS 65°F TO PLUS 250°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA (TENTATIVE)			SCALE FULL
OPERATING FORCE-----10-22 OZ	CONTACT ARRANGEMENT S P D T			DO NOT SCALE PRINT
RELEASE FORCE-----4 OZ MIN	LINE VOLTAGE	INDUCTIVE LOAD	RESISTIVE LOAD	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL-----.020 MAX	28 VAC	8 AMP	25 AMP	TOLERANCES ARE:
OVERTRAVEL-----.010 MIN	125 VAC	1 AMP	5 AMP	ONE PLACE (.0) ±.030
		(SEA LEVEL-100,000 FT)		TWO PLACE (.00) ±.015
		(SEA LEVEL-70,000 FT)		THREE PLACE (.000) ±.005
				ANGLES ±
	L277 A-125VAC, 5A-28VDC			WEIGHT 1.6 OZ MAX

FO-50378
FORMTEK

DRAWN

LMH 20 APR 61

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[5SE1-6](#)