




- 1 HOUSING MATERIAL: LIQUID CRYSTAL POLYMER
COLOR: NATURAL.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE
- 3 CONTACT FINISH:(C)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS:
0.0005 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.
- A 4 PART MARKING PER TE SPEC 115-9009 LOCATED APPROXIMATELY
AS SHOWN BETWEEN RIBS/SLOTS ON EITHER SIDE OF HOUSING AT
MANUFACTURER'S DISCRETION.
- 5 PART TO BE MARKED WITH DATE CODE ONLY.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

RECOMMENDED CIRCUIT PATTERN
PER IPC-D300 TYPE II, CLASS C
(COMPONENT SIDE)

82		41	83.88	3	210	5223524-7
70		35	71.88	3	180	5223524-6
58		29	59.88	3	150	5223524-5
46		23	47.88	3	120	5223524-4
34		17	35.88	3	90	5223524-3
22		11	23.88	3	60	5223524-2
10		5	11.88	3	30	5223524-1
C		B	A	FINISH	NO OF POSN	PART NUMBER
6 OBSOLETE						
6 OBSOLETE						

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.MCMMASTER	14DEC04	Tyco Electronics Corporation	
DIMENSIONS: mm		CHK R.WERTZ	14DEC04	Harrisburg, PA 17105-3608	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.WERTZ	14DEC04	NAME	
0 PLC ± -		PRODUCT SPEC		ASSEMBLY, PIN HEADER, RIGHT ANGLE,	
1 PLC ± -		APPLICATION SPEC		5 ROW, Z-PACK 2mm FB,	
2 PLC ± 0.13		WEIGHT		PRESS FIT LEADS	
3 PLC ± -		SIZE		RESTRICTED TO	
4 PLC ± -		SCALE		A1 00779 C=5223524	
MATERIAL		FINISH		CUSTOMER DRAWING	
1		2	3	SHEET 1 OF 1	
				REV A	