

INTRODUCTION:

Adam Tech BHR Series .100" Box Headers are a dual row shrouded header for use with dual row IDC female socket connectors. Our low profile, space saving design has a center slot for the socket's polarization bump. Adam Tech's Box Headers are available in Straight PCB Mount, Right Angle PCB Mount and SMT Mounting. Plating options include choice of Gold, Tin or Selective Gold. SMT versions are manufactured with a Hi-Temp insulator. Additional options include latches and custom pin lengths.

FEATURES:

- Superior low profile design
- Slot for IDC socket Polarization bump
- Straight PCB, Right Angle PCB and SMT versions
- Gold, Tin or Selective Gold plating
- Options include Elevated types and integral latches
- Hi-Temp insulator available

MATING SOCKETS:

Adam Tech .100" X .100" dual row IDC sockets

SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL94V-0
Optional Hi-Temp insulator: Nylon 6T, rated UL94V-0
Insulator Color: Black (Gray optional)
Contacts: Brass

Plating:

U = Gold flash (30u" optional) over nickel underplate
SG = Gold flash (30u" optional) over nickel underplate on contact area, tin over copper underplate on tails.
T = Tin over copper underplate overall

Electrical:

Operating voltage: 250V AC max.
Current rating: 1 Amp max
Contact resistance: 20 mΩ max. initial
Insulation resistance: 5000 MΩ min.
Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Mating durability: 500 cycles min.

Temperature Rating:


Operating temperature: -55°C to +105°C

PACKAGING:

Anti-ESD plastic trays

SAFETY AGENCY APPROVALS:

UL Recognized File No. E224053
CSA Certified File No. LR1578596






ORDERING INFORMATION


BHR	50	V	U	A
SERIES INDICATOR BHR = .100" Box Header		MOUNTING ORIENTATION V = Straight Mount H = Right Angle Mount		PIN LENGTH A = Standard solder tail B = Special length, customer specified SMT = Surface Mount
	NO. OF POSITIONS 08, 10, 14, 16, 20, 24, 26, 30, 34, 40, 44, 50, 60, 64		CONTACT PLATING U = Gold Plated T = Tin Plated SG = Gold Plating in contact area, tin plated tails	

OPTIONS:


Add designator(s) to end of part number
LL = Box header with long latches
SL = Box header with short latches
30 = 30 μin gold plating in contact area
GY = Gray color insulator
HT = Hi-Temp insulator for Hi-Temp soldering processes up to 260°C (Add this option for thru-hole products only.
All SMT products are manufactured with Hi-Temp insulators)






BHR
STRAIGHT PCB MOUNT



BHR-34-VUA




A = .100 [2.54] X No. of Positions / 2 + .300 [7.62]
B = .100 [2.54] X No. of Positions / 2 + .200 [5.08]
C = .100 [2.54] X No. of Spaces






BHR
RIGHT ANGLE PCB MOUNT




BHR-34-HUA




A = .100 [2.54] X No. of Positions / 2 + .300 [7.62]
B = .100 [2.54] X No. of Positions / 2 + .200 [5.08]
C = .100 [2.54] X No. of Spaces



BHR
SURFACE MOUNT







BHR-30-VSG-SMT



A = .100 [2.54] X No. of Positions / 2 + .300 [7.62]
B = .100 [2.54] X No. of Positions / 2 + .200 [5.08]
C = .100 [2.54] X No. of Spaces

BHR

STRAIGHT MOUNT BOX HEADER WITH LATCHES







BHR-34-VUA-LL

A = .100 [2.54] X No. of Positions / 2 + .301
B = .100 [2.54] X No. of Positions / 2 + .189
C = .100 [2.54] X No. of Positions / 2


BHR

RIGHT ANGLE MOUNT BOX HEADER WITH LATCHES



BHR-34-HUA-LL

A = .100 [2.54] X No. of Positions / 2 + .301
B = .100 [2.54] X No. of Positions / 2 + .189
C = .100 [2.54] X No. of Positions / 2



Recommended PCB Layout

LATCH TYPE	DIMENSIONS	
	X	Y
LONG LATCH (-LL)	1.035 [26.30]	.575 [14.60]
SHORT LATCH (-SL)	.901 [22.90]	.417 [10.60]

INTRODUCTION:

Adam Tech BHR Series Elevated Box Headers provide all of the advantages of our standard Box Headers such as our Low Profile design, snug fit & polarized mating but have additional plastic insulators in place to stabilize rows of pins for stacking applications. This series is available in Straight, Right Angle & SMT mounting with standard or customer specified Stacking Heights and PCB tail lengths.

FEATURES:

Elevated for Stacking applications
Low Profile design
Straight, Right Angle & SMT mounting options
Standard or customer specified Stacking Heights & PCB tail lengths

MATING SOCKETS:

Adam Tech .100" X .100" dual row IDC sockets

SPECIFICATIONS:

MATERIAL:

Insulator: PBT, glass reinforced, rated UL94V-0
Optional Hi-Temp insulator: Nylon 6T, rated UL94V-0
Insulator Color: Black (Gray optional)
Contacts: Brass

PLATING:

U = Gold flash (30u" optional) over nickel underplate
SG = Gold flash (30u" optional) over nickel underplate on contact area, tin over copper underplate on tails.
T = Tin over copper underplate overall

ELECTRICAL:

Operating voltage: 250V AC max.
Current rating: 1 Amp max
Contact resistance: 20 mΩmax. initial
Insulation resistance: 5000 MΩmin.
Dielectric withstanding voltage: 1000V AC for 1 minute

MECHANICAL:

Mating durability: 500 cycles min.

TEMPERATURE RATING:


Operating temperature: -55°C to +105°C

PACKAGING:


Anti-ESD plastic trays

SAFETY AGENCY APPROVALS:

UL Recognized
CSA Certified



ORDERING INFORMATION



OPTIONS:

Add designator(s) to end of part number

30 = 30u" Gold on contact area

GY = Gray color insulator

HT = Hi-Temp insulator for Hi-Temp soldering processes up to 260°C (Add this option for thru-hole products only.)

All SMT products are manufactured with Hi-Temp insulators)