

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

09-01-7094

Status:


Active

Overview:

Edge Card Connectors

Description:

3.96mm Pitch KK® Crimp Housing, Edge Card Connector, Single-Sided, Surface Mount, Polarized, with Flange, 9 Circuits, Rib between 5 & 6



Series

image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-08-50 \(PDF\)](#)
- [Packaging Specification PK-2574-001 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL

E29179

General

Product Family

Series

Component Type

Overview

Product Name

UPC

Edge Card Connectors

2574

Edgecard to Wire

Edge Card Connectors

Edge Card, KK®

800753845138

Physical

(p)ower-(s)ignal Configuration

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Entry Angle

Flammability

Keying to Mating Part

Material - Plating Mating

Material - Resin

Net Weight

PCB Retention

PCB Thickness - Recommended

Packaging Type

Panel Mount

Pitch - Mating Interface

Polarized to Mating Part

Temperature Range - Operating

Termination Interface: Style

9s - 0p

9

9

Natural

25

Vertical (Top Entry)

94V-2

Yes

N/A

Nylon

3.447/g

None

1.60mm

Bag

With Flange

3.96mm

Yes

0°C to +75°C

N/A

Electrical

Current - Maximum per Contact

Voltage - Maximum

4.25A, 4.5A, 4.75A, 4A, 5A

250V

Material Info

Old Part Number

2574-09B4

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

PK-2574-001

PS-08-50

SD-2574

EU RoHS

ELV and RoHS  
Compliant

REACH SVHC

Contains SVHC: No  
Low-Halogen Status  
Low-Halogen

China RoHS



Need more information on product  
environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of  
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
non-product compliance questions.

Search Parts in this Series

2574Series

Mates With

PCB, 1.60mm Max. Thickness

Use With

2878 Terminals, 2478 Terminals, 2578  
Terminals, Bifurcated

This document was generated on 09/22/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[09-01-7094](#)