

Design Support

Technical Documentation



Design Resources

Design & Development Tools

Evaluation Boards

Conversion Services

Evaluation Board Documents

Custom Foundry Services

Sample Kits

Simulation Models

Product Recommendation Tools

Software

Video

Technical Support

Home > Support > Design Support > Design Resources > Evaluation Boards

NCP3064DFBCKGEVB:NCP3064 DFN8 BUCK DB

Evaluation Board Description


The NCP3064 device supports a buck configuration with a wide input voltage range from 3.0V to 40.0V. The NCP3064 is a low cost converter that supports a pcurrent of 1.5A with a maximum duty cycle of 85.7%. The ON/OFF function allows turn the device to low consumption mode. Size: 45mm x 28mm x 14mm

Features and Applications

Features

- Input Voltage Range from 3.0 V to 40 V
- Logic Level Shutdown Capability
- Low Power Standby Mode, Typical 100 uA
- Output Switch Current to 1.5 A
- Adjustable Output Voltage Range
- 150 kHz Frequency Operation
- Precision 2% Reference
- Internal Thermal Shutdown Protection
- CyclebyCycle Current Limiting
- NCV Prefix for Automotive and Other Applications Requiring Site and Control Changes
- These are PbFree Devices

Evaluation Board Information

Evaluation Board	Status	Pb - free	Short Description	Parts Used	Action
NCP3064DFBCKGEVB	Active	 Pb - fr	NCP3064 DFN8 BUCK DB	NCP3064MNTXG	Contact Local Sales Office

Technical Documents

Type	Document Title	Document ID/Size	Rev
Eval Board: BOM	NCP3064DFBCKGEVB Bill of Materials ROHS Compliant	NCP3064DFBCKGEVB_BOM_ROHS.PDF - 39.0 KB	1
Eval Board: Gerber	NCP3064DFBCKGEVB Gerber Layout Files (Zip Format)	NCP3064DFBCKGEVB_GERBER.ZIP - 38.0 KB	0
Eval Board: Schematic	NCP3064DFBCKGEVB Schematic	NCP3064DFBCKGEVB_SCHEMATIC.PDF - 137.0 KB	0
Eval Board: Test Procedure	NCP3064DFBCKGEVB Test Procedure	NCP3064DFBCKGEVB_TEST_PROCEDURE.PDF - 152.0 KB	0

Previously Viewed Products

Select Product ...



Clear List

Design Support

- Technical Documentation
- Design Resources
- Technical Support
- Sales Support