




Features


- > PLL solution.
- > 3.3V and 2.5V operation available.
- > LVPECL output, output frequencies 50 MHz to 700 MHz.
- > Low phase noise and jitter.
- > Tri-state function available.
- > Applications : Fibre Channel, Gigabit Ethernet, Serial ATA, Serial Attached SCSI, PCI-Express, SDH / SONET.
- > RoHS compliant / Pb Free.

Electrical Specifications

Item / Type	BC
Output Type	LVPECL
Output Load	50 Ω to VDD - 2 V
Oscillation Mode	PLL
Supply Voltage	2.5 V , 3.3 V
Frequency Range	50 ~ 700 MHz
Overall Frequency Stability *	± 50 ppm (- 40 ~ + 85 °C)
Operating Temperature Range	- 40 ~ + 85 °C
Storage Temperature Range	- 55 ~ + 125 °C
Voltage Vol (Max.) / Voh (Min.)	VDD - 1.7 V / VDD - 1.4 V
Rise (Tr) / Fall (Tf) Time (20 % ~ 80 %)	1 ns Max.
Supply Current	99 mA Max.
Symmetry	45 ~ 55 %
Start-up Time	10 ms Max.
Phase Jitter (12 KHz ~ 20 MHz)	1 ps Max.

* Inclusive of initial tolerance, operating temperature, supply voltage variation and aging.


Dimensions



PAD FUNCTION:
 1:ENABLE CONTROL
 2:NC
 3:GND
 4:OUT
 5:~OUT
 6:VDD

Suggested Layout

* :Power Supply Decoupling Capacitor is Required.



Units:mm

Remark : Specification subject to change without prior notice. Please confirm with our sales.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[BC-187.500MBE-T](#) [BC-212.500MBE-T](#) [BC-250.000MBE-T](#) [BC-312.500MBE-T](#) [BC-622.080MBE-T](#) [BB-80.000MCE-T](#)
[BC-187.500MCE-T](#) [BC-212.500MCE-T](#) [BC-250.000MCE-T](#) [BC-312.500MCE-T](#) [BC-622.080MCE-T](#)