


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	75710-4006
Status:	Active
Overview:	GbX I-Trac™ Backplane Connector System
Description:	1.85mm by 3.70mm Pitch, GbX I-Trac™ Right Angle Receptacle Module, Right Guide, 11 Rows, 6 Columns, 132 Circuits
Replacement Part Number:	757105006



Documents:	
3D Model	Test Summary TS-75710-998 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-75710-999 (PDF)	

Agency Certification	
UL	E29179
General	
Product Family	Backplane Connectors
Series	75710
Application	Coplanar, Daughtercard
Component Type	PCB Receptacle
Overview	GbX I-Trac™ Backplane Connector System
Product Name	GbX I-Trac™
Replacement Part Number	757105006
Style	N/A
UPC	822350316866
Physical	
Circuits (Loaded)	132
Circuits (maximum)	132
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Material - Resin	High Temperature Thermoplastic
Net Weight	20.726/g
Number of Columns	6
Number of Pairs	6, Open Pin Field
Number of Rows	11
Orientation	Right Angle
PC Tail Length	2.00mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.85mm, 3.70mm
Pitch - Termination Interface	1.00mm, 2.70mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	Yes
Stackable	No

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[75710Series](#)

Mates With
75705 GbX I-Trac™ Vertical Header Module. 75910 GbX I-Trac™ Right Angle Header Module

Use With
[78234](#) GbX I-Trac™ Right Angle Power Header. [76153](#) Pirate Cannon Wide Guide Module

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Daughter Card	0622023000
Signal Module	
Removal Tool	

Surface Mount Compatible (SMC)	Yes	Press-In Tool	<u>0622018605</u>
Temperature Range - Operating	-55°C to +80°C	for Right Angle	
Termination Interface: Style	Through Hole - Compliant Pin	Receptacle and	
		Header 11-Row, 6-	
		Column	
Electrical			
Current - Maximum per Contact	1A		
Data Rate	12.0 Gbps		
Real Signals (per 25mm)	75		
Shield Type	N/A		
Shielded	No		
Voltage - Maximum	120V AC (RMS)/DC		
Material Info			
Reference - Drawing Numbers			
Product Specification	PS-75710-999		
Sales Drawing	SD-75710-004		
Test Summary	TS-75710-998		

This document was generated on 03/13/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75710-4006](#)