



RECOMMENDED PANEL LAYOUT





TERMINAL DETAIL
SCALE 2X

- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 3. TERM. NOS. FOR REF. ONLY
 4. CONTACT RATING: 4A @125VAC/28VDC, 2A @250VAC
 5. DIELECTRIC STRENGTH: 1500VAC-1 min.
 6. ELECTRICAL LIFE: 10,000 make-and-break cycles
at full load.
 7. MATERIALS:
CONTACTS: Silver Plated Cu (Q Contact material)
TERMINALS: Silver Plated Cu (Q Contact material)
MOUNTING NUT: Nickel Plated zinc alloy
CONTACT SPRING: Piano Wire
KEYS: (QTY. 2) Brass with code no. A126
LOCK: Bright Ni plated zinc alloy with NI facing
TUMBLER Mechanism: 4-disc tumbler cylinder.
 8. 2002/95/EC (ROHS) COMPLIANT



Pos. 1 Ref.



CIRCUIT: DP (45° INDEXING)
CONTACT CONFIGURATION

SWITCH FUNCTION			
CONNECTED TERMINAL #			
POS. 1	POS. 2	POS. 3	
8-1,4-5	1-2,5-6	8-7,3-4	

- LEGEND
- =Detent Positions (45°)
 - ⊙ =Key pull possible in these positions
 - ▲ =MOMENTARY POS.

D	19509	CHANGED THREAD DESCRIPTION	12/08/10	BGL
C	16963	FIXED SWITCH FUNCTION	2/5/07	TN
B	15031	UPDATED DRAWING	6/24/05	JB
A	11566	RELEASED FOR PRODUCTION	7/12/01	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				
TITLE				
K0129D-A126				
E-SWITCH®				
SCALE				
1:1				
DATE				
2/5/2007				
DR				
TN				
DWG				
K200308				
REV				
D				