

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION





- . - .

© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS


| P | LTR | DESCRIPTION   | DATE    | DWN | APVD |
|---|-----|---------------|---------|-----|------|
|   | A   | ECR-19-009119 | 03JUL19 | T.Q | W.H  |



PANEL CUTOUT DIMENSION (TOLERANCE:±0.1)  
RECOMMEND PANEL THICKNESS :0.8mm~1.6mm

NOTES:

- 1 MATERIAL : HOUSING - 66 NYLON (UL94V-0)  
POST - TIN BRASS  
COMMONING BAR - TIN BRASS
- 2 THE PANEL SHOULD BE PUNCHED IN THE  
SAME DIRECTION OF THE HOUSING MOUNTNG  
DIRECTION.
- 3 PRODUCT SPEC : 108-5408, 108-60016



|               |                     |               |
|---------------|---------------------|---------------|
| COMMONING BAR | 1 4                 | COMMONING BAR |
|               | 2 3                 |               |
|               | 3 2                 |               |
|               | 4 1                 |               |
|               | A B                 |               |
|               | CIRCUIT NO.         |               |
|               | <COMMONING CIRCUIT> |               |
|               | (2-292157-4)        |               |

|               |                     |               |
|---------------|---------------------|---------------|
| COMMONING BAR | 1 4                 | COMMONING BAR |
|               | 2 3                 |               |
|               | 3 2                 |               |
|               | 4 1                 |               |
|               | A B                 |               |
|               | CIRCUIT NO.         |               |
|               | <COMMONING CIRCUIT> |               |
|               | (292157-4)          |               |

|               |                     |               |
|---------------|---------------------|---------------|
| COMMONING BAR | 1 6                 | COMMONING BAR |
|               | 2 5                 |               |
|               | 3 4                 |               |
|               | 4 3                 |               |
|               | 5 2                 |               |
|               | 6 1                 |               |
|               | A B                 |               |
|               | CIRCUIT NO.         |               |
|               | <COMMONING CIRCUIT> |               |
|               | (2-292157-6)        |               |

|               |                     |               |
|---------------|---------------------|---------------|
| COMMONING BAR | 1 6                 | COMMONING BAR |
|               | 2 5                 |               |
|               | 3 4                 |               |
|               | 4 3                 |               |
|               | 5 2                 |               |
|               | 6 1                 |               |
|               | A B                 |               |
|               | CIRCUIT NO.         |               |
|               | <COMMONING CIRCUIT> |               |
|               | (292157-6)          |               |

|               |                     |               |
|---------------|---------------------|---------------|
| COMMONING BAR | 1 8                 | COMMONING BAR |
|               | 2 7                 |               |
|               | 3 6                 |               |
|               | 4 5                 |               |
|               | 5 4                 |               |
|               | 6 3                 |               |
|               | 7 2                 |               |
|               | 8 1                 |               |
|               | A B                 |               |
|               | CIRCUIT NO.         |               |
|               | <COMMONING CIRCUIT> |               |
|               | (292157-8)          |               |

|               |                     |               |
|---------------|---------------------|---------------|
| COMMONING BAR | 1 15                | COMMONING BAR |
|               | 2 14                |               |
|               | 3 13                |               |
|               | 4 12                |               |
|               | 5 11                |               |
|               | 6 10                |               |
|               | 7 9                 |               |
|               | 8 8                 |               |
|               | 9 7                 |               |
|               | 10 6                |               |
|               | 11 5                |               |
|               | 12 4                |               |
|               | 13 3                |               |
|               | 14 2                |               |
|               | 15 1                |               |
|               | A B                 |               |
|               | CIRCUIT NO.         |               |
|               | <COMMONING CIRCUIT> |               |
|               | (1-292157-5)        |               |

|          |             |     |      |      |      |      |
|----------|-------------|-----|------|------|------|------|
| OBSOLETE | 2-292157-6  | 6   | 19.6 | 16.0 | 15.8 | 10.0 |
|          | 2-          | -4  | 4    | 15.6 | 12.0 | 11.8 |
| OBSOLETE | -1          | -5  | -15  | 37.6 | 34.0 | 33.8 |
|          |             | -8  | 8    | 23.6 | 20.0 | 19.8 |
|          |             | -6  | 6    | 19.6 | 16.0 | 15.8 |
|          |             | -4  | 4    | 15.6 | 12.0 | 11.8 |
|          | 292157-2    | 2   | 11.6 | 8.0  | 7.8  | 2.0  |
|          | NATURAL     | POS | D    | C    | B    | A    |
|          | PART NUMBER |     |      |      |      |      |

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
10>X : ± 0.2  
30>X>10 : ± 0.25  
100>X>30 : ± 0.3  
ANGEL : ± 3°

|                                        |                                                                                                                       |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |                                                                                                                       |
| DIMENSIONS:<br>mm                      | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ± -<br>1 PLC ± -<br>2 PLC ± -<br>3 PLC ± -<br>4 PLC ± -<br>ANGLES ± - |
| MATERIAL<br>SEE NOTE                   | FINISH<br>SEE NOTE                                                                                                    |

|                          |                         |                             |
|--------------------------|-------------------------|-----------------------------|
| DWN<br>S.XU<br>31JAN03   | CHK<br>S.YAO<br>31JAN03 | APVD<br>T.SASAKI<br>31JAN03 |
| PRODUCT SPEC<br>SEE NOTE |                         |                             |
| APPLICATION SPEC<br>-    |                         |                             |
| WEIGHT<br>-              |                         |                             |
| CUSTOMER DRAWING         |                         |                             |

|                                                                                        |                    |                        |                    |
|----------------------------------------------------------------------------------------|--------------------|------------------------|--------------------|
| TE Connectivity                                                                        |                    |                        |                    |
| RELAY POST HDR ASS'Y(PANEL MOUNT TYPE)<br>WITH COMMONING BAR<br>AMP CT CONN. 2mm PITCH |                    |                        |                    |
| SIZE<br>A3                                                                             | CAGE CODE<br>00779 | DRAWING NO<br>C=292157 | RESTRICTED TO<br>- |
| SCALE<br>4:1                                                                           | SHEET<br>1 OF 1    | REV<br>A               |                    |