


17H

D-Sub connectors - Stamped and Formed Contacts

DUAL PORT D-SUB CONNECTORS



MAIN CHARACTERISTICS

Specifications

- Connectors according to MIL C24308

Materials and platings	
Shells	Steel, tin plated
Insulator	Glass-filled thermoplastic, UL 94V-0
Pin contacts	Brass, selected gold in mating area; 2.54µm (100µ") min. tin on termination area over 1.27µm (50µ") min. nickel
Socket contact	Phosphor bronze, selected gold in mating area; 2.54µm (100µ") min. tin on termination area over 1.27µm (50µ") min. nickel
Rear insert	Brass, 2.54µm (100µ") min. nickel plated
Boardlock	Phosphor bronze, 2.54µm (100µ") min. tin plated
Screwlock	Brass, 2.54µm (100µ") min. nickel plated

Electrical Data	
Current rating	3A
Voltage rating	250V AC/rms 60Hz
Withstanding voltage	1000V AC/rms 60Hz for one minute
Insulation resistance	1000MΩ
Contact resistance	20mΩ max

Climatic Data	
Operating temperature	-55°C to +125°C
Salt spray	24 hours

Mechanical Data		
Single contact insertion force	0.54kg (1.19lb) max	
Single contact withdrawal force	0.06kg (0.13lb) min	
Mating and unmating force	Unit: kg (lb)	
No. of Cts	Mate (max)	Unmate (min)
9	3.05 (6.74)	0.36 (0.79)
15	5.09 (11.24)	0.46 (1.01)
25	8.44 (18.66)	0.81 (1.8)
15 (Hi-den)	3.81 (8.42)	0.52 (1.14)
Standard plating thicknesses		
• gold flash		
• 0.4µm (15µ") gold		
• 0.76 µm (30µ") gold		

DESCRIPTION

Amphenol's G17H dual port connectors are a state of the art design. The front metal shell helps reduce EMI / RFI emissions.

Designed to save PC board space, Amphenol's dual port provides two I / O connectors in a minimal amount of board space.

*Economical
dual port
connectors*



APPLICATIONS

- Industrial
- Telecom
- Any industry standard I / O connections



Amphenol

17H / E13




Technical drawing of a quad boardlock showing dimensions and tolerances. The drawing includes the following specifications:

- Overall width: $3.81 (.150)$
- Top edge dimension: $1.27 (.050)$
- Bottom edge dimension: $2.84 (.112)$
- Internal width dimension: $B \pm 0.13 (.005)$
- Internal width dimension: $E \pm 0.05 (.002)$
- Internal width dimension: X
- Top edge dimension: $2.84 (.112)$
- Bottom edge dimension: $8.08 (.318)$
- Bottom edge dimension: $8 (.315)$
- Top edge dimension: $\phi 3.05 (.120)$
- Bottom edge dimension: $\phi 1.02 (.040)$
- Note: "only for quad boardlock"


Amphenol

Panel mounting option


Flange mounting options:



Threaded rear insert

0 / 4


Fixed front female screwlock

7


Removable female screwlock

1 / 5


Board mounting options:



Threaded hole

1

Dual arrowhead boardlock

2

Quad arrowhead boardlock

3

Dual Port Connectors

L17H X X X X X X X X

Spacing Between Ports

- 1 - F = 15.88mm (.625")
G = 28.42mm (1.12")
- 2 - F = 19.05mm (.750")
G = 31.60mm (1.24")
- 3 - F = 22.86mm (.900")
G = 35.41mm (1.39")
- 4 - **SCSI**
G = 12.80mm (.504")
- 7 - F = 20.70mm (.815")
G = 32.20mm (1.26")

Top Connector

- 1 = 9 Pos. Male
- 2 = 9 Pos. Female
- 3 = 15 Pos. Male
- 4 = 15 Pos. Female
- 5 = 25 Pos. Male
- 6 = 25 Pos. Female
- 7 = 15 Pos. High Density Female
- 8 = 50 Pos. Female SCSI
- 9 = 26 Pos. High Density Female
- J = 15 Pos. High Density Male
- D = 37 Pos. Male
- E = 37 Pos. Female
- F = 44 Pos. High Density Male
- G = 44 Pos. High Density Female
- M = 62 Pos. High Density Male
- N = 62 Pos. High Density Female
- P = 78 Pos. High Density Male
- Q = 78 Pos. High Density Female

Bottom Connector

- 1 = 9 Pos. Male
- 2 = 9 Pos. Female
- 3 = 15 Pos. Male
- 4 = 15 Pos. Female
- 5 = 25 Pos. Male
- 6 = 25 Pos. Female
- 7 = 15 Pos. High Density Female
- 8 = 50 Pos. Female SCSI
- 9 = 26 Pos. High Density Female
- K = 15 Pos. High Density Male
- D = 37 Pos. Male
- E = 37 Pos. Female
- F = 44 Pos. High Density Male
- G = 44 Pos. High Density Female
- M = 62 Pos. High Density Male
- N = 62 Pos. High Density Female
- P = 78 Pos. High Density Male
- Q = 78 Pos. High Density Female
- R = 9 Pos. Male + 9 Pos. Male
- S = 9 Pos. Female + 9 Pos. Female

Footprint Options

- SD / SD**
BLANK = 8.08mm (.318")
- SD / HD**
BLANK = 5.08mm (.200")
- 889** = 8.89mm (.350")
- HD / HD**
BLANK = 8.89mm (.350")
- 508** = 5.08mm (.200")

Flange Mounting Options

- 0 = 4-40unc Rear Insert
- 1 = 4-40unc Removable Screwlock
- 3 = 3.05mm (.120") Clear Hole
- 4 = M3 Rear Insert
- 5 = M3 Removable Screwlock
- 7 = 4-40unc Fixed Front Screwlock

Board Mounting Options

- 0 = Triple Arrowhead Boardlock
- 1 = 4 * Threaded 4-40unc Inserts
- 2 = Dual Arrowhead Boardlocks
- 3 = Quad Arrowhead Boardlocks
- 4 = 3.18mm (.125") Clear Hole

Shell Plating

- 1 = Bright Tin / Nickel
- 2 = Nickel

Contact Plating

- 0 = Flash Fold
- 1 = 0.4μm (15μ") Gold
- 2 = 0.76μm (30μ") Gold
- 3 = Full Flash Gold
- 4 = 1.27μm (50μ") Gold

For special request, please consult factory

Do not hesitate to contact us for further information

Amphenol

Amphenol IT & Communication Products

Block A3/A4, The 4th Industrial District of
Industrial Headquarters, Dong Keng Road
Gong Ming Town, Shen Zhen China
Fax: +86(0)755 2754 9955

Technical Support

Tel: +86(0)755 2717 7945
Info-dsub@amphenol.com.cn
http://www.dsubconnector.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>L17HRD2M115K</u>	<u>L17H2222120</u>	<u>L17H1110120</u>	<u>L17H1110121</u>	<u>L17H1110124</u>	<u>L17H1110125</u>	<u>L17H1110127</u>
<u>L17H1110130</u>	<u>L17H1110131</u>	<u>L17H1110134</u>	<u>L17H1110135</u>	<u>L17H1110137</u>	<u>L17H1111120</u>	<u>L17H1111121</u>
<u>L17H1111124</u>	<u>L17H1111125</u>	<u>L17H1111127</u>	<u>L17H1111130</u>	<u>L17H1111131</u>	<u>L17H1111134</u>	<u>L17H1111135</u>
<u>L17H1111137</u>	<u>L17H1112120</u>	<u>L17H1112121</u>	<u>L17H1112124</u>	<u>L17H1112125</u>	<u>L17H1112127</u>	<u>L17H1112130</u>
<u>L17H1112131</u>	<u>L17H1112134</u>	<u>L17H1112135</u>	<u>L17H1112137</u>	<u>L17H1120120</u>	<u>L17H1120121</u>	<u>L17H1120124</u>
<u>L17H1120125</u>	<u>L17H1120127</u>	<u>L17H1121120</u>	<u>L17H1121121</u>	<u>L17H1121124</u>	<u>L17H1121125</u>	<u>L17H1121127</u>
<u>L17H1122120</u>	<u>L17H1122121</u>	<u>L17H1122124</u>	<u>L17H1122125</u>	<u>L17H1122127</u>	<u>L17H1130130</u>	<u>L17H1130131</u>
<u>L17H1130134</u>	<u>L17H1130135</u>	<u>L17H1130137</u>	<u>L17H1131130</u>	<u>L17H1131131</u>	<u>L17H1131134</u>	<u>L17H1131135</u>
<u>L17H1131137</u>	<u>L17H1132130</u>	<u>L17H1132131</u>	<u>L17H1132134</u>	<u>L17H1132135</u>	<u>L17H1132137</u>	<u>L17H1210120</u>
<u>L17H1210121</u>	<u>L17H1210124</u>	<u>L17H1210125</u>	<u>L17H1210127</u>	<u>L17H1210130</u>	<u>L17H1210131</u>	<u>L17H1210134</u>
<u>L17H1210135</u>	<u>L17H1210137</u>	<u>L17H1211120</u>	<u>L17H1211121</u>	<u>L17H1211124</u>	<u>L17H1211125</u>	<u>L17H1211127</u>
<u>L17H1211130</u>	<u>L17H1211131</u>	<u>L17H1211134</u>	<u>L17H1211135</u>	<u>L17H1211137</u>	<u>L17H1212120</u>	<u>L17H1212121</u>
<u>L17H1212124</u>	<u>L17H1212125</u>	<u>L17H1212127</u>	<u>L17H1212130</u>	<u>L17H1212131</u>	<u>L17H1212134</u>	<u>L17H1212135</u>
<u>L17H1212137</u>	<u>L17H1220120</u>	<u>L17H1220121</u>	<u>L17H1220124</u>	<u>L17H1220125</u>	<u>L17H1220127</u>	<u>L17H1220130</u>
<u>L17H1220131</u>	<u>L17H1220134</u>					