



Copyright FCI.

A

B

C

D

PRODUCT NUMBER

ICD056GVPI63X-XX

PRODUCT NUMBER DESCRIPTION:

ICD056GVPI63 X - XX

LENGTH


XX= METERS

EXAMPLE : 05 = 05 METERS (DIM "L")

C0 = 100 METERS (DIM "L")



DIGITAL DIAGNOSTIC MONITORING

D : WITH DDM SUPPORT



VIEW A


VIEW A



spec ref	-	dr	M Srinivasan	2012/05/02	projection	MM	size	A3	scale	1:1
tolerance std	ASME Y14.5	eng	Andreas Krink	2012/05/08	chr	-	ecn no	-	rel level	Released
surface	✓	appr	Sven Otte	2012/05/08	product family	QSFP+ AOC	rel level	Released	rev	A
linear	0.X	±0.3	0.XX	±0.10	0.XXX	±0.05	angular	0°	±2°	
ASME Y14.5										
TOLERANCES UNLESS OTHERWISE SPECIFIED		www.fci.com		cat. no.		Product - Customer Drw		sheet 1 of 2		
STRAIGHT BOOT PRODUCT ASSEMBLY		QSFP+ AOC FDR		ICD056GVPI63X		PDS: Rev :A		STATUS:Released		Printed: May 10, 2012

FCI
Copyright FCI.

PRODUCT NUMBER
ICD056GVP163X-XX




NOTES:

1. MATERIAL:
COVERS : ZINC ALLOY/ COPPER UNDERPLATE/ NICKEL OVERPLATE
PULL TAB : THERMOPLASTIC POLYMER
LATCH RELEASE: ZINC ALLOY/ COPPER UNDERPLATE/ NICKEL OVERPLATE
DRIVE SCREWS: STAINLESS STEEL
STRAIN RELIEF BOOT : THERMOPLASTIC
SPRING : STAINLESS STEEL
PADDLE CARD: PRINTED CIRCUIT SUBSTRATE-FR4.
DUST COVER : POLY ETHYLENE
TOP & BOTTOM BLISTER (NOT SHOWN) : PET
PACKAGING: FOR CABLE-LENGTH >30M ONE BOX-SET IS USED INSTEAD OF TOP/BOTTOM BLISTER
BOX-SET MATERIAL: PAPERBOARD AND ANTISTATIC PLASTIC
2. REFERENCE PRODUCT SPECIFICATION GS-12-1059
FOR DETAILED SPECIFICATIONS.
3. THIS PRODUCT MEETS THE RESTRICTION OF HAZARDOUS SUBSTANCES IN
ELECTRICAL AND ELECTRONIC EQUIPMENT (RoHS).DIRECTIVE 2002/95/EC.
4. THIS DIMENSION IS A FINISHED PRODUCT LENGTH.
5. A "△" SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED
WITH THE CURRENT DRAWING REVISION. THE CURRENT REVISION WILL BE SHOWN IN THE SYMBOL.

EDGE CONNECTOR PAD DESCRIPTION

POSITION	SYMBOL	POSITION	SYMBOL
19	GND	20	GND
18	RX1n	21	RX2n
17	RX1p	22	RX2p
16	GND	23	GND
15	RX3n	24	RX4n
14	RX3p	25	RX4p
13	GND	26	GND
12	SDA	27	ModPrsL
11	SCL	28	In+L
10	VccRx	29	VccTx
9	ResetL	30	VccI
8	ModSelL	31	LPMode
7	GND	32	GND
6	TX4p	33	TX3p
5	TX4n	34	TX3n
4	GND	35	GND
3	TX2p	36	TX1p
2	TX2n	37	TX1n
1	GND	38	GND

spec ref		-		dr	M Srinivasan	2012/05/02	projection 	MM 	size	A3	scale	2:1	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Andreas Krink	2012/05/08			ecn no		-		
ASME Y14.5				chr	-	-			rel level		Released		
-				appr	Sven Otte	2012/05/08	product family		QSFP+ AOC				
surface ✓	linear	0.X	±0.3		title	STRAIGHT BOOT PRODUCT ASSEMBLY				dwg no	ICD056GVP163X		rev
		0.XX	±0.10										
		0.XXX	±0.05										
ASME Y14.5	angular	0°	±2°	www.fci.com	cat. no.	-	Product - Customer Drw				sheet 2 of 2		A