

High Ohmic/High Voltage Metal Glaze Led Resistors



A metal glazed film is deposited on a high grade ceramic body. After a helical groove has been cut in the resistive layer, tinned electrolytic copper wires are welded to the end-caps. The resistors are coated with a light blue lacquer which provides electrical, mechanical, and climatic protection.

The encapsulation is resistant to all cleaning solvents in accordance with IEC 60068-2-45.

FEATURES

- Technology: Metal glaze
- $R_{max.} = 68 \text{ M}\Omega$; $U_{max.} = 10\,000 \text{ V}_{DC}$
- These resistors meet the safety requirements of:
 - UL1676 (510 k Ω to 11 M Ω); File No: E171160
 - IEC 60065, clause 14.1.a)
 - DIN EN 60065, clause 14.1.a)
 - VDE 0860, clause 14.1.a)
 - CQC, China
- High pulse loading capability (10 kV)
- Small size (0718)
- Pure tin plating provides compatibility with lead (Pb)-free and lead containing soldering processes
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

APPLICATIONS

- Where high resistance, high stability and high reliability at high voltage are required
- Safety component in combination with high voltage
- Picture tubes
- High voltage bleeders
- Cascade switches

TECHNICAL SPECIFICATIONS		
DESCRIPTION	UNIT	VR68
Resistance Range ⁽¹⁾	Ω	100K to 68M
Resistance Tolerance	%	± 1 ; ± 5
Resistance Series		± 1 %: E24/E96 series; ± 5 %: E24 series
Rated Dissipation, P_{70}	W	1
Thermal Resistance (R_{th})	K/W	70
Temperature Coefficient	ppm/K	$\leq \pm 200$
Maximum Permissible Voltage $U_{max.}$:		
DC	V	10 000
RMS		7000
Dielectric Withstanding Voltage of the Insulation for 1 Min	V	700
Basic Specifications		IEC 60115
Safety Requirements		UL1676 (510 k Ω to 11 M Ω); DIN EN 60065, IEC 60065 clause 14.1.a); VDE 0860, clause 14.1.a), CQC
Climatic Category (IEC 60068-1)		55/155/56
Max. Resistance Change for Resistance Range, $\Delta R_{max.}$, after:		
Load (1000 h, P_{70})		$\pm (1.5 \% R + 0.1 \Omega)$
Long Term Damp Heat Test (56 Days)		$\pm (1.5 \% R + 0.1 \Omega)$
Soldering (10 s, 260 °C)		$\pm (0.5 \% R + 0.1 \Omega)$
Noise	$\mu V/V$	max. 2.5

Note


⁽¹⁾ Ohmic values (other than resistance range) are available on request

PART NUMBER																	
PART NUMBER: VR68000001503JAC00																	
V	R	6	8	0	0	0	0	0	1	5	0	3	J	A	C	0	0
MODEL/SIZE	VARIANT			TCR/MATERIAL			VALUE			TOLERANCE		PACKAGING ⁽¹⁾		SPECIAL			
VR68000	0 = Neutral Z = Value overflow (special)			0 = Standard			3 digit value 1 digit multiplier MULTIPLIER 3 = *10 ³ 4 = *10 ⁴ 5 = *10 ⁵			F = ± 1 % J = ± 5 %		AC RD		The 2 digits are used for all special parts. 00 = Standard			
PRODUCT DESCRIPTION: VR68 5 % AC 150K																	
VR68					5 %						AC					150K	
MODEL/SIZE					TOLERANCE						PACKAGING ⁽¹⁾					RESISTANCE VALUE	
VR68					± 1 % ± 5 %						AC RD					150K = 150 kΩ 8M2 = 8.2 MΩ	

Notes

- The PART NUMBER is shown to facilitate the introduction of a unified part numbering system for ordering products
- ⁽¹⁾ Please refer to table PACKAGING

PACKAGING					
MODEL	TAPING	AMMOPACK		REEL	
		PIECES	CODE	PIECES	CODE
VR68	Axial, 66 mm	500	AC	750	RD

DIMENSIONS


DIMENSIONS - Resistor type and relevant physical dimensions				
TYPE	Ø D _{max.}	L ₁ max.	L ₂ max.	Ø d
VR68	6.8	18.0	19.0	0.78 ± 0.05

MASS PER UNIT	
TYPE	MASS (mg)
VR68	1690

MARKING

The nominal resistance and tolerance are marked on the resistor using four or five colored bands in accordance with IEC 60062, marking codes for resistors and capacitors.

Yellow and grey are used instead of gold and silver because metal particles in the lacquer could affect high-voltage properties.

**OUTLINES**

The length of the body (L_1) is measured by inserting the leads into holes of two identical gauge plates and moving

these plates parallel to each other until the resistor body is clamped without deformation (IEC 60294).

FUNCTIONAL PERFORMANCE**PRODUCT CHARACTERIZATION**

Standard values of nominal resistance are taken from the E96/E24/E12 series for resistors with a tolerance of $\pm 1\%$,

or 5 %. The values of the E96/E24 series are in accordance with IEC 60063.


LIMITING VALUES			
TYPE	LIMITING VOLTAGE ⁽¹⁾ $U_{max.}$		LIMITING POWER P_{70} (W)
	DC	RMS	
VR68	10 000	7000	1.0

Notes


- The maximum permissible hot-spot temperature is 155 °C
- ⁽¹⁾ The maximum voltage that may be continuously applied to the resistor element, see IEC 60115-1

DERATING

The power that the resistor can dissipate depends on the operating temperature.




Maximum dissipation ($P_{max.}$) in percentage of rated power as a function of the ambient temperature (T_{amb})


PULSE LOADING CAPABILITY

Maximum allowed peak pulse voltage in accordance with IEC 60065, 14.1.a); 50 discharges from a 1 nF capacitor charged to $\hat{U}_{max.}$; 12 discharges/min (drift $\Delta R/R \leq 2\%$)

APPLICATION INFORMATION



Hot-spot temperature rise (ΔT) as a function of dissipated power



Temperature rise (ΔT) at the lead end (soldering point) as a function of dissipated power at various lead lengths after mounting

TESTS AND REQUIREMENTS

Essentially all tests are carried out in accordance with IEC 60115-1 specification, category LCT/UCT/56 (rated temperature range: Lower Category Temperature, Upper Category Temperature; damp heat, steady state, test duration: 56 days).

The tests are carried out in accordance with IEC 60068-2-xx. Test method under standard atmospheric conditions according to IEC 60068-1, 5.3.

In the Test Procedures and Requirements table the test and requirements are listed with reference to the relevant clauses of IEC 60115-1 and IEC 60068-2-xx test methods. A short description of the test procedure is also given. In some instances deviations from the IEC recommendations were necessary for our method of specifying.

All soldering tests are performed with mildly activated flux.

TEST PROCEDURES AND REQUIREMENTS				
IEC 60115-1 CLAUSE	IEC 60068-2-TEST METHOD	TEST	PROCEDURE	REQUIREMENTS
4.16		Robustness of terminations:		
4.16.2	21 (Ua1)	Tensile all samples	Ø 0.8 mm; load 10 N; 10 s	Number of failures < 10 x 10 ⁻⁶
4.16.3	21 (Ub)	Bending half number of samples	Ø 0.8 mm; load 5 N; 4 x 90°	Number of failures < 10 x 10 ⁻⁶
4.16.4	21 (Uc)	Torsion other half of samples	3 x 360° in opposite directions	No damage ΔR max.: ± (0.5 % R + 0.05 Ω)
4.17	20 (Ta)	Solderability	2 s; 235 °C: Solder bath method; SnPb40 3 s; 245 °C: Solder bath method; SnAg3Cu0.5	Good tinning (≥ 95 % covered); no damage
		Solderability (after aging)	8 h steam or 16 h 155 °C; leads immersed 6 mm; for 2 s at 235 °C; solder bath (SnPb40) for 3 s at 245 °C; solder bath (SnAg3Cu0.5) method	Good tinning (≥ 95 % covered); no damage
4.18	20 (Tb)	Resistance to soldering heat	Thermal shock: 10 s; 260 °C; 3 mm from body	ΔR max.: ± (0.5 % R + 0.05 Ω)
4.19	14 (Na)	Rapid change of temperature	30 min at - 55 °C and 30 min at + 155 °C; 5 cycles	ΔR max.: ± (0.5 % R + 0.05 Ω)

TEST PROCEDURES AND REQUIREMENTS

IEC 60115-1 CLAUSE	IEC 60068-2- TEST METHOD	TEST	PROCEDURE	REQUIREMENTS
4.20	29 (Eb)	Bump	3 x 1500 bumps in 3 directions; 40 g	No damage $\Delta R \text{ max.: } \pm (0.5 \% R + 0.05 \Omega)$
4.22	6 (Fc)	Vibration	Frequency 10 Hz to 500 Hz; displacement 1.5 mm or acceleration 10 g; 3 directions; total 6 h (3 x 2 h)	No damage $\Delta R \text{ max.: } \pm (0.5 \% R + 0.05 \Omega)$
4.23	2 (Ba) 30 (Db) 1 (Aa) 13 (M)	Climatic sequence:		
4.23.2		Dry heat	16 h; 155 °C	
4.23.3		Damp heat (accelerated) 1 st cycle	24 h; 55 °C; 90 % to 100 % RH	$\Delta R_{\text{ins min.: } 10^3 \text{ M}\Omega$ $\Delta R \text{ max.: } \pm (1.5 \% R + 0.1 \Omega)$
4.23.4		Cold	2 h; - 55 °C	
4.23.5		Low air pressure	2 h; 8.5 kPa; 15 °C to 35 °C	
4.24	78 (Cab)	Damp heat (steady state)	56 days; 40 °C; 90 % to 95 % RH; dissipation 0.01 P_{70} ; limiting voltage $U = 100 V_{DC}$	$\Delta R \text{ max.: } \pm (1.5 \% R + 0.1 \Omega)$
4.25.1		Endurance	1000 h at 70 °C; P_{70} or U_{max}	$\Delta R \text{ max.: } \pm (1.5 \% R + 0.1 \Omega)$
4.8		Temperature coefficient	Between - 55 °C and + 155 °C	$\leq \pm 200 \text{ ppm/K}$
4.7		Voltage proof on insulation	$U_{\text{RMS}} = 700 \text{ V}$ during 1 min; V-block method	No breakdown
4.12		Noise	IEC 60195	Max. 2.5 $\mu\text{V/V}$
4.6.1.1		Insulation resistance	$U = 500 V_{DC}$ during 1 min; V-block method	$R_{\text{ins min.: } 10^4 \text{ M}\Omega$
4.13		Short time overload	Room temperature; dissipation 6.25 x P_{70} (voltage not more than 2 x limiting voltage; 10 000 V max.); 10 cycles; 5 s ON and 45 s OFF	$\Delta R \text{ max.: } \pm (2.0 \% R + 0.05 \Omega)$

12NC INFORMATION FOR HISTORICAL CODING REFERENCE

- The resistors have a 12-digit numeric code starting with 2322 244
- The subsequent:
First digit for 1 % tolerance products (E24 and E96 series) or 2 digits for 5 % (E24 series) indicate the resistor type and packing.
- The remaining digits indicate the resistance value:
 - The first 3 digits for 1 % or 2 digits for 5 % tolerance products indicate the resistance value.
 - The last digit indicates the resistance decade.

Last Digit of 12NC Indicating Resistance Decade

RESISTANCE DECADE	LAST DIGIT
100 k Ω to 976 k Ω	4
1 M Ω to 9.76 M Ω	5
$\geq 10 \text{ M}\Omega$	6

12NC Example

The 12NC for a VR68, resistor value 7.5 M Ω , 5 % tolerance, supplied on a bandolier of 500 units in ammpack, is: 2322 244 13755.

12NC - Resistor type and packaging

TYPE	TAPE WIDTH (mm)	TOL. (%)	2322 244	
			BANDOLIER IN AMMOPACK	BANDOLIER ON REEL
			500 UNITS	750 UNITS
VR68	66.7	± 1	8....	6....
		± 5	13...	23...



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.