

1 2 3 4 5 6 7 8

REV	ZONE	ECO	DESCRIPTION	DATE	BY	APPR
01	--	--	RELEASE NUMBER	15-JAN-10	--	--

A

A


B

B

C

C

Contact Orientation On Reel
For Auto Crimp Machine



D

General specification:


1. Suitable pin diameter: 2.5mm
2. Current rating: 23A
3. Termination type: crimp
4. Crimp wire range: 2.5mm²~3.0mm²
5. Plating Specification: See Below

1. When XX=T Tin over Nickel
2. When XX=F Gold flash plate overall.
3. When XX=G10 Contact plating 10u"Gold.
4. When XX=G30 Contact plating 30u"Gold.

6. Material Specification: See Below

- 6.1. Contact Body: Copper Alloy

- 6.2. Outer Spring: Stainless Steel



E

E

F

1 2 3 4 5 6 7 8

UNLESS OTHERWISE SPECIFIED		MATERIAL SPECIFICATIONS:		SINE Systems Corporation	
1) All dimensions are in metric(mm).		A Subsidiary of Amphenol Corporation			
2) Tolerances are as follows:					
1 PL DEC ±0.30					
2 PL DEC ±0.15					
3 PL DEC ±0.10					
Fractions ±1/64					
Angles ±1°					
签 名 SIGNATURE		日期 DATE		THIS DRAWING IS SUPPLIED FOR INFORMATION	
制图 DRAWN		TOM		ONLY DESIGN FEATURES, SPECIFICATIONS AND	
审核 CHECKED		POER		PERFORMANCE DATA SHOWN HEREON ARE THE	
I. 艺 ENGINEER		15-JAN-10		PROPERTY OF THE AMPHENOL CORPORATION.	
批准 APPROVAL		FOUNI		NO RIGHTS OF REPRODUCTION ARE IMPLIED.	
客户 CUSTOMER		DENR		ALL DIMENSIONS ARE SUBJECT TO NORMAL	
MANUFACTURING VARIATIONS.					
SHEET NO. 1 OF 1		NEXT ASSY:			
F		N.W. ASSY			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SS12A1T](#)