




- 1 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 2 CONTINUOUS STRIP ON REELS.
- 3 THIS DIMENSIONS MUST BE MAINTAINED FOR
PROPER FUNCTION OF THE LATCHING MECHANISM.
- 4 TO BE REELED WITH INTERLEAVING PAPER




VIEW A—A



SECTION B-B

SECTION C-C

- 1 MATL: #2 HARD BRASS OR NICKEL PLATED STEEL.
- 2 NO BURRS PERMISSIBLE AT HOLE.
- 3 TIN PLATING IS REQUIRED ON BRASS WHEN
TERMINAL TEMPATURE IS OVER 225°F
- 4 MUST BE FLAT WITHIN 0.076 [.003] OVER
THIS LENGTH.
- 5 HOLE MUST BE SYMMETRICAL ABOUT TAB C
WITHIN 0.076 [.003].
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.

2.29 — 3.30 [.090 — .130]		0.5 — 1.4mm ² [20 — 16]		 63313-1	
INSULATION RANGE		WIRE SIZE		PART NO.	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 5/27/87 JR RUTH CHK 6/2/87 G YETTER APVD 6/2/87 R KUZO PRODUCT SPEC — APPLICATION SPEC —		 TE Connectivity RECEPTACLE, POSITIVE LOCK, .187 SERIES —	
DIMENSIONS: mm [INCHES] 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.25 .010 4 PLC ± — ANGLES ± —	SIZE A2	GAGE CODE 00779	DRAWING NO C-63313	RESTRICTED TO —
MATERIAL BRASS	FINISH TIN	WEIGHT 0.000000		SCALE 1:1 SHEET 1 of 1 REV E1	
		CUSTOMER DRAWING			