

# FDMC8878 N-Channel Power Trench® MOSFET 30V, 16.5A, 14mΩ

## Features

- Max  $r_{DS(on)}$  = 14mΩ at  $V_{GS}$  = 10V,  $I_D$  = 9.6A
- Max  $r_{DS(on)}$  = 17mΩ at  $V_{GS}$  = 4.5V,  $I_D$  = 8.7A
- Low Profile - 0.8 mm max in MLP 3.3X3.3
- RoHS Compliant





## General Description

This N-Channel MOSFET is a rugged gate version of Fairchild Semiconductor's advanced Power Trench process. It has been optimized for power management applications.

## Application

- DC - DC Conversion



## MOSFET Maximum Ratings $T_A = 25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Ratings	Units
$V_{DS}$	Drain to Source Voltage	30	V
$V_{GS}$	Gate to Source Voltage	$\pm 20$	V
$I_D$	Drain Current -Continuous (Package limited) $T_C = 25^\circ\text{C}$	16.5	A
	-Continuous (Silicon limited) $T_C = 25^\circ\text{C}$	38	
	-Continuous $T_A = 25^\circ\text{C}$ (Note 1a)	9.6	
	-Pulsed	60	
$P_D$	Power Dissipation $T_C = 25^\circ\text{C}$	31	W
	Power Dissipation $T_A = 25^\circ\text{C}$ (Note 1a)	2.1	
$T_J, T_{STG}$	Operating and Storage Junction Temperature Range	-55 to +150	$^\circ\text{C}$

## Thermal Characteristics

$R_{\theta JC}$	Thermal Resistance, Junction to Case	4	$^\circ\text{C/W}$
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Note 1a)	60	

## Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FDMC8878	FDMC8878	MLP 3.3X3.3	13"	12 mm	3000 units

**Electrical Characteristics**  $T_J = 25^\circ\text{C}$  unless otherwise noted

Symbol	Parameter	Test Conditions	Min	Typ	Max	Units
--------	-----------	-----------------	-----	-----	-----	-------

**Off Characteristics**

$BV_{DSS}$	Drain to Source Breakdown Voltage	$I_D = 250\mu\text{A}$ , $V_{GS} = 0\text{V}$	30			V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	$I_D = 250\mu\text{A}$ , referenced to $25^\circ\text{C}$		20		mV/ $^\circ\text{C}$
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS} = 24\text{V}$ , $V_{GS} = 0\text{V}$ $T_J = 125^\circ\text{C}$			1 100	$\mu\text{A}$
$I_{GSS}$	Gate to Source Leakage Current	$V_{GS} = \pm 20\text{V}$ , $V_{DS} = 0\text{V}$			$\pm 100$	nA

**On Characteristics**

$V_{GS(th)}$	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}$ , $I_D = 250\mu\text{A}$	1	1.7	3	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	$I_D = 250\mu\text{A}$ , referenced to $25^\circ\text{C}$		-5.7		mV/ $^\circ\text{C}$
$r_{DS(on)}$	Drain to Source On Resistance	$V_{GS} = 10\text{V}$ , $I_D = 9.6\text{A}$		9.6	14.0	m $\Omega$
		$V_{GS} = 4.5\text{V}$ , $I_D = 8.7\text{A}$		12.1	17.0	
		$V_{GS} = 10\text{V}$ , $I_D = 9.6\text{A}$ , $T_J = 125^\circ\text{C}$		13.5	20.0	
$g_{FS}$	Forward Transconductance	$V_{DS} = 5\text{V}$ , $I_D = 9.6\text{A}$		35		S

**Dynamic Characteristics**

$C_{iss}$	Input Capacitance	$V_{DS} = 15\text{V}$ , $V_{GS} = 0\text{V}$ , $f = 1\text{MHz}$		1000	1230	pF
$C_{oss}$	Output Capacitance			183	255	pF
$C_{rss}$	Reverse Transfer Capacitance			118	180	pF
$R_g$	Gate Resistance	$f = 1\text{MHz}$		1.1		$\Omega$

**Switching Characteristics**


$t_{d(on)}$	Turn-On Delay Time	$V_{DD} = 15\text{V}$ , $I_D = 9.6\text{A}$ $V_{GS} = 10\text{V}$ , $R_{GEN} = 6\Omega$		8	16	ns
$t_r$	Rise Time			4	10	ns
$t_{d(off)}$	Turn-Off Delay Time			20	36	ns
$t_f$	Fall Time			3	10	ns
$Q_{g(TOT)}$	Total Gate Charge	$V_{GS} = 10\text{V}$ , $V_{DD} = 15\text{V}$ , $I_D = 9.6\text{A}$		18	26	nC
$Q_{gs}$	Gate to Source Gate Charge			2.8		nC
$Q_{gd}$	Gate to Drain "Miller" Charge			3.9		nC

**Drain-Source Diode Characteristics**

$V_{SD}$	Source to Drain Diode Forward Voltage	$V_{GS} = 0\text{V}$ , $I_S = 9.6\text{A}$ (Note 2)		0.8	1.2	V
$t_{rr}$	Reverse Recovery Time	$I_F = 9.6\text{A}$ , $di/dt = 100\text{A}/\mu\text{s}$		23	35	ns
$Q_{rr}$	Reverse Recovery Charge			14	21	nC

**Notes:**

1:  $R_{\theta JA}$  is determined with the device mounted on a 1in<sup>2</sup> pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material.  $R_{\theta JC}$  is guaranteed by design while  $R_{\theta CA}$  is determined by the user's board design.



a.  $60^\circ\text{C}/\text{W}$  when mounted on a 1 in<sup>2</sup> pad of 2 oz copper



b.  $135^\circ\text{C}/\text{W}$  when mounted on a minimum pad of 2 oz copper

2: Pulse Test: Pulse Width < 300 $\mu\text{s}$ , Duty cycle < 2.0%.

## Typical Characteristics $T_J = 25^\circ\text{C}$ unless otherwise noted




Figure 1. On-Region Characteristics




Figure 2. Normalized On-Resistance vs Drain Current and Gate Voltage




Figure 3. Normalized On-Resistance vs Junction Temperature




Figure 4. On-Resistance vs Gate to Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source to Drain Diode Forward Voltage vs Source Current

## Typical Characteristics $T_J = 25^\circ\text{C}$ unless otherwise noted




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs Drain to Source Voltage




Figure 9. Unclamped Inductive Switching Capability




Figure 10. Maximum Continuous Drain Current vs Ambient Temperature




Figure 11. Forward Bias Safe Operating Area




Figure 12. Single Pulse Maximum Power Dissipation

# Typical Characteristics $T_J = 25^\circ\text{C}$ unless otherwise noted








Figure 13. Transient Thermal Response Curve

# Dimensional Outline and Pad Layout





## NOTES:

- A. EXCEPT AS NOTED, PACKAGE CONFORMS TO JEDEC REGISTRATION MO-240 VARIATION BA..
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 1994.
- D. SEATING PLANE IS DEFINED BY TERMINAL TIPS ONLY
- E. BODY DIMENSIONS DO NOT INCLUDE MOLD FLASH PROTRUSIONS NOR GATE BURRS.
- F. FLANGE DIMENSIONS INCLUDE INTERTERMINAL FLASH OR PROTRUSION. INTERTERMINAL FLASH OR PROTRUSION SHALL NOT EXCEED 0.25MM PER SIDE.
- G. IT IS RECOMMENDED TO HAVE NO TRACES OR VIA WITHIN THE KEEP OUT AREA.
- H. DRAWING FILENAME: MKT-MLP08Trev3.
- I. GENERAL RADII FOR ALL CORNERS SHALL BE 0.20MM MAX.
- J. FAIRCHILD SEMICONDUCTOR.

## TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

AccuPower <sup>™</sup>	F-PFST <sup>™</sup>	PowerTrench <sup>®</sup>	Sync-Lock <sup>™</sup>
AX-CAP <sup>®</sup> *	FRFET <sup>®</sup>	PowerXS <sup>™</sup>	SYSTEM <sup>®</sup> *
BitSiC <sup>™</sup>	Global Power Resource <sup>SM</sup>	Programmable Active Droop <sup>™</sup>	TinyBoost <sup>®</sup>
Build it Now <sup>™</sup>	GreenBridge <sup>™</sup>	QFET <sup>®</sup>	TinyBuck <sup>®</sup>
CorePLUS <sup>™</sup>	Green FPS <sup>™</sup>	QS <sup>™</sup>	TinyCalc <sup>™</sup>
CorePOWER <sup>™</sup>	Green FPS <sup>™</sup> e-Series <sup>™</sup>	Quiet Series <sup>™</sup>	TinyLogic <sup>®</sup>
CROSSVOLT <sup>™</sup>	Gmax <sup>™</sup>	RapidConfigure <sup>™</sup>	TINYOPTO <sup>™</sup>
CTL <sup>™</sup>	GTO <sup>™</sup>	Saving our world, 1mW/W/kW at a time <sup>™</sup>	TinyPower <sup>™</sup>
Current Transfer Logic <sup>™</sup>	IntelliMAX <sup>™</sup>	SignalWise <sup>™</sup>	TinyPWM <sup>™</sup>
DEUXPEED <sup>®</sup>	ISOPLANAR <sup>™</sup>	SmartMax <sup>™</sup>	TinyWire <sup>™</sup>
Dual Cool <sup>™</sup>	Marking Small Speakers Sound Louder and Better <sup>™</sup>	SMART START <sup>™</sup>	TransiC <sup>™</sup>
EcoSPARK <sup>®</sup>	MegaBuck <sup>™</sup>	Solutions for Your Success <sup>™</sup>	TriFault Detect <sup>™</sup>
EfficientMax <sup>™</sup>	MICROCOUPLER <sup>™</sup>	SPM <sup>®</sup>	TRUECURRENT <sup>®</sup> *
ESBC <sup>™</sup>	MicroFET <sup>™</sup>	STEALTH <sup>™</sup>	μSerDes <sup>™</sup>
	MicroPak <sup>™</sup>	SuperFET <sup>®</sup>	
Fairchild <sup>®</sup>	MicroPak2 <sup>™</sup>	SuperSOT <sup>™</sup> -3	UHC <sup>®</sup>
Fairchild Semiconductor <sup>®</sup>	MillerDrive <sup>™</sup>	SuperSOT <sup>™</sup> -6	Ultra FRFET <sup>™</sup>
FACT Quiet Series <sup>™</sup>	MotionMax <sup>™</sup>	SuperSOT <sup>™</sup> -8	UniFET <sup>™</sup>
FACT <sup>®</sup>	mWSaver <sup>®</sup>	SupreMOS <sup>®</sup>	VCX <sup>™</sup>
FAST <sup>®</sup>	OptoHiT <sup>™</sup>	SynCFET <sup>™</sup>	VisualMax <sup>™</sup>
FastvCore <sup>™</sup>	OPTOLOGIC <sup>®</sup>		VoltagePlus <sup>™</sup>
FETBench <sup>™</sup>	OPTOPLANAR <sup>®</sup>		XST <sup>™</sup>
FPS <sup>™</sup>			

\*Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used here in:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

## ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, [www.fairchildsemi.com](http://www.fairchildsemi.com), under Sales Support. Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address and warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

## PRODUCT STATUS DEFINITIONS

### Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.

Rev. I66

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fairchild Semiconductor:

[FDMC8878](#) [FDMC8878\\_F126](#)