

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL INC.
FED.MFG.CODE 91929

ACTUATOR-SWITCH

CATALOG LISTING

JS-183

JS-183

M

DRAWING
NUMBER

5

ISSUE

REPLACES

RELEASE NO. PR-20038

CHECK

REVISIONS

A	PR-20038	T S M
	26 MAY 92	
B	CO-79303	J A K
	15 FEB 95	

CHECK

22 AUG 91



D A W

CHECK

S A V 21 AUG 91

DDM/CAD

DRAWN




NOTES

- ¹ FURNISHED UNASSEMBLED
- ² CHARACTERISTICS WITH 6HM1-1 BASIC SWITCH INSTALLED
- ³ ADJUSTMENT CAUTION: TO PREVENT SWITCH SEAL DAMAGE DO NOT ALLOW ACTUATOR LEAF TO COME IN CONTACT WITH HM LEVER
- ⁴ POSITION ADJUSTMENT OF BASIC SWITCH TO LEVER MAY BE REQUIRED TO ACHIEVE STATED TOLERANCE AT OPERATE POSITION

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS ²	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — — 9 OZ MAX	CONTACT ARRANGEMENT	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE — — — — 2 OZ MIN		ONE PLACE (.0) ±.030	
DIFFERENTIAL TRAVEL — — — .030 MAX		TWO PLACE (.00) ±.015	
OVERTRAVEL — — — — .030 MIN		THREE PLACE (.000) ±.005	
		ANGLES ±	
		RAW MATERIAL—COMMERCIAL STANDARD	
		WEIGHT	