

PLUGSERIES PRS 120VAC LD 2CO AU

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com



High power/currents can be safely switched with the PLUGSERIES. The modular system enables conventional relays and LED indicators simply to be plugged in. Retaining and disassembly clips provide a secure mount. Pre-assembled relays with 1 or 2 changeover contacts and input voltages from 24V to 230V round of the product range. Plug-in ZQV 2.5 cross-connectors enable relay multiplexers to be set up quickly thanks to simple side-by-side mounting.

General ordering data

Order No.	8595960000
Part designation	PRS 120VAC LD 2CO AU
Version	PLUGSERIES, Relays, No. of contacts: 2, CO contact, Rated control voltage: 120 V AC $\pm 10\%$, Screw connection
GTIN (EAN)	4032248254903
Qty.	10 pc(s).

PLUGSERIES PRS 120VAC LD 2CO AU

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Dimensions

Length	92 mm	Width	15.3 mm
Height	95 mm		

Temperature

Ambient temperature (operational)	-40 °C...+50 °C	Storage temperature	-40 °C...+85 °C
-----------------------------------	-----------------	---------------------	-----------------

Input

Rated voltage	300 V AC _{eff}	Rated control voltage	120 V AC ±10 %
Response / drop-out voltage AC coil	53 V / 49 V	Rated current AC	9.1 mA
Power rating	1.1 VA	Status indicator	Green LED

Output

Continuous current	2 x 8 A	Max. switching current	16 A
Max. switching frequency at rated load	0.1 Hz	Sparkover time / Drop-out time	7.8 ms / 41.5 ms
Switch-off delay	<45ms	Switch-on delay	9 ms
Switching voltage AC, max.	250 V	making current	2 x 8 A
max. switching capacity	2x2 kVA	min. switching capacity	1 V / 1 mA

Contact data

Contact design	CO contact	No. of contacts	2
Contact material	AgNi 5µm Au	Mechanical service life	5 x 10 ⁶ switching cycles

Rated data

Conductor connection system	Screw connection	DIN Rail compatibility	TS 35
Flammability class UL 94	V-0	Humidity	40°C / 93% rel. humidity, no condensation
Solid, max.	2.5 mm ²		

Insulation coordination (EN 50 178)

Clearance and creepage distances for control/load side	> 8 mm	Impulse withstand voltage	6 kV
Overvoltage category	III	Pollution severity	2
Protection class	IP 20	Protective separation acc. to VDE 0106 part 101	Yes

Other technical data

Free-wheel diode	No	Reverse polarity protection	No
Status indicator	Green LED	Version	Relay coupler

Approvals

Approvals institutes	CURUS; GOSTME25; CE
----------------------	---------------------

Classifications

ETIM 2.0	EC001437	ETIM 3.0	EC001437
eClass 5.1	27-37-16-01	eClass 6.0	27-37-16-01

PLUGSERIES PRS 120VAC LD 2CO AU

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Notes

Note, technical data

Cross-connectors and markers - refer to PLUGSERIES accessories

PLUGSERIES PRS 120VAC LD 2CO AU

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Drawings

Electric symbol

