


 1. RECOMMENDED SPARE PARTS.

2. GREASE RAM, CAM, CAM FOLLOWER AND FEED ROD LIGHTLY.

3. LUBRICATE DAILY PER THE APPLICATOR INSTRUCTION SHEET SUPPLIED WITH THE APPLICATOR.



GUIDE OFF
INSULATION BARREL

DIMENSIONS: mm [INCHES]		MATL		HT TR		FIN	
DO NOT SCALE PRINT.		-		-		-	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		DR 120CT00		APP 120CT00		 AMP Incorporated Harrisburg, PA 17105-3508	
1 PLC DEC ±0.5 [0.02 IN]		M. CLIFFORD		F. BACKHURST			
2 PLC DEC ±		CHK 08-11-00		REL 08-11-00			
3 PLC DEC ±		M. CLIFFORD		M. CLIFFORD			
ANGLES -							
SURF TEXTURE: ☒		NAME SIDE FEED HD-1 APPLICATOR					
REMOVE BURRS, BREAK SHARP EDGES R0.38 MAX		SCALE -		D		DWG NO 1426095	
						SHEET 1 OF 1	
						REV D	

	-	1	1	1	1	1	1	1426095	PRINT, APPLICATOR LOG SHEET	73
	-	1	1	1	1	1	1	1338705-1	DOCUMENTATION PACKAGE	72
										71
										70
										69
										68
	-	1	1	1	1	1	1	461264-1	PLATE, IDENTIFICATION	67
	-	2	2	2	2	2	2	21017-2	SCR,DRIVE (#2x.19) ID PLATE	66
										65
	-	1	1	1	1	1	1	986950-1	WASHER, FLAT PRECISION	64
	-	1	1	1	1	1	1	3-18031-0	SCR,SKT SET(M6X6)RAM	63
	-	1	1	1	1	1	1	18023-9	SCR,SHC (M4X6) INS DISC	62
	-	2	2	2	2	2	2	2-18032-5	SCR,SET (M5X20)DRAG	61
	-	1	1	1	1	1	1	18024-7	SCR,BHC (M4X10) ANVIL	60
	-	1	1	1	1	1	1	5-18022-2	SCR,HEX (M4X8)FEED FINGER	59
										58
										57
	-	1	1	1	1	1	1	1338685-1	PAWL, FEED	56
	-	1	-	-	1	-	-	1338723-1	HOLDER,SHEAR, REAR (NO CUT)	55
	-	4	4	4	4	4	4	18024-8	SCR,BHC (M4x12)SHEAR HOLDER	54
	-	2	2	2	2	2	2	1-18023-3	SCR,SHC (M4x16)TERM HLD DWN	53
										52
										51
										50
	-	1	1	1	1	1	1	18024-3	SCR,BHC (M3X10)CAM	49
	-	-	1	-	-	1	-	1338675-1	CAM, PRE FEED 30 & 40 mm ST	48
	-	1	-	1	1	-	1	1338676-1	CAM, POST FEED 30 & 40 mm ST	47
	-	1	1	1	1	1	1	1320999-3	APPLICATOR BASIC SUBASSY	46
	-	1	1	1	1	1	1	690191-1	PLUG, NYLON	45
	-	1	1	1	1	1	1	1338660-1	RAM	44
	-	1	1	1	1	1	1	690125-1	WASHER, LAMINATED	43
	-	1	1	1	1	1	1	690124-1	WASHER, RAM	42
	-	1	1	1	1	1	1	2-18024-6	SCR,BHC (M8X25)RAM	41
	-	1	1	1	1	1	1	23241-1	BALL, STEEL	40
	-	1	1	1	1	1	1	2-22278-7	SPRING, COMPRESSION	39
	-	1	1	1	1	1	1	1320922-1	DISC, INSULATION	38
	-	1	1	1	1	1	1	354777-1	WIRE DISC, PLASTIC	37
	-	1	1	1	1	1	1	22480-5	WASHER, SPRING	36
	-	1	1	1	1	1	1	690212-1	POST, RAM	35
										34
	-	2	2	2	2	2	2	1-18024-0	SCR,BHC (M4X20)STRIP GUIDE	33
	-	1	1	1	1	1	1	18027-2	WASHER, FLAT (M4)	32
	-	1	1	1	1	1	1	1-18023-2	SCR,SKT CAP (M4X12)MOUNT BLOCK	31
	-	1	1	1	1	1	1	1320908-9	SPACER, STRIP GUIDE	30
	-	1	1	1	1	1	1	1633073-1	STRIP GUIDE PLATE ASSY	29
										28
	-	2	2	2	2	2	2	1-22284-0	SPRING, DRAG	27
	-	1	1	1	1	1	1	356835-1	LEVER, DRAG RELEASE	26
	-	1	1	1	1	1	1	240792-1	DRAG, TERMINAL	25
	-	1	1	1	1	1	1	1320928-1	PLATE, STRIP GUIDE	24
	-	1	1	1	1	1	1	980371-4	SCR,SHC SHLD	23
	-	1	-	1	1	-	1	690472-2	STRIPPER	22
	-	1	1	1	1	1	1	1-18023-1	SCR,SHC (M4X10)STRIPPER	21
	-	4	4	4	4	4	4	18025-2	WASHER,LOCK (M4)STRIPPER	20
	-	-	1	-	-	1	-	690472-1	STRIPPER	19
	-	1	1	1	1	1	1	690518-1	HOLDER, TERMINAL	18
	-	1	-	-	1	-	-	1338684-1	HOLDER, SHEAR, FRONT (NO-CUT)	17
	-	2	2	2	2	2	2	18023-2	SCR,SHC (M3X6)REAR SHEAR PL	16
	-	1	1	1	1	1	1	1-690464-0	PLATE, SHEAR (SHEAR)	15
	-	-	1	1	-	1	1	1320920-1	HOLDER, SHEAR, REAR (CUT)	14
	-	1	1	1	1	1	1	1-690463-1	SHEAR, FLOAT (REAR)	13
	-	2	2	2	2	2	2	3-22280-3	SPRING, SHEAR	12
	-	2	2	2	2	2	2	356885-4	STOP, SHEAR	11
	-	-	1	1	-	1	1	1320921-1	HOLDER, SHEAR, FRONT (CUT)	10
	-	1	1	1	1	1	1	462006-1	SHEAR, FLOAT (FRONT)	9
	1	2	2	2	1	1	1	1333200-7	ANVIL	8
	-	1	1	1	1	1	1	3-240641-0	SPACER, DEPRESSOR (REAR)	7
	-	1	1	1	1	1	1	690468-2	DEPRESSOR, SHEAR (REAR)	6
	-	1	1	1	1	1	1	2-455889-9	DEPRESSOR, SHEAR (FRONT)	5
	-	1	1	1	1	1	1	238011-7	SPACER, BLOCK CRIMPER	4
	1	2	2	2	1	1	1	5-683454-4	CRIMPER, INSULATION	3
	-	1	1	1	1	1	1	455888-4	SPACER, CRIMPER	2
	1	2	2	2	1	1	1	456400-9	CRIMPER, WIRE	1
-77	-76	-72	-71	-6	-2	-1		PART NO	DESCRIPTION	ITEM NO
←								REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)		
								PARTS LIST		
QTY								READ PER ASSY		