



Bestell-Nr. Part No.	Farbe Colour	V _{OP} +10% (VAC)	I _{OP} typ. (mA)	I _V typ. (mcd)	Elektrische und optische Daten sind bei T _U = 25°C gemessen. Electrical and optical data are measured at T _A = 25°C.
1957*130	Rot / Red	130	6	45	
1957*131	Grün / Green	130	6	30	
1957*132	Gelb / Yellow	130	6	80	
1957*133	U-rot / U-red	130	6	70	
1957*136	U-gelb / U-yellow	130	6	175	
1957*137	Blau / Blue	130	6	100	
1957*230	Rot / Red	230	4	28	
1957*231	Grün / Green	230	4	20	
1957*232	Gelb / Yellow	230	4	48	
1957*233	U-rot / U-red	230	4	42	
1957*236	U-gelb / U-yellow	230	4	105	
1957*237	Blau / Blue	230	4	46	
Umgebungstemperatur (T _U) : -25°C - +60°C Lagertemperatur (T _{STG}) : -25°C - +85°C max. Schleiflast : 200mA					Ambient temperature (T _A) : -25°C - +60°C Storage temperature (T _{STG}) : -25°C - +85°C max. loop current : 200mA
SCHUTZART: IP 67 nach DIN EN 60529 Frontseitig zwischen LED und Gehäuse, sowie zwischen Gehäuse und Frontplatte bei Verwendung des mitgelieferten Dichtringes. * Die Signalleuchte kann mit Glanzchrom oder Schwarzchrom geliefert werden. Die 5. Stelle der Bestellnummer wird mit 0 oder 1 codiert. Glanzchrom = 0 Schwarzchrom = 1 Beispiel: 19570130 Rot mit Glanzchrom 19571130 Rot mit Schwarzchrom					DEGREE OF PROTECTION: IP 67 in accordance to DIN EN 60529 Gap between LED and bezel and gap between bezel and frontplate sealed to IP 67 when using the supplied gasket. * The LED indicator can be delivered in bright or black chrome reflector. The 5. digit has to be coded with 0 or 1. Bright chrome = 0 Black chrome = 1 Example: 19570130 Red with bright chrome 19571130 Red with black chrome
ACHTUNG: Hinweise zur Anwendung, s. Kundeninformation 97.001a					ATTENTION: Instruction for application, s. customer information 97.001a
LED Signalleuchten mit anderen Spannungen auf Anfrage Technische Änderungen vorbehalten					LED Indicators with other voltages upon request Specification subject to change without notice



Hinweise zur Anwendung Instruction for application



Anschluß:

Die Anzeigen mit Flachsteckanschlüssen sind **nicht** für Lötanschluß geeignet.

Chemikalienbeständigkeit:

Der Kunststoff (Polycarbonat) ist nur bedingt chemikalienbeständig.
Weitere Angaben auf Anfrage.

Die Auswahl und der technisch richtige Einbau unserer Produkte nach den entsprechenden Vorschriften (z.B. VDE 0100 und VDE 0160), obliegen dem Anwender.

Connection:

The indicators with tabconnection are **not** qualified for soldering.

Resistancy against chemicals

The plastic (polycarbonate) is limited resistant against chemicals.
Further information upon request.

The selection and technical correct installation of our products, conforming for the relevant standards (e.g. VDE 0100 and VDE 0160) is incumbent on the user.