




1. THIS PART CONFORMS TO REQUIREMENTS FOR DANIELS CRIMP TOOL NO. M300-BT, WITH DANIELS POSITIONER PART NO. SP689, STRIP LENGTH .375, #8 AWG SETTING 7, #10 AWG SETTING 6.
2. MATES WITH 211159-1 IN AMPLIMITE CONNECTOR ASSEMBLIES ONLY.
- A3 FINISH: PLATED GOLD .000050 [0.00127] MIN THK PER ASTM-B-488 OVER NICKEL .000050 [0.00127] MIN THK PER AMS-QQ-N-290.
- A4 FINISH: PLATED GOLD .000030 [0.00076] MIN THK PER ASTM-B-488 OVER NICKEL .000050 [0.00127] MIN THK PER AMS-QQ-N-290.
- A5 RING GAGE MUST BE USED TO CHECK THE ϕ .203-.212 DIMENSION.
- A6 RESTRICTED PART NUMBER.

PRELIMINARY NOT RELEASED FOR PRODUCTION	A6				1-211161-2
	A6				1-211161-1
PRELIMINARY NOT RELEASED FOR PRODUCTION	A4	.185 [4.70]	.136 [3.45]	#10 AWG	211161-4
PRELIMINARY NOT RELEASED FOR PRODUCTION	A4	.230 [5.84]	.181 [4.60]	#8 AWG	211161-3
	A3	.185 [4.70]	.136 [3.45]	#10 AWG	211161-2
	A3	.230 [5.84]	.181 [4.60]	#8 AWG	211161-1
	FINISH	DIM B	DIM A	WIRE SIZE	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN C.C.THOMAS 9-6-00	TE Connectivity
			0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 [0.13] 4 PLC ± - ANGLES ± -	CHK CHAD BAKER 9-6-00 APVD CHAD BAKER 9-6-00 PRODUCT SPEC APPLICATION SPEC	
MATERIAL SEE CALLOUTS	FINISH SEE CALLOUTS	WEIGHT -	SCALE 10:1	SHEET 1 OF 1	RESTRICTED TO -
CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779	DRAWING NO C-211161	REV T