




1		2		3		4		5		6		7																																																																																																																														
A	PLUG COMPONENT			PLUG STRIP DIMENSION			SJT 16AWGx3C 60°C Unshielded Black Length 1000±30	END STRIP DIMENSION			CONNECTOR COMPONENT																																																																																																																															
	COLOR	DESCRIPTION	Q'ty	R.I.J	R.O.J	COLOR		R.O.J	R.I.J	COLOR	COLOR	DESCRIPTION	Q'ty																																																																																																																													
	40P BLACK	IH-500(320 C14)	1	6 ⁺¹ ₋₀	19 ± 1	BLACK(L)		6 ⁺¹ ₋₀	15 ± 1	BLACK(L)	40P BLACK	IH-501(320 C13)	1																																																																																																																													
	Nickel-Plated	GEM 98672BS-1	3	6 ⁺¹ ₋₀	19 ± 1	WHITE(N)		6 ⁺¹ ₋₀	15 ± 1	WHITE(N)	True color	Assembly Body 111-001-005	1																																																																																																																													
	BLACK Outer Body	GEM 8671P	1	6 ⁺¹ ₋₀	19 ± 1	GREEN(E)		6 ⁺¹ ₋₀	15 ± 1	GREEN(E)																																																																																																																																
B																																																																																																																																										
C																																																																																																																																										
D																																																																																																																																										
E	Material: - SJT 3 x 16AWG(1.31mm²) VW-1, 60°C 300V - Jacket Color: Black - E - Green; L - Black; N - White Electrical: 100% Open & Short Testing - Insulation Resistance: 100MΩ (min.) - Voltage: 500V DC / 1 minute																																																																																																																																									
F	 Hank Dimension  Wire Cross section																																																																																																																																									
G	<table><tr><td>Scale</td><td>Free</td><td></td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td colspan="4">Title</td></tr><tr><td colspan="2">TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>10.10.15</td><td>Wilson</td><td colspan="4">Power Extension cord - SJT</td></tr><tr><td>X.</td><td>±X</td><td></td><td></td><td></td><td></td><td></td><td>Approved</td><td>10.10.15</td><td>Groll</td><td colspan="4">60°C 16AWG M/F, Unshielded 1 Meter</td></tr><tr><td>X.X</td><td>±X</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td colspan="4">ASSMANN WSW-No.</td></tr><tr><td>X.XX</td><td>±X</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td colspan="4">AK500/16-OE-11-1</td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td colspan="4">Drawing-No.</td></tr><tr><td>X.°</td><td>±X°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td colspan="4">rev00</td></tr><tr><td>X.X°</td><td>±X°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td colspan="4">Sheet</td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td></td><td>Date</td><td>Name</td><td colspan="3"></td><td colspan="4">1/1</td></tr></table> Unit: mm RoHS Compliant													Scale	Free						Date	Name	Title				TOLERANCE							Drawn	10.10.15	Wilson	Power Extension cord - SJT				X.	±X						Approved	10.10.15	Groll	60°C 16AWG M/F, Unshielded 1 Meter				X.X	±X									ASSMANN WSW-No.				X.XX	±X									AK500/16-OE-11-1				DIM	TOL									Drawing-No.				X.°	±X°									rev00				X.X°	±X°									Sheet				Angle	TOL	Id.	Modification		Date	Name				1/1			
Scale	Free						Date	Name	Title																																																																																																																																	
TOLERANCE							Drawn	10.10.15	Wilson	Power Extension cord - SJT																																																																																																																																
X.	±X						Approved	10.10.15	Groll	60°C 16AWG M/F, Unshielded 1 Meter																																																																																																																																
X.X	±X									ASSMANN WSW-No.																																																																																																																																
X.XX	±X									AK500/16-OE-11-1																																																																																																																																
DIM	TOL									Drawing-No.																																																																																																																																
X.°	±X°									rev00																																																																																																																																
X.X°	±X°									Sheet																																																																																																																																
Angle	TOL	Id.	Modification		Date	Name				1/1																																																																																																																																
H	<table><tr><td>1</td><td>2</td><td>3</td><td>4</td><td>5</td><td>6</td><td>7</td></tr></table>													1	2	3	4	5	6	7																																																																																																																						
1	2	3	4	5	6	7																																																																																																																																				