


Number of contacts



96, 64, 32




Female connectors

Identification	No. of contacts	Contact arrangement	Part number	Performance levels according to IEC 60603-2.	Explanation chapter 00
			3	2	1
Female connector with angled solder pins Length 2.8 mm	96		09 73 296 7801 09 73 496 7801 ^{b)}	09 73 296 6801 09 73 496 6801 ^{b)} 09 73 796 6801 ^{c)}	09 73 296 2801
	96			09 73 296 6804 ^{d)} 09 73 496 6804 ^{b)d)}	09 73 496 2804 ^{b)d)}
	64		09 73 264 7801 09 73 464 7801 ^{b)}	09 73 264 6801 09 73 464 6801 ^{b)}	09 73 264 2801
	64			09 73 264 6804 ^{d)} 09 73 464 6804 ^{b)d)}	09 73 264 2804 ^{d)} 09 73 464 2804 ^{b)d)}
	32		09 73 232 7801	09 73 232 6801 09 73 232 6811	09 73 232 2801
	32				
Length 4.3 mm	96			09 73 496 6855 ^{b)}	

Dimensions

Board drillings
Mounting side

Cross section of solder terminations



Cross area (A) of contacts row a, b, c: A = 0.20 - 0.23 mm²

Dimensions in mm

Other contact arrangements on request

^{b)} Connectors with snap-in clips see chapter 00^{c)} Connectors with coding see chapter 00^{d)} CTI > 400