

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0901200764

Status:

Active

Overview:

C-Grid III™

Description:

2.54mm (.100") Pitch C-Grid III™ Header, Single Row, Vertical, 4 Circuits, 0.38μm (15μ") Gold (Au) Selective Plating

Documents:

3D Model

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

PCB Headers

Series

90120

Application

Wire-to-Board

Overview

C-Grid III™

Product Name

C-Grid III™

Physical

Breakaway

Yes

Circuits (Loaded)

4

Circuits (maximum)

4

Color - Resin

Black

First Mate / Last Break

No

Glow-Wire Compliant

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

Polyester

Number of Rows

1

Orientation

Vertical

PC Tail Length (in)

0.114 In

PC Tail Length (mm)

2.90 mm

PCB Locator

No

PCB Retention

None

Packaging Type

Bag

Pitch - Mating Interface (in)

0.100 In

Pitch - Mating Interface (mm)

2.54 mm

Plating min: Mating (μin)

15

Plating min: Mating (μm)

0.38

Polarized to Mating Part

No

Polarized to PCB

No

Shrouded

No

Stackable

No

Temperature Range - Operating

-55°C to +125°C

Termination Interface: Style

Through Hole

Electrical

Current - Maximum

3A

Voltage - Maximum

350V


Solder Process Data

Duration at Max. Process Temperature (seconds)

5

Lead-free Process Capability

Wave Capable (TH only)



Series

image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

90120Series

Mates With

90147 C-Grid® PC Board Connector. 90123 C-Grid III™ Modular Crimp Housing

Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	230

Material Info

Reference - Drawing Numbers

Sales Drawing	SDA-90120
---------------	-----------

This document was generated on 01/14/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION