







GENERAL TOLERANCES: $\pm 0.10(0.25)$ EXCEPT ON
PCB LAYOUT AND CONTACTS SPACING $\pm .006(0.15)$

ELECTRICAL:

RATED CURRENT: 1.5A

RATED VOLTAGE: 30V (rms) MAX

FORCES:

MATING FORCE: 35N MAX

UNMATING FORCE: 10N MIN

MATERIALS:

SHELL: COPPER ALLOY, NICKEL PLATED

CONTACTS: COPPER ALLOY GOLD PLATE ON CONTACT AREA

TIN ON TAIL END


GOLD FLASH

30 MICROINCHES OF GOLD 260 CONTACT CODE

INSULATOR: THERMOPLASTIC (HIGH TEMPERATURE RESISTANCE)

PART NUMBER: 690-004-260-013

CONTACT CODE




ISSUE NUMBER

RE-DWG.	APR.22/08	⑤
F.BRIONES	SEP.14/08	⑥
REMOVE 15u" GOLD	JUN.29/10	⑦
TAILS DIM'S ADDED	JUN.22/11	⑧
TOLERANCES ADDED	JUN.29/11	⑨
ADD NOTES FORCES	JUN.26/14	⑩
NEW METAL SHELL	SEPT.12/14	⑪
ADD ELEC. SPECS	APR.11/2016	⑫
NEW TOOLING	OCT.30/2016	⑬



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES
2011/65/EU FOR ROHS COMPLIANCY.

USB CONNECTOR A TYPE, VERTICAL, SINGLE DECK



THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC. AND
SHALL NOT BE REPRODUCED OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO. 690-004-260-013	DRAWN: J.CHOW	DATE: OCT 16/98
CHECKED:	DATE:	
SCALE: (IN C.A.D. 1:1)	SHEET 1 OF 1	ISSUE 13
DRAWING NUMBER 690-004-260-013		