

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD




-

-

-

-

-



B-B

A-A

5.6 MAX.

4.0 MAX.

5.4

3.9

NOTES:

1. WIRE RANGE

CONDUCTOR: 0.75mm² - 2.5mm²


INSULATION DIAMETER: 2.3mm - 3.9mm

REEL	BRASS PRE-TIN	RECEPTACLE H3374ET/R8000	1-1627215-4
REEL	BRASS	RECEPTACLE H3374/R8000	1-1627215-3
LP	BRASS	RECEPTACLE H3374/10000	1-1627215-2
LP	BRASS	RECEPTACLE H3374/1000	1-1627215-1
LP	BRASS	RECEPTACLE H3374/100	1-1627215-0
REMARKS	MATERIAL	DESCRIPTION	PART No.

THIS DRAWING IS A CONTROLLED DOCUMENT.

ALL DIMENSIONS IN mm:

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
DIMENSION (mm)	TOLERANCE(+/-mm)
LESS THAN 10	0.4
OVER 10 TO 30	0.5
OVER 30 TO 80	0.7
OVER 80 TO 250	1.0
ANGLES	±2°



MATERIAL

FINISH

DWN: W.RIEDE 2.12.04

CHK: H.THA 2.12.04

APVD: W.RIEDE 2.12.04

PRODUCT SPEC:

APPLICATION SPEC:

WEIGHT:

tyco Tyco Electronics Corporation
Electronics AUSTRALIA

NAME:

RECEPTACLE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

© 1627215

-

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 OF 1

REV 0

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA, USA.