

Crimping pliers - CRIMPFOX CENTRUS 6H - 1213146

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² to 6 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

Product Features

- ✓ Ergonomic handle design ensures comfortable, fatigue-free handling
- ✓ With a particularly small handle width, the tool fits perfectly in your hand
- ✓ Sturdy plastic guard over the head of the pliers protects the tool against damage caused by dropping
- ✓ Up to 30% lower actuation force, thanks to optimized leverage
- ✓ Pressure lock ensures consistently high quality crimping results



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	470.0 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	180 mm
Width (a)	70 mm

General

Color	black
Compression	HEX crimp
Type of contact	Insulated and uninsulated ferrules
Designation	Crimping position 1

Crimping pliers - CRIMPFOX CENTRUS 6H - 1213146

Technical data

General

Min. cross section	0.14 mm ²
Max. cross section	6 mm ²
AWG min	26
AWG max	10

Classifications

eCl@ss

eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 8.0	21049090

ETIM

ETIM 4.0	EC000168
ETIM 5.0	EC000168

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC
