








LOC		DIST		REVISIONS					
HM		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					J	REV ECO-12-019894	12NOV2012	JM	SJ
					J1	REV ECO-14-002629	25FEB2014	JM	SJ

- 1 MATERIAL: JACK HOUSING - POLYCARBONATE, 94V-0 RATED.
110 BLOCK - POLYCARBONATE.
ARRAY TRAY - PBT POLYESTER.
JACK CONTACTS ARRAY - BERYLLIUM COPPER, PLATED WITH 1.27µm [.0000501] MINIMUM THICK GOLD IN LOCALIZED AREA AND 3.81µm [.0001501] MINIMUM THICK MATTE TIN IN BOARD INTERFACE AREA OVER 1.27µm [.0000501] MINIMUM THICK NICKEL UNDERPLATE.
IDC TERMINALS - PHOSPHOROUS BRONZE, PLATED WITH 3.81µm [.000151] MINIMUM THICK MATTE TIN OVER 1.27µm [.000051] MINIMUM THICK NICKEL UNDERPLATE.
- 2 SL 110 JACK WILL TERMINATE 22-24 AWG SOLID AND 24-26 AWG STRANDED CONDUCTORS, 1.27[.050] MAXIMUM INSULATION DIAMETER.
- 3 CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68 SUBPART F REQUIREMENTS.
- 4 MOUNTING PANEL THICKNESS 1.47 - 1.60 [.058 - .063].
- 5 THESE TWO SUGGESTED CUTOUT OPENINGS ARE USED IN TANDEM WITH DUAL FRONT AND BACK CUTOUTS.
- 6 ONE MODULAR JACK ASSEMBLY PER POLYBAG.
- 7 REFER TO 408-8858 FOR TERMINATION INSTRUCTIONS USING SL SERIES TOOL TERMINATION. REFER TO 408-8602 FOR TERMINATION INSTRUCTIONS USING 110 PUNCH DOWN TOOL.



6	ALPINE WHITE	1-1375192-3
	BLUE	1375192-6
	GRAY	1375192-4
	BLACK	1375192-2
PACKAGE	LIGHT ALMOND	1375192-1
	HOUSING COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PITTS 05NOV01	 TE Connectivity		
DIMENSIONS: MM[Inches]		CHK L. SMITH 15NOV01			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. DOOLEY 15NOV01	NAME ASSEMBLY, SL 110 JACK, CATEGORY 3		
		PRODUCT SPEC 108-131001	SIZE CAGE CODE DRAWING NO		
		APPLICATION SPEC 	RESTRICTED TO		
		WEIGHT	A100779C1375192		
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV J	
		MATERIAL			