



**RoHS
Compliant**

[illegible]

- Type: Upright, Through hole
- Contact Timing: Shorting type, make before break
- Contact Rating: 300mA at 125 VAC
- Termination: PCB mount
- Contact Resistance: 20 milliohms max.
- Insulation Resistance: 100 megohms min. at 500 VDC
- Dielectric Strength: 500 VRMS
- Actuation Force: 400 ±150 grams
- Operating Life: 15,000 cycles

Material:

- Housing: Steel, bright tin plated
- Base: Phenolic
- Actuator: PB1T, UL94V-0
- Moving Contacts: Phosphor bronze, 30 micro-inches gold over 50 micro-inches
- Fixed Contact/Terminals: Brass, 30 micro-inches gold over 50 micro-inches
- Plating - Gold Plating

Environmental:

- Operating Temperature: -40°C to +85°C

- Housing: Steel, bright tin plated
- Base: Phenolic
- Actuator: PBT, UL94V-0
- Moving Contacts: Phosphor bronze,
30 micro-inches gold over 50 micro-inches nickel
- Fixed Contact/Terminals: Brass.

- Operating Temperature: -40°C to +85°C

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

JEFF McVICKER
CHECKED BY:

DRAWING TITLE:
Side Switch, Miniature, Upright, DP3T, PCB Mount

SPC21213

11M0408.dwg

RE

DATE:

SCALE:

11/35/03

U.O.M.: Millimeters

SHEET:

OF 1