

48567.75




FIG "F"

CATALOG NUMBER	FIG. NO.	COMMERCIAL COPPER CABLE RANGE			METRIC COPPER CABLE RANGE			B"	H"	J" DIA.	L"	T"	W"
		COMPLETE CABLE RANGE	SMALL GROOVE	LARGE GROOVE	COMPLETE CABLE RANGE	SMALL GROOVE	LARGE GROOVE						
NAS29-N	1B							60.5 2.38	45.7 1.80	3/8"-16	98.6 3.88 142.7 5.62		50.8 2.00
NAS29-2N	1D	6 SOL. (.162 DIA.) TO	6 SOL. (.162 DIA.) TO	2/0 STR. (.420 DIA.) TO	10mm ² (.412mm DIA.) TO	10mm ² (.412mm DIA.) TO	70mm ² (.922mm DIA.) TO						
NAH29-34N	1E	250 kcmil (.575 DIA.)	1/0 STR. (.372 DIA.)	250 kcmil (.575 DIA.)	120mm ² (.440mm DIA.)	50mm ² (.27mm DIA.)	120mm ² (.440mm DIA.)	66.8 2.63	53.8 2.12	1/2"-13	149.4 5.88	6.4 .25	62.0 2.44
NAH29-22N	1A												
NAS29-34N	1E												
NAS34-N	1C							60.5 2.38	52.1 2.05	3/8"-16	148.7 5.85 142.7 5.62		50.8 2.00
NAS34-2N	1A												
NAH34-2N	1A	1/0 SOL. (.325 DIA.) TO	1/0 SOL. (.325 DIA.) TO	250 kcmil (.575 DIA.) TO	50mm ² (.27mm DIA.) TO	50mm ² (.27mm DIA.) TO	120mm ² (.440mm DIA.) TO	66.5 2.62	60.5 2.38	1/2"-13	149.4 5.88	7.9 .31	65.0 2.56
NAS34-34N	1E	500 kcmil (.813 DIA.)	4/0 STR. (.529 DIA.)	500 kcmil (.813 DIA.)	240mm ² (.20.35mm DIA.)	95mm ² (.12.80mm DIA.)	240mm ² (.20.35mm DIA.)	60.5 2.38	52.1 2.05	3/8"-16	142.7 5.62	6.4 .25	55.9 2.20
NAH34-34N	1E												
NAS40-2N	1A												
NAH40-2N	1A												
NAS40-34N	1E	2/0 STR. (.420 DIA.) TO	2/0 STR. (.420 DIA.) TO	500 kcmil (.813 DIA.) TO	70mm ² (.922mm DIA.) TO	70mm ² (.922mm DIA.) TO	240mm ² (.20.35mm DIA.) TO	66.5 2.62	58.4 2.30	3/8"-16	149.4 5.88	9.7 .38	62.0 2.44
NAH40-34N	1E	800 kcmil (1.031 DIA.)	500 kcmil (.813 DIA.)	800 kcmil (1.031 DIA.)	400mm ² (.26.10mm DIA.)	240mm ² (.20.35mm DIA.)	400mm ² (.26.10mm DIA.)						
NAS40-44N	1												
NAH40-44N	1												
NAH44-2N	1A	4/0 STR. (.529 DIA.) TO	4/0 STR. (.529 DIA.) TO	750 kcmil (1.938 DIA.) TO	95mm ² (.12.80mm DIA.) TO	95mm ² (.12.80mm DIA.) TO	400mm ² (.26.10mm DIA.) TO	73.2 2.88	66.5 2.62		155.4 6.12 180.6 7.12	11.2 .44 3.7 .31	73.8 2.88
NAH44-34N	1E	1000 kcmil (1.152 DIA.)	750 kcmil (1.938 DIA.)	1000 kcmil (1.152 DIA.)	500mm ² (.29.30mm DIA.)	400mm ² (.26.10mm DIA.)	500mm ² (.29.30mm DIA.)						
NAH44-44N	1												
NAH46-2N	1A												
NAH46-34N	1E	1000 kcmil (1.152 DIA.) TO	—	1000 kcmil (1.152 DIA.) TO	500mm ² (.29.30mm DIA.) TO	—	500mm ² (.29.30mm DIA.) TO	77.7 3.06	73.2 2.88	1/2"-13	160.3 6.31 185.7 7.31	12.7 .50 3.7 .38	81.0 3.19
NAH46-44N	1	1500 kcmil (1.442 DIA.)		1500 kcmil (1.442 DIA.)	800mm ² (.36.90mm DIA.)		800mm ² (.36.90mm DIA.)						
NAH48-2N	1A												
NAH48-34N	1E	500 kcmil (.813 DIA.) TO	500 kcmil (.813 DIA.) TO	1500 kcmil (1.442 DIA.) TO	240mm ² (.20.35mm DIA.) TO	240mm ² (.20.35mm DIA.) TO	800mm ² (.36.90mm DIA.) TO	82.6 3.25	79.2 3.12		165.1 6.50 185.7 7.31	17.5 .69 3.7 .38	85.9 3.38
NAH48-44N	1	2000 kcmil (1.632 DIA.)	1500 kcmil (1.442 DIA.)	2000 kcmil (1.632 DIA.)	1000mm ² (.41.10mm DIA.)	800mm ² (.36.90mm DIA.)	1000mm ² (.41.10mm DIA.)						
NAH48-34N	1E	2000 kcmil (1.632 DIA.) TO	—	2000 kcmil (1.632 DIA.) TO	1000mm ² (.41.10mm DIA.)	—	1000mm ² (.41.10mm DIA.)	95.2 3.75	96.8 3.81	5/8"-11	180.8 7.12	16 .63	100.6 3.96
NAH48-2N	1F	2500 kcmil (1.824 DIA.)		2500									

NOTES:

▷ COMPLETE CABLE RANGE MAY BE ACCOMMODATED BY REVERSING CAP.

2 CATALOG NUMBER NAH48-44NTMH2 INCLUDES
THE NAH48-44N TERMINAL SHOWN AND THE
TMH2 KIT CONSISTS OF:
(4) 1/2 X 1.75 LONG HEX HEAD BOLTS
(4) 1/2 HEX NUTS
(4) 1/2 SPLIT LOCK WASHERS

MATERIALS:
CAST COPPER ALLOY
(4) 1/2 FLAT WASHERS
ALL HARDWARE IS SILICONE BRONZE

GENERAL NOTES:

1. ALTHOUGH THIS DRAWING MAY ORIGINALLY HAVE BEEN DEVELOPED TO BE USED IN THE ELECTRIC DESIGN OF NON-SPECIFIC TECHNOLOGIES MAY RESULT IN THIS COPY NOT BEING TO SCALE, THEREFORE, DO NOT SCALE THIS PRINT.
2. THE DIMENSIONS, TOLERANCES AND SPECIFICATIONS OF THIS DRAWING ARE PREVIOUS TO THE DEFINITION OF THE FUNCTIONAL REQUIREMENTS FOR THIS COMPONENT OR PRODUCT. ANY PART MEETING THESE REQUIREMENTS SHALL BE CONSIDERED AS COMPLIANT.

THIS DRAWING AND/OR SPECIFICATION IS THE PROPERTY OF FORMAN ENGINEERING CO. INC. IT IS TO BE USED IN STRICT CONFIDENCE AND SHALL NOT BE REPRODUCED, OR COPIED, OR DISCLOSED TO OTHERS, OR USED AS THE BASIS FOR THE MANUFACTURE OF ANY PRODUCT OR SERVICE WITHOUT THE WRITTEN PERMISSION OF FORMAN ENGINEERING CO. INC.

TERMINAL			
CAT. NO. <i>NAS-N</i>		<i>(TABLE)</i>	
DRAWN <i>ASJ</i>		DESIGNED <i>H.C. 12-8-83</i>	
<i>12-8-83</i>		SEL. APPROV. <i>12/14/83</i>	
FRAMPHONE CONNECTORS USA INC.		PROJ. APPROV.	
BURNBY ELECTRICAL		DRAWING NO.	
 MANCHESTER, NH 03028 U.S.A.		SE79584	
		6	