


PIN RECEPTACLES

FOR .015" - .025" DIAMETER PINS

1707

1707-0-19-XX-30-XX-10-0


Press-fit in .061 mounting hole
Wire Crimp Termination. Accepts wire
sizes 22 AWG Max. / 24 AWG Min.



0240

0240-0-15-XX-30-XX-04-0


Press-fit in .059 mounting hole



0307

0307-0-15-XX-30-XX-04-0


Press-fit in .059 mounting hole



1753

1753-0-15-XX-30-XX-04-0


Press-fit in .057 mounting hole



1705/1706/1762

17XX-0-15-XX-3X-XX-04-0

Press-fit in .057 mounting hole




Basic Part Number	Height A
1705-0	.165
1706-0	.218
1762-0	.300

0672

0672-X-15-XX-30-XX-10-0

Swage mount in .049 hole




Basic Part Number	Board Thickness	Length V
0672-1	.031	.052
0672-2	.062	.084
0672-3	.094	.115
0672-4	.125	.146

1024/1104

1XX4-0-18-XX-30-XX-10-0

Press-fit in .059 mounting hole
Accepts wire sizes up to .028" dia.




Basic Part Number	Length L
1024-0	.290
1104-0	.450

0498

0498-0-15-XX-35-XX-04-0


Press-fit in .057 mounting hole



8131

8131-0-15-XX-30-XX-10-0

Press-fit in .057 mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$

Diameters: $\pm .002$

Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 1X - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 200 μ " TIN/LEAD OVER NICKEL
- ◆ 80 200 μ " TIN OVER NICKEL (RoHS)
- ◆ 15 10 μ " GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 02 100 μ " TIN/LEAD OVER NICKEL
- ◆ 84 100 μ " TIN OVER NICKEL (RoHS)
- ◆ 27 30 μ " GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#30 or #35 CONTACT (DATA ON PAGE 253 & 254)

(For alternate contact choices, see groups B and C on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com