

LOC	DIST	REVISIONS					
A1	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C38	ECR-18-000171	05JAN2018	KD	RR
			C39	ECR-18-001281	24FEB2018	LZ	RR

REMARKS/Bemerkungen

- 1

CAVITY SUITABLE FOR STANDARD TIMER CONTACTS LISTED IN PROD.SPEC. 108-18049, ITEM 3.3.2
Kammer geeignet für Standard Timer Kontakte gelistet in Prod. Spec. 108-18049, Punkt 3.3.2
- 2

CONTACT CAVITY NO.
Kontaktkammernummerierung
- 3

MATING STOP
Tiefenanschlag
- 4

AREA FOR TE LOGO ACC: TO SPEC 202-36
Bereich für TE Logo nach Spec. 202-36
- 5

POLARIZATION RIB POSITION "a" AND/OR "b"
Polarisierungsrippe Position "a" und/oder "b"
- 6

KEYING RIB POSITION "c" AND/OR "d"
Kodierrippe Position "c" und/oder "d"
- 6a

KEYING RIB POSITION "c" AND/OR "d" AT THE END WALLS OF THE HOUSING
Kodierrippe Position "c" und/oder "d" an den Gehäusestirnseiten
- 7

LOCKING LATCH
Rasthaken
- 8

TE PART NO (PN)
TE Bestell Nr. (PN)
- 9

DESIGN OF THE HOUSINGS ACC. TO RAST 5 STANDARD
Gehäuseausführung gemäss RAST 5 Vorgabe
- 10

GENERAL SUITABLE TAB HEADER SEE RAST 5 PERFORMANCE
Generell passende Flachsteckerwannen siehe RAST 5 Vorgabe
- 11





PACKAGING: BULK PACKAGING IN CORRUGATED BOX PN 740580-2
2 POS. 2500 PIECES PER BOX / 3 POS. 2000 PIECES PER BOX
Verpackung: Schüttgut in Versandkarton Pn 740580-2
2pol. 2500 Stück per Karton / 3pol. 2000 Stück per Karton
- 12

DIMENSION A, B C AND D SEE SHEET 2 OF 3
- 13

MATERIAL CORRESPONDS TO THE REQUIRMENT EN 60335
(INCL. GLOW WIRE TEST 750° WITHOUT FLAME)
Material entspricht den Anforderungen der EN 60335
(inkl. Glühdrahttest 750° ohne Flamme)
- 14

RATIO NUMBER OF THE KEYING VERSION,INKJET PRINTED. SEE SHEET 2
Kodierungskennnummer, mit Tintenstrahlendrucker aufgebracht . siehe Blatt 2
- 15


PRELIMINARY- NOT RELEASED FOR PRODUCTION



SECTION A-A / Schnitt A-A


SECTION B-B / Schnitt B-B

5 POSITION
STD. TIMER MARK-II HOUSING




SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Kishor M	18-10-07	TE Connectivity			
DIMENSIONS:		CHK K.Munz	18-10-07				
mm		APVD T.Klenner	18-10-07	NAME STANDARD TIMER HSG. RAST 5 MARK II Standard Timer Gehäuse RAST 5 Mark II			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC.			
		0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±°		APPLICATION SPEC.			
MATERIAL		SEE TABLE		SIZE			
SHEET 2 OF 3		-		CAGE CODE			
		-		DRAWING NO			
		-		RESTRICTED TO			
		-		A 1 00779 ©=1241961			
		-		Customer Drawing			
				SCALE 5:1 SHEET 1 OF 3 REV C39			



UL94 V0 & GWT 750 NF										
UL94 V0 & GWT 750 NF	2322917-4	4	4	0.5	20	15	UL94 V0 & GWT 750 NF	NATURAL	1	
	2322917-2	2			10	5		NATURAL	1	
	2315717-1	2			10	5		NATURAL	C	
	2315717-2	2	10	5	NATURAL	C				
	2315717-3	2	10	5	NATURAL	C				
	2315717-4	4	4	0.5	20	15		NATURAL	C	
	2315717-5	4			20	15		NATURAL	C	
	2315717-6	3			15	10		NATURAL	C	
	2315717-7	3			15	10		NATURAL	C	
	PART NO.	POS			DIM C	DIM D		DIM A	DIM B	MATERIAL



ALL OTHER DIMENSIONS SEE SHEET 1 OF 3
Alle anderen Masse siehe Seite 1 von 3

SPECIAL MATERIAL									
	1955507-4	4	6	1	20	15	PA66 UL 94 V0	NATURAL	1
	9-1955506-2	2			10	5		NATURAL	1
	6-124 1961-7	3	4	0.5	15	10	PA 6 UL94V-2	NATURAL 	1
	4-124 1961-7	3			15	10	PA 6 UL94V-2	NATURAL 	A
	3-124 1961-7	3			15	10	PA 6 UL94V-2	NATURAL 	A
	1-1955422-7	3			15	10	PA 66 UNFILLED UL94 V0	NATURAL	A
	5-1955422-7	3			15	10	PA 66 UNFILLED UL94 V0	NATURAL	A
	4-1955422-3	2	6	1	10	5	PA 66 UNFILLED UL94 V0	NATURAL	A
	2-124 1817-3	3	4 or 6	0.5 or 1	15	10	PA 66 UL94 V-2	Green	E
	0-1955422-6	3	4	0.5	15	10	PA 66 UNFILLED UL94 V0	NATURAL	A
	8-124 1961-8	3			15	10	PA 6 UL94V-2	natural 	C
	0-124 1961-8	3			15	10			A
8-124 1961-3	2	10			5	C			
3-124 1961-1	2	10			5	PA 6 UL94V-2	NATURAL 	C	
0-1955422-1	2	10	5	PA 66 UNFILLED UL94 V0	NATURAL	A			
PART NO	POS	DIM C 	DIM D 	DIM A 	DIMM B 	MATERIAL	COLOUR Farbe	REV./Rev.	

[illegible]

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2011

ALL RIGHTS RESERVED.

2 POSITION VARIANTS

2.00

0-969484-1

2.14

1-969484-1
2315717-2

2.13

2-969484-1

2.12

3-969484-1 OBSOLETE

2.11

4-969484-1

2.10

5-969484-1 OBSOLETE

2.09

6-969484-1

2.07

7-969484-1 OBSOLETE

2.06

8-969484-1

2.04

9-969484-1 OBSOLETE

2.03

0-969484-2

2.02

1-969484-2 OBSOLETE

2.08

2-969484-2

2.21

3-969484-2

2.99

4-969484-2
2315717-1

2.20

5-969484-2

2.19

6-969484-2

2.18

7-969484-2

2.17

8-969484-2
2315717-3

2.16

9-969484-2

2.31

0-969484-3

2.15

1-969484-3 OBSOLETE

2.05

2-969484-3 OBSOLETE

2.30

3-969484-3 OBSOLETE

Ohne/None

4-969484-3

Ohne/None

5-969484-3

Ohne/None

6-969484-3

Ohne/None

7-969484-3 OBSOLETE

Ohne/None

8-1241961-2

Ohne/None

9-1241961-2

Ohne/None

0-1241961-1

PA6

2-1241961-2

PA6

3-1241961-2

PA6

6-1241961-2

PA6

7-1241961-2

PA6

8-1241961-2
8-2178412-2

PA6

9-1241961-2

PA6

0-1241961-3

PA6

3-1241961-3 OBSOLETE

PA6

4-1241961-3

PA6

5-1241961-3

PA6

6-1241961-3

PA6

7-1241961-3

PA6

6-1241983-2

PA6

8-1241983-2

PA6

5-1241983-3

0-1241983-2

1-1241983-2

2-1241983-2

3-1241961-1

8-1241961-3
2322917-2

4-1955422-3

9-1955506-2

0-1955422-1

PRELIMINARY

3 POSITION VARIANTS

3.00

0-969484-6 OBSOLETE

3.38

1-969484-6 OBSOLETE

3.18

2-969484-6

3.37

3-969484-6

3.35

4-969484-6 OBSOLETE

3.33

5-969484-6 OBSOLETE

3.32

6-969484-6 OBSOLETE

3.20

7-969484-6

3.10

8-969484-6

3.09

9-969484-6

3.08

0-969484-7 OBSOLETE

3.39

1-969484-7
1-1955422-7 PRELIMINARY

3.31

2-969484-7 OBSOLETE

3.40

3-969484-7

3.99

4-969484-7 OBSOLETE

Ohne/NONE

5-969484-7

3.45

6-969484-7 OBSOLETE

3.47

7-969484-7 OBSOLETE

3.65

8-969484-7

3.48

9-969484-7 OBSOLETE

3.66

0-969484-8

Ohne/NONE

1-969484-8 OBSOLETE

Ohne/NONE

2-969484-8

PA6

9-1241961-9

3-1241961-8

9-969484-9

4-1241961-8

5-1241961-8

4 POSITION VARIANTS

0-1241959-4

2-1241959-4

4-1241959-4

0-1955507-4

0-2315717-5

2-1241817-4

3-1241817-4

3-1241817-4
2322164-1
2322917-4

0-1241959-5

0-1241817-5

2-1241817-5

5 POSITION VARIANTS

0-1241961-6

2-1241961-7

1-1241961-8

2-1241961-8

6-1241961-8

7-1241961-7

7-1241961-8

1-1241961-7

9-1241961-8

8-1241961-8

2-1241817-3

0-1241961-8

3-1241961-7

4-1241961-7

5-1955422-7

6-1241961-7

1-1241961-9

0-1955422-6

6-2178575-7

0-2315717-6

0-2315717-7

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: Kishor M. 18-10-07
CHK: K. Munz 18-10-07

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.2
1 PLC ±0.2
2 PLC ±0.2
3 PLC ±0.2
4 PLC ±0.2
ANGLES FINISH

MATERIAL: SEE TABLE
SHEET 2 OF 3

WEIGHT: -

Customer Drawing

APVD: T. Klenner 18-10-07
PRODUCT SPEC: 108-18049
APPLICATION SPEC: -

NAME: STANDARD TIMER HSG. RAST 5 MARK II
Standard Timer Gehäuse RAST 5 Mark II

SIZE: A1
CAGE CODE: 00779
DRAWING NO: 1241961

RESTRICTED TO: -

SCALE: 5:1
SHEET: 3 OF 3
REV: C39

4805 (3/11)