

Power choke coils

■ PCMB series.

Features

- Low profile (3.0 mm max) and small size (7.3mm x6.6mm)
- Occupying small board spaces
- Low loss and high saturating current.


Applications

- PCs, servers, power sources, mobile devices, flat screen TVs etc.


Specifications

*All made to order.

Dimensions • Electrical characteristics



Equivalent circuits



Series Name	Size L x W x T (mm)	LO Inductance (uH)	DC resistance (mOhm)		Rated current (A)	Saturating current(A)	Packaging
			Typical	Max			
PCMB042T- XXXMS	4.15±0.35 x 4.0 ±0.3 x 1.8±0.2	0.1	3.5	4	12	22	2,000 pcs/reel
		0.22	6	6.6	9	12.5	
		0.47	12.5	14	7	9.5	
		1.0	24	27	4.5	7	
		1.5	38	46	4	6	
		2.2	52	58	3	5	
		3.3	74	87	2.5	4	
		0.68	11	12	8.5	14	
		1.0	13	14	7	11	
		1.2	15	16	6.5	11	
PCMB053T- XXXMS	4.85±0.35 x 4.7 ±0.2 x 2.8±0.2	1.5	18	20	6	10	2,000 pcs/reel
		2.2	29	35	5.5	9	
		3.3	32	38	5	7	
		0.1	1.5	1.7	32.5	60	
		0.2	2.4	3.0	24	41	
		0.22	2.5	2.8	23	40	
		0.25	3.0	3.5	21	39	
		0.33	3.5	3.9	20	30	
		0.47	4.0	4.2	17.5	26	
		0.56	4.7	5	16.5	25.5	
PCMB063T- XXXMS	6.95±0.35 x 6.6 ±0.2 x 2.8±0.2	0.68	5	5.5	15.5	25	1,000 pcs/reel
		0.82	6.7	8	13	24	
		0.9	9	10	11	22	
		1.0	9	10	11	22	
		1.2	10	12	10	20	
		1.5	14	15	9	18	
		2.2	18	20	8	14	
		2.5	20	22	7	14	
		3.3	28	30	6	13.5	
		4.7	37	40	5.5	10	
PCMB065T- XXXMS	7.05±0.35 x 6.6 ±0.2 x 4.8±0.2	6.8	54	60	4.5	8	1,000 pcs/reel
		0.2	0.9	1.2	32	50	
		0.22	1.2	1.4	30	50	
		0.36	3.2	3.5	21	25	
		0.40	3.2	3.5	20	23	
		0.47	3.5	3.9	20	23	
		0.56	3.4	3.6	20	18	
		0.68	3.9	4.2	18	16	
		0.82	4.6	4.9	16.5	17	
		1.0	5.6	6.5	13	15	
PCMB103T- XXXMS	11.15±0.35 x10.0 ±0.3 x 2.8±0.2	1.2	6	7.5	11	12	500 pcs/ reel
		1.5	6.7	7.5	11	12	
		2.2	11.2	12.5	8	12	
		3.3	19.9	20.9	7	8	
		4.7	23	25	6.5	7	
		8.2	40	43	5.5	5.5	
		0.36	1.3	1.6	23	28	
		0.47	2.1	2.5	23	26	
		0.56	2.4	3	22	24	
		0.68	2.9	3.4	21	23	
PCMB103E- XXXMS	11.15±0.35 x10.0 ±0.3 x 3.3±0.2	1.0	5.3	6	13	18	500 pcs/ reel
		1.5	6.5	7.5	13	20	
		2.2	8	9	13	16	
		3.3	14.5	16	9	14	
		4.7	20.5	22.5	7	13	
		8.2	35	45	5	8.5	
		10	50	55	5	7.5	
		1.0	2.7	3.0	20	27	
		1.0	2.7	3.0	20	27	
		1.0	2.7	3.0	20	27	

Series Name	Size L x W x T (mm)	LO Inductance (uH)	DC resistance (mOhm)		Rated current (A)	Saturating current(A)	Packaging
			Typical	Max			
PCMB104T- XXXMS	11.15±0.35 x10.0±0.3 x 3.8±0.2	0.15	0.5	0.65	40	75	500 pcs/ reel
		0.19	0.7	0.8	38	60	
		0.22	0.9	1.0	35	60	
		0.36	1.05	1.2	30	50	
		0.39	1.1	1.2	31	45	
		0.41	1.1	1.3	30	60	
		0.47	1.6	1.8	26	40	
		0.56	1.6	1.8	25	33	
		0.68	2.4	2.7	22	39	
		0.88	2.7	3.0	20	38	
PCMB104E- XXXMS	10.85±0.35 x10.0±0.3 x 3.8±0.2	1.0	3	3.3	18	28	500 pcs/ reel
		1.5	3.8	4.2	16	32	
		1.8	4.5	5	15	15	
		2.0	5.2	5.8	14	14	
		2.2	6.0	7	12	18	
		3.3	10.8	11.8	10	16	
		4.7	17	20	8.5	15	
		5.6	20	23	7.5	14	
		6.8	22.5	25	6.5	9	
		10	27.5	30	7.5	8.5	
PCMB104E- XXXMS	10.85±0.35 x10.0±0.3 x 4.3±0.2	15	40	45	6.25	7.0	500 pcs/ reel
		22	60	66	5.0	5.5	
		33	85	92	4.4	5.0	
		47	130	145	3.3	3.5	
		68	178	195	2.3	3.0	
		1.0	2.7	3.2	22	34	
		2.2	5.8	7	14	16	
		3.3	11	13.2	11	14.5	
		4.7	13.2	15	10	13	
		5.6	16	18.5	8.5	10.5	
PCMB105T- R47MS	11.15±0.35 x10.0±0.3 x 4.8±0.2	6.8	21.5	24	7.5	9.5	500 pcs/ reel
		0.47	0.95	1.1	36	50	
		0.22	1.1	1.3	38	65	
		0.33	1.3	1.5	36.5	62	
		0.39	1.1	1.3	38	65	
		0.47	1.7	2	32	55	
		0.56	1.8	2.2	29	51	
		0.62	1.8	2.2	29	51	
		0.68	2.3	2.5	28	49	
		1.0	3.3	3.5	24	40	
PCMB133E- XXXMS	13.45±0.35 x12.6±0.3 x 3.3±0.2	1.5	5.1	5.5	19	35	500 pcs/ reel
		2.2	7.2	8.0	16	29	
		3.3	10	12	12	27	

Rated current : the current that increases the temperature by 40°C

Saturating current : The current that reduces inductance by 30% (PCMB)

* Contact us for details.

Part numbering system

PCMB 13 - *** M S**

Part code

Size
(063T=6.6*7.3*3.0mm, 104T=10*11.5*4.0mm,
133E=12.6*13.8*3.5mm, 135T=12.6*13.8*5.0mm)

Inductance value (R56=0.56mH, R68=0.68mH)

Inductance tolerance M=±20%

Material: refer to the table for electrical characteristics