


Product Description



Application

Brass gland for earthing with strain relief and metric connection thread in accordance to EN 50262. This special earthing gland was designed on the basis of technical and economic aspects:

- Optimal earthing
- Perfect seal with antikink protection
- Cable protecting strain relief
- Simple assembly

Note

- For painted, anodised or powdered-coated housings, you will require our EMC counter nut SKINDICHT® SM-PE-M for best contact
- Counter nut to be used SKINDICHT® SM-M

Special feature

Example - order identification:

SRE-M 20 / 13.5 / 9 / 6

- 20 = Connection thread
- 13.5 = Function thread PG
- 9 = Clear width of polychloroprene-sleeve
- 6 = Clear width of earthing sleeve

Technical Data
Caution

Installation dimensions see T21

Material

Compression screw and fitting: nickel-plated brass

Anti-kink sleeve: CR/NBR O-ring: NBR Earthing

sleeve: plain brass

Degree of protection

IP 65

Range of temperature

-20°C up to +80°C

Article List

Part number	Part designation / size	Function thread PG	Outer sheath clamping range ØF mm	Inner sheath clamping range mm	Overall length C mm	Thread length D mm	Clear opening EH ØB	Clear opening F mm	SW1 / SW2 mm	Pieces / VPE
SKINDICHT® SRE-M										
52105600	20 x 1,5	13.5	7,5 - 9	4,5 - 6	59,5	6	6	9	22 / 22	25
52105610	20 x 1,5	13.5	9 - 11	5,5 - 7	59,5	6	7	11	22 / 22	25
52105620	20 x 1,5	16	11 - 13	7 - 9	64,5	6	9	13	24 / 24	25
52105630	20 x 1,5	16	11 - 13	8 - 10	64,5	6	10	13	24 / 24	25
52105640	20 x 1,5	16	13,5 - 15	9 - 11	64,5	6	11	15	24 / 24	25
52105650	25 x 1,5	21	13,5 - 15	10 - 12	78	7	12	15	30 / 30	25
52105660	25 x 1,5	21	15 - 17	12 - 14	78	7	14	17	30 / 30	25
52105670	25 x 1,5	21	17 - 19	13 - 15	78	7	15	19	30 / 30	25
52105680	25 x 1,5	21	18 - 20	14 - 16	78	7	16	20	30 / 30	25
52105690	32 x 1,5	29	18 - 20	15 - 17	90	8	17	20	40 / 40	10
52105700	32 x 1,5	29	21 - 23	17 - 19	90	8	19	23	40 / 40	10

52105710	40 x 1,5	36	23,5 - 26	20 - 22	108	8	22	26	50 / 50	5
52105720	40 x 1,5	36	27 - 30	22 - 24	108	8	24	30	50 / 50	5
52105730	40 x 1,5	36	30 - 33	26 - 28	108	8	28	33	50 / 50	5
52105740	40 x 1,5	36	32 - 35	28 - 30	108	8	30	35	50 / 50	5