




REV.	DATE	DESCRIPTION
A	12/09/03	UPDATE DRAWING FORMAT



NOTE:

1. CRIMPED CONTACT PIN,
HEX CRIMP SIZE .100"

9	HEX NUT	BRASS	NEXCOTE	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN () ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	DO NOT SCALE DRAWING	CAD FILE C:/172/172137.DWG	APPROVALS		DATE	Amphenol Connex		
8	LOCK WASHER	BRASS	NEXCOTE	1				DRAWN	G.R.S.			12/09/03	
7	GASKET	SILICONE	RED	1				CHECKED					
6	SOLDER NUT	BRASS	GOLD	1				ISSUED					
5	INSULATOR	TEFLON	NATURAL	1				SHEET	1 OF 1				
4	CONTACT PIN	PHOS. BRONZE	GOLD	1				PART NO.					
3	INNER BODY	BRASS	NEXCOTE	1				DWG. NO.					
2	INSULATOR	TEFLON	NATURAL	1				REV.					
1	OUTER BODY	BRASS	NEXCOTE	1				SIZE					
DESCRIPTION		MATERIAL		FINISH				QTY				SCALE	