

454709-1

✓ ACTIVE

AMP

TE Internal #: 454709-1

Spare & Wear Tooling, Standard

[View on TE.com >](#)

Application Tooling > Spare & Wear Tooling

Applicator & Product Style: **Standard**

Features

Other

Applicator & Product Style	Standard
----------------------------	----------

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1855041-1
HINGE BAR F.A. EMPO160TAB1800
LM & G



TE Part # 1855465-1
HDM w/FA HINGE BAR EAPR160TAB-
LOCK180O



TE Part # 1855601-1
HDM/FA EAPRHB.160TABLOC.1800
G CUT



TE Part # 567408-2
HDMHB 9EAPR160T180O G



TE Part # 680194-3
HDM*HB* 9EAPR160T1800 G



TE Part # 687395-8
HINGE BAR 9EAPR160T1800 G



TE Part # 687395-9
EF HINGE BAR 9EMPR160TL2100 T



TE Part # 7-1855041-7
SPARE PART KIT



TE Part # 687395-1
END FEED HINGE BAR APPLICATOR

Documents

Datasheets & Catalog Pages CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets Instruction Sheet (U.S.)

English

Agency Approvals CSA Certificate English

CSA Certificate

English