

MICRO SWITCH
 FREEPORT ILLINOIS, U.S.A
 A DIVISION OF HONEYWELL
 FED. MFG. CODE 91929

**MINIATURE PRECISION
 LIMIT SWITCH**

CATALOG LISTING
914CE2-3G

M 914CE2-3G

**DRAWING
 NUMBER**

ISSUE

REVISIONS

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

DRAWN

REPLACES

RELEASE NO. PR-16275

CHECK


CHECK

10 MAR 88

10 MAR 88


10 MAR 88

10 MAR 88



NOTES

- 1 - ZINC HOUSING FINISHED WITH GRAY PAINT
- 2 - BIFURCATED GOLD CONTACT BASIC SWITCH



CIRCUIT DIAGRAM

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS	
OPERATING FORCE — — —	2.7 LB MAX
RELEASE FORCE — — —	1.0 LB MIN
DIFFERENTIAL TRAVEL — —	.004 MAX
OVERTRAVEL — — — — —	.118 MIN

ELECTRICAL DATA	
CONTACT ARRANGEMENT S P D T	
UL LISTED — FILE E12252	
21 MA, 24 VDC	

SCALE	FULL
DO NOT SCALE PRINT	
TOLERANCES APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED TOLERANCES ARE ±	
DIM. mm/IN	TOL. mm/IN
NO PLACES ONE PLACE TWO PLACES THREE PLACES ANGLES	X X X, XX X, XX 1/64 0.4/0.10 0.15/0.008 X X X XX X, XX 0.07/03 0.38/0.18 0.13/0.008
DESIGN UNITS	METRIC ☐ US CUSTOMARY ☒
WEIGHT	

FD-32848-A