



ISSUE 13; September 2014 - RoHS 2011/65/EU

Description

- Standard 7 x 5mm SMD crystal. 7 x 5mm SMD crystal available in three different pad designs and two different package materials. 12SMX-A, -C, -D are ceramic package with a resin sealed ceramic lid, hermetically sealed. 12SMX-B is a ceramic package with a seam sealed metal lid, hermetically sealed. Please Note: 12SMX-B is the standard package style. For low profile version of a 7 x 5mm crystal please see our 14SMX. For tighter tolerances and stabilities please see our 14SMX. Stock parts available.
- -A 2 pad (ceramic lid)
- A ceramic package with a resin sealed ceramic lid, hermetically sealed. 2 pad device.
- -B 4 pad (metal lid)
- A ceramic package with a seam sealed metal lid, hermetically sealed. 4 pad device metal lid.
- -C 2 into 4 pad (ceramic lid)
- A ceramic package with a resin sealed ceramic lid, hermetically sealed. 2 into 4 pad device.
- -D 4 pad (ceramic lid)
- A ceramic package with a resin sealed ceramic lid, hermetically sealed. 4 Pad device, ceramic lid

Frequency Parameters

- | | |
|-----------------------|-------------------------|
| ■ Frequency | 6.0MHz to 84.0MHz |
| ■ Frequency Tolerance | ±20.00ppm to ±100.00ppm |
| ■ Frequency Stability | ±20.00ppm to ±100.00ppm |
| ■ Ageing | ±5ppm per year max |

Electrical Parameters

- | | |
|---------------------|------------------|
| ■ Load Capacitance | 10.0pF to 75.0pF |
| ■ Shunt Capacitance | 7pF max |
| ■ Drive Level | 100µW max |

Operating Temperature Ranges


- 0 to 50°C
- -10 to 60°C
- -20 to 70°C
- -40 to 85°C

Environmental Parameters




- Storage Temperature Range: -40 to 125°C

Ordering Information


- Frequency*
- Model*
- Variant*
- Frequency Tolerance (@25°C)*
- Frequency Stability (over operating temperature range)*
- Operating Temperature Range*
- Load Capacitance*
- Overtone
- Example
- 10.0MHz 12SMX-B
- 50/50/-20 to 70C/10 FUND





Outline (mm) -A = 2 pad (ceramic lid)



Solder Pad Layout




Outline (mm) -B = 4 pad (metal lid)



Pad Connection

1. Crystal
2. GND & Lid
3. Crystal
4. GND & Lid

Solder Pad Layout



Sales Office Contact Details:

UK: +44 (0)1460 270200
Germany: +49 (0) 30 408 192 300

France: +33 (0)5 34 50 91 18
USA: +1 408.273.4530

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com




Compliance

- RoHS Status Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable


Packaging Details

- Pack Style: Bulk Loose in bulk pack
Pack Size: 100
- Pack Style: Reel Tape & reel in accordance with EIA-481-D
Pack Size: 1,000
- Pack Style: R250 Tape & reel in accordance with EIA-481-D
Pack Size: 250
- Pack Style: Cutt In tape, cut from a reel
Pack Size: 10

Outline (mm) -C = 2 into 4 pad (ceramic lid)



Outline (mm) -D = 4 pad (ceramic lid)



Sales Office Contact Details:

UK: +44 (0)1460 270200
Germany: +49 (0) 30 408 192 300

France: +33 (0)5 34 50 91 18
USA: +1 408.273.4530

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com

**Electrical Specification - maximum limiting values**

Frequency Min	Frequency Max	Temperature Range	Stability (min)	Over Tone Order	ESR
		°C	ppm		Ω
6.0MHz	7.999999MHz	0 to 50 -10 to 60 -20 to 70 -40 to 85	±20 ±20 ±20 ±30	Fundamental	150
8.0MHz	9.999999MHz	0 to 50 -10 to 60 -20 to 70 -40 to 85	±20 ±20 ±20 ±30	Fundamental	80
10.0MHz	15.999999MHz	0 to 50 -10 to 60 -20 to 70 -40 to 85	±20 ±20 ±20 ±30	Fundamental	60
16.0MHz	49.999999MHz	0 to 50 -10 to 60 -20 to 70 -40 to 85	±20 ±20 ±20 ±30	Fundamental	40
50.0MHz	84.0MHz	0 to 50 -10 to 60 -20 to 70 -40 to 85	±20 ±20 ±20 ±30	3rd Overtone	60

**Stability Maximum values ±100ppm*

This document was correct at the time of printing; please contact your local sales office for the latest version.

[Click to view latest version on our website.](#)

Sales Office Contact Details:

UK: +44 (0)1460 270200
Germany: +49 (0) 30 408 192 300

France: +33 (0)5 34 50 91 18
USA: +1 408.273.4530

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com